

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P361298

Luminaire Tested: NVN-SA4D-727-U-T3

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P361298
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-14)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA4D-727-U-T3
Description: NAVION ROADWAY AND AREA LUMINAIRE
(4) 70 CRI, 2700K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 26603 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 258
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P361298
 CATALOG NUMBER: NVN-SA4D-727-U-T3

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.1 fc
 Type III - Short - N/A

REPORT NUMBER: P361298
CATALOG NUMBER: NVN-SA4D-727-U-T3

Luminous Intensity Polar Plot



— Vertical Plane Through 56-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P361298
 CATALOG NUMBER: NVN-SA4D-727-U-T3

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5924.4 | 0.0 | 5924.4 |
| | % Fixture | 22.3 | 0.0 | 22.3 |
| Street Side | Lumens | 20678.6 | 0.0 | 20678.6 |
| | % Fixture | 77.7 | 0.0 | 77.7 |
| Total | Lumens | 26603.0 | 0.0 | 26603.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 341.6 | 1.3 |
| 10°-20° | 1098.4 | 4.1 |
| 20°-30° | 1917.4 | 7.2 |
| 30°-40° | 2754.3 | 10.4 |
| 40°-50° | 3811.8 | 14.3 |
| 50°-60° | 5584.8 | 21.0 |
| 60°-70° | 6808.9 | 25.6 |
| 70°-80° | 3764.4 | 14.2 |
| 80°-90° | 521.4 | 2.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 26603.0 | 100.0 |
| 0°-180° | 26603.0 | 100.0 |




REPORT NUMBER: P361298
 CATALOG NUMBER: NVN-SA4D-727-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 1893.3 | 7.1 | | | |
| FM (30°-60°) | 9458.4 | 35.6 | | | |
| FH (60°-80°) | 9019.7 | 33.9 | | | G4/12000 |
| FVH (80°-90°) | 307.1 | 1.2 | | | G3/500 |
| BL (0°-30°) | 1464.1 | 5.5 | B3/2500 | | |
| BM (30°-60°) | 2692.5 | 10.1 | B3/5000 | | |
| BH (60°-80°) | 1553.6 | 5.8 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 214.3 | 0.8 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G4
 Type III Short





REPORT NUMBER: P361298

CATALOG NUMBER: NVN-SA4D-727-U-T3

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 56° | 65° | 75° | 85° |
|-------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 |
| 2.5° | 3499.9 | 3503.6 | 3500.9 | 3508.2 | 3499.9 | 3505.4 | 3500.9 | 3500.9 | 3498.1 | 3489.9 | 3480.7 |
| 5° | 3554.9 | 3562.3 | 3557.7 | 3565.0 | 3554.9 | 3556.8 | 3548.5 | 3548.5 | 3540.3 | 3522.8 | 3504.5 |
| 7.5° | 3641.1 | 3649.3 | 3645.7 | 3653.0 | 3639.2 | 3639.2 | 3628.2 | 3627.3 | 3610.8 | 3582.4 | 3561.3 |
| 10° | 3743.7 | 3754.7 | 3751.0 | 3762.0 | 3751.0 | 3754.7 | 3743.7 | 3743.7 | 3721.7 | 3681.4 | 3654.8 |
| 12.5° | 3893.1 | 3906.8 | 3896.8 | 3895.8 | 3891.3 | 3898.6 | 3889.4 | 3887.6 | 3867.4 | 3812.4 | 3775.8 |
| 15° | 4092.9 | 4107.5 | 4086.5 | 4084.6 | 4059.0 | 4056.2 | 4056.2 | 4053.5 | 4040.6 | 3974.7 | 3914.2 |
| 17.5° | 4322.9 | 4327.5 | 4309.2 | 4279.8 | 4246.8 | 4225.8 | 4223.0 | 4230.4 | 4230.4 | 4153.4 | 4057.1 |
| 20° | 4548.4 | 4556.6 | 4541.9 | 4509.0 | 4466.8 | 4435.6 | 4413.6 | 4428.3 | 4427.4 | 4335.7 | 4199.2 |
| 22.5° | 4794.0 | 4813.2 | 4791.2 | 4749.1 | 4699.6 | 4664.7 | 4626.3 | 4639.1 | 4640.0 | 4527.3 | 4338.5 |
| 25° | 5112.0 | 5094.6 | 5080.8 | 5021.2 | 4950.7 | 4914.9 | 4879.2 | 4892.0 | 4888.4 | 4733.5 | 4482.4 |
| 27.5° | 5393.3 | 5397.0 | 5378.7 | 5315.4 | 5233.9 | 5155.1 | 5153.2 | 5161.5 | 5147.7 | 4947.9 | 4618.0 |
| 30° | 5720.5 | 5722.3 | 5696.7 | 5639.9 | 5551.0 | 5449.2 | 5425.4 | 5439.2 | 5409.8 | 5151.4 | 4761.0 |
| 32.5° | 6045.8 | 6055.0 | 6026.6 | 5957.9 | 5886.4 | 5762.7 | 5715.0 | 5724.2 | 5650.9 | 5359.4 | 4908.5 |
| 35° | 6330.9 | 6343.7 | 6334.5 | 6288.7 | 6210.8 | 6104.5 | 6047.7 | 6042.2 | 5951.5 | 5614.2 | 5103.7 |
| 37.5° | 6621.4 | 6633.3 | 6623.2 | 6584.7 | 6553.6 | 6440.8 | 6410.6 | 6410.6 | 6253.0 | 5874.5 | 5352.1 |
| 40° | 6920.1 | 6938.5 | 6926.6 | 6873.4 | 6846.8 | 6795.5 | 6723.1 | 6705.7 | 6535.2 | 6187.0 | 5757.2 |
| 42.5° | 7197.8 | 7221.7 | 7269.3 | 7238.2 | 7184.1 | 7191.4 | 7045.7 | 7036.5 | 6911.9 | 6648.9 | 6265.8 |
| 45° | 7591.9 | 7626.7 | 7707.4 | 7683.5 | 7672.6 | 7632.2 | 7459.0 | 7450.8 | 7403.1 | 7270.2 | 6897.2 |
| 47.5° | 8021.7 | 8069.4 | 8215.1 | 8219.7 | 8337.9 | 8261.8 | 8026.3 | 7997.9 | 8008.9 | 8014.4 | 7668.0 |
| 50° | 8417.6 | 8469.9 | 8709.1 | 8821.8 | 9100.4 | 9116.9 | 8740.2 | 8714.6 | 8757.6 | 8884.1 | 8566.1 |
| 52.5° | 8733.8 | 8799.8 | 9098.6 | 9446.8 | 9924.3 | 10059.9 | 9619.1 | 9599.9 | 9631.9 | 9850.0 | 9581.5 |
| 55° | 8965.7 | 9037.1 | 9362.5 | 9996.7 | 10759.2 | 10998.4 | 10630.9 | 10612.5 | 10632.7 | 10910.4 | 10685.9 |
| 57.5° | 9019.7 | 9037.1 | 9509.1 | 10366.9 | 11463.9 | 12038.5 | 11869.0 | 11832.3 | 11733.4 | 11975.3 | 11904.7 |
| 60° | 8765.9 | 8835.5 | 9388.2 | 10497.1 | 12009.2 | 13064.0 | 13163.0 | 13117.2 | 12839.5 | 13037.5 | 12980.7 |
| 62.5° | 8250.8 | 8375.5 | 8936.3 | 10299.1 | 12222.7 | 13901.7 | 14432.3 | 14377.3 | 13898.9 | 14027.2 | 13754.1 |
| 65° | 7409.5 | 7462.7 | 8052.0 | 9616.3 | 11951.5 | 14437.8 | 15564.1 | 15536.6 | 14934.5 | 14733.8 | 13897.1 |
| 67.5° | 5904.7 | 6004.6 | 6505.0 | 8189.4 | 10841.6 | 14374.6 | 16439.3 | 16436.6 | 15610.9 | 14995.9 | 13390.3 |
| 69° | 4664.7 | 4768.3 | 5244.9 | 6746.0 | 9593.4 | 13796.3 | 16586.0 | 16618.1 | 15801.5 | 14836.5 | 12666.3 |
| 70° | 3719.0 | 3839.0 | 4166.2 | 5682.0 | 8485.4 | 13033.8 | 16464.1 | 16521.8 | 15764.8 | 14573.4 | 11998.2 |
| 72.5° | 1582.7 | 1679.9 | 1912.6 | 2929.0 | 5171.5 | 9732.7 | 15053.7 | 15271.8 | 14915.3 | 13338.1 | 9916.0 |
| 75° | 691.0 | 721.2 | 826.6 | 1194.1 | 2295.7 | 5297.1 | 11792.9 | 12196.2 | 12753.4 | 11274.2 | 7386.6 |
| 77.5° | 505.9 | 518.7 | 576.4 | 701.1 | 1030.1 | 2000.6 | 7583.7 | 7818.3 | 9197.5 | 8204.1 | 4530.9 |
| 80° | 391.3 | 400.5 | 445.4 | 515.0 | 672.7 | 809.2 | 3458.7 | 3660.3 | 5171.5 | 4213.9 | 1887.0 |
| 82.5° | 311.6 | 318.0 | 349.2 | 379.4 | 464.6 | 490.3 | 1148.3 | 1273.9 | 1909.0 | 1163.9 | 499.5 |
| 85° | 289.6 | 296.9 | 307.9 | 276.8 | 297.8 | 287.8 | 496.7 | 519.6 | 576.4 | 457.3 | 209.0 |
| 87.5° | 131.1 | 154.9 | 305.2 | 215.4 | 158.5 | 126.5 | 203.5 | 212.6 | 239.2 | 240.1 | 92.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P361298
 CATALOG NUMBER: NVN-SA4D-727-U-T3

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 | 3477.9 |
| 2.5° | 3486.2 | 3483.4 | 3488.0 | 3477.0 | 3490.8 | 3489.9 | 3485.3 | 3487.1 | 3496.3 | 3495.4 | 3496.3 |
| 5° | 3507.3 | 3505.4 | 3510.9 | 3502.7 | 3519.2 | 3524.7 | 3525.6 | 3533.8 | 3543.9 | 3546.7 | 3546.7 |
| 7.5° | 3560.4 | 3560.4 | 3563.2 | 3552.2 | 3563.2 | 3562.3 | 3557.7 | 3565.9 | 3576.0 | 3576.9 | 3576.0 |
| 10° | 3652.1 | 3653.0 | 3648.4 | 3620.0 | 3610.8 | 3586.1 | 3563.2 | 3564.1 | 3576.9 | 3587.0 | 3589.7 |
| 12.5° | 3767.5 | 3763.9 | 3743.7 | 3691.5 | 3653.0 | 3602.6 | 3578.8 | 3577.8 | 3590.7 | 3598.9 | 3601.7 |
| 15° | 3899.5 | 3889.4 | 3837.2 | 3752.0 | 3684.1 | 3634.7 | 3596.2 | 3587.0 | 3579.7 | 3570.5 | 3571.4 |
| 17.5° | 4024.1 | 4001.2 | 3914.2 | 3796.0 | 3724.5 | 3658.5 | 3584.3 | 3524.7 | 3483.4 | 3459.6 | 3452.3 |
| 20° | 4150.6 | 4105.7 | 3980.2 | 3837.2 | 3746.5 | 3626.4 | 3483.4 | 3362.5 | 3287.3 | 3252.5 | 3246.1 |
| 22.5° | 4266.1 | 4193.7 | 4041.6 | 3880.3 | 3729.1 | 3518.3 | 3293.7 | 3117.8 | 3013.3 | 2966.6 | 2970.2 |
| 25° | 4378.8 | 4278.0 | 4105.7 | 3910.5 | 3641.1 | 3327.6 | 3029.8 | 2813.5 | 2692.5 | 2640.3 | 2638.5 |
| 27.5° | 4477.8 | 4363.2 | 4175.4 | 3885.8 | 3477.0 | 3056.4 | 2717.3 | 2506.5 | 2405.7 | 2360.8 | 2353.5 |
| 30° | 4591.4 | 4470.5 | 4267.9 | 3791.4 | 3236.9 | 2742.9 | 2412.1 | 2263.6 | 2192.2 | 2147.3 | 2139.0 |
| 32.5° | 4729.8 | 4616.2 | 4344.0 | 3620.0 | 2929.9 | 2415.8 | 2173.8 | 2070.3 | 2005.2 | 1954.8 | 1945.6 |
| 35° | 4931.4 | 4808.6 | 4363.2 | 3374.4 | 2592.6 | 2157.3 | 1998.8 | 1892.5 | 1804.5 | 1739.4 | 1733.0 |
| 37.5° | 5184.4 | 5049.7 | 4319.2 | 3056.4 | 2265.5 | 1989.6 | 1853.1 | 1722.0 | 1607.5 | 1515.8 | 1501.2 |
| 40° | 5549.1 | 5345.7 | 4197.4 | 2689.8 | 2024.4 | 1860.4 | 1711.0 | 1561.6 | 1419.6 | 1312.4 | 1291.3 |
| 42.5° | 5987.2 | 5693.0 | 4010.4 | 2325.0 | 1847.6 | 1729.3 | 1569.9 | 1384.8 | 1249.1 | 1173.1 | 1162.1 |
| 45° | 6544.4 | 6054.1 | 3751.0 | 2006.1 | 1673.4 | 1598.3 | 1417.8 | 1247.3 | 1163.0 | 1107.1 | 1097.9 |
| 47.5° | 7180.4 | 6459.2 | 3478.9 | 1746.8 | 1525.9 | 1475.5 | 1295.9 | 1185.9 | 1119.0 | 1075.0 | 1066.8 |
| 50° | 7962.1 | 6916.5 | 3190.2 | 1534.1 | 1377.4 | 1327.9 | 1238.1 | 1152.0 | 1098.8 | 1064.9 | 1056.7 |
| 52.5° | 8843.8 | 7432.4 | 2982.1 | 1366.4 | 1254.6 | 1218.9 | 1207.9 | 1133.7 | 1090.6 | 1064.9 | 1056.7 |
| 55° | 9793.2 | 7957.6 | 2757.6 | 1225.3 | 1148.3 | 1158.4 | 1187.7 | 1135.5 | 1106.2 | 1075.0 | 1063.1 |
| 57.5° | 10743.6 | 8500.1 | 2507.4 | 1106.2 | 1064.0 | 1113.5 | 1174.0 | 1139.2 | 1114.4 | 1084.2 | 1073.2 |
| 60° | 11495.1 | 8843.8 | 2119.8 | 1006.3 | 997.1 | 1064.0 | 1141.0 | 1111.7 | 1079.6 | 1080.5 | 1078.7 |
| 62.5° | 11846.1 | 8825.4 | 1691.8 | 917.4 | 930.2 | 997.1 | 1087.8 | 1068.6 | 1042.0 | 1077.7 | 1080.5 |
| 65° | 11649.0 | 8385.6 | 1316.9 | 836.7 | 858.7 | 927.5 | 1032.8 | 1047.5 | 1056.7 | 1125.4 | 1134.6 |
| 67.5° | 10822.4 | 7529.6 | 1020.0 | 766.2 | 793.6 | 879.8 | 1038.3 | 1141.0 | 1152.9 | 1225.3 | 1224.4 |
| 69° | 9967.4 | 6726.8 | 886.2 | 729.5 | 761.6 | 891.7 | 1109.8 | 1200.6 | 1155.6 | 1232.6 | 1221.6 |
| 70° | 9250.7 | 6091.7 | 814.7 | 704.8 | 746.9 | 912.8 | 1157.5 | 1199.6 | 1141.9 | 1207.9 | 1189.6 |
| 72.5° | 7124.5 | 4382.5 | 691.0 | 658.9 | 697.4 | 873.4 | 1171.2 | 1173.1 | 1109.8 | 1122.7 | 1091.5 |
| 75° | 4886.5 | 2769.5 | 603.0 | 596.6 | 622.3 | 787.2 | 1127.2 | 1120.8 | 1026.4 | 1008.1 | 982.4 |
| 77.5° | 2694.4 | 1406.8 | 512.3 | 537.0 | 554.5 | 697.4 | 1024.6 | 1015.4 | 937.5 | 899.0 | 889.9 |
| 80° | 1039.3 | 615.9 | 432.6 | 477.5 | 488.5 | 603.9 | 898.1 | 889.9 | 824.8 | 775.3 | 761.6 |
| 82.5° | 392.2 | 322.6 | 357.4 | 413.3 | 409.7 | 498.6 | 760.7 | 756.1 | 692.8 | 620.4 | 598.4 |
| 85° | 181.5 | 193.4 | 283.2 | 340.9 | 314.3 | 369.3 | 608.5 | 616.8 | 539.8 | 453.6 | 453.6 |
| 87.5° | 77.0 | 108.1 | 200.7 | 257.5 | 211.7 | 249.3 | 446.3 | 426.2 | 391.3 | 271.3 | 254.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)