

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P362439

Luminaire Tested: NVN-SA5B-727-U-AFL

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P362439
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-29)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA5B-727-U-AFL
Description: NAVION ROADWAY AND AREA LUMINAIRE
(5) 70 CRI, 2700K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE FRONTLINE OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24736 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G2


Input Watts (W): 210
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P362439
 CATALOG NUMBER: NVN-SA5B-727-U-AFL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 12.2 fc
 Type II - Short - N/A

REPORT NUMBER: P362439
CATALOG NUMBER: NVN-SA5B-727-U-AFL

Luminous Intensity Polar Plot



— Vertical Plane Through 56-Deg Lateral - - - Horizontal Cone Through 57-Deg Vertical

REPORT NUMBER: P362439
 CATALOG NUMBER: NVN-SA5B-727-U-AFL


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4264.0 | 0.0 | 4264.0 |
| | % Fixture | 17.2 | 0.0 | 17.2 |
| Street Side | Lumens | 20472.0 | 0.0 | 20472.0 |
| | % Fixture | 82.8 | 0.0 | 82.8 |
| Total | Lumens | 24736.0 | 0.0 | 24736.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 524.1 | 2.1 |
| 10°-20° | 1481.7 | 6.0 |
| 20°-30° | 2413.5 | 9.8 |
| 30°-40° | 3607.9 | 14.6 |
| 40°-50° | 5472.4 | 22.1 |
| 50°-60° | 6133.6 | 24.8 |
| 60°-70° | 3622.7 | 14.6 |
| 70°-80° | 1186.9 | 4.8 |
| 80°-90° | 293.3 | 1.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 24736.0 | 100.0 |
| 0°-180° | 24736.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P362439
 CATALOG NUMBER: NVN-SA5B-727-U-AFL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 3186.4 | 12.9 | | | |
| FM (30°-60°) | 13321.2 | 53.9 | | | |
| FH (60°-80°) | 3835.4 | 15.5 | | | G2/5000 |
| FVH (80°-90°) | 129.1 | 0.5 | | | G2/225 |
| BL (0°-30°) | 1232.9 | 5.0 | B3/2500 | | |
| BM (30°-60°) | 1892.6 | 7.7 | B2/2500 | | |
| BH (60°-80°) | 974.3 | 3.9 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 164.1 | 0.7 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2
 Type II Short





REPORT NUMBER: P362439
 CATALOG NUMBER: NVN-SA5B-727-U-AFL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 56° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|--------|
| 0° | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 |
| 2.5° | 6300.0 | 6357.8 | 6332.3 | 6243.9 | 6175.9 | 6079.8 | 5972.7 | 5940.4 | 5827.4 | 5700.7 | 5548.5 |
| 5° | 7297.2 | 7268.3 | 7226.6 | 7088.9 | 6943.5 | 6774.4 | 6505.7 | 6463.2 | 6211.6 | 5925.1 | 5622.5 |
| 7.5° | 7865.0 | 7862.5 | 7837.8 | 7757.1 | 7624.4 | 7403.4 | 7079.5 | 7029.4 | 6649.4 | 6188.6 | 5719.4 |
| 10° | 7782.6 | 7776.6 | 7817.4 | 7901.6 | 7941.5 | 7895.6 | 7622.7 | 7572.6 | 7105.9 | 6480.2 | 5831.6 |
| 12.5° | 7314.2 | 7317.6 | 7383.0 | 7559.8 | 7800.4 | 8089.4 | 8045.2 | 8020.6 | 7579.4 | 6810.1 | 5967.6 |
| 15° | 6949.5 | 6957.1 | 7009.0 | 7162.8 | 7446.8 | 7971.3 | 8302.0 | 8310.5 | 8037.6 | 7173.9 | 6126.6 |
| 17.5° | 6789.7 | 6805.8 | 6829.6 | 6937.6 | 7197.7 | 7735.8 | 8363.2 | 8409.1 | 8438.8 | 7551.3 | 6279.6 |
| 20° | 6840.7 | 6856.0 | 6862.8 | 6931.6 | 7145.0 | 7593.0 | 8320.7 | 8403.1 | 8746.6 | 7906.7 | 6432.6 |
| 22.5° | 7069.3 | 7078.7 | 7082.9 | 7100.8 | 7266.6 | 7633.8 | 8292.6 | 8379.3 | 8969.3 | 8225.5 | 6548.2 |
| 25° | 7448.5 | 7441.7 | 7414.5 | 7391.5 | 7502.9 | 7795.3 | 8357.2 | 8439.7 | 9150.3 | 8514.5 | 6623.9 |
| 27.5° | 7902.4 | 7893.9 | 7841.2 | 7778.3 | 7842.1 | 8046.9 | 8543.4 | 8608.8 | 9312.7 | 8784.8 | 6662.1 |
| 30° | 8447.3 | 8425.2 | 8325.8 | 8251.0 | 8275.6 | 8424.4 | 8850.3 | 8909.8 | 9563.5 | 9091.7 | 6699.5 |
| 32.5° | 9077.2 | 9053.4 | 8909.8 | 8785.7 | 8785.7 | 8909.8 | 9166.5 | 9215.8 | 9776.0 | 9438.5 | 6759.9 |
| 35° | 9866.1 | 9836.4 | 9649.3 | 9441.1 | 9382.4 | 9445.3 | 9597.5 | 9632.3 | 10158.6 | 9875.5 | 6869.6 |
| 37.5° | 10796.1 | 10756.2 | 10513.9 | 10235.1 | 10106.7 | 10103.3 | 10213.0 | 10284.4 | 10769.8 | 10449.3 | 7055.7 |
| 40° | 11728.7 | 11700.6 | 11488.9 | 11269.6 | 11018.0 | 10937.2 | 11106.4 | 11128.5 | 11568.8 | 11161.7 | 7293.8 |
| 42.5° | 12449.5 | 12444.4 | 12405.3 | 12434.2 | 12176.7 | 12013.4 | 12146.1 | 12163.9 | 12544.7 | 11932.7 | 7547.1 |
| 45° | 12830.4 | 12838.9 | 13028.4 | 13448.4 | 13543.6 | 13424.6 | 13490.0 | 13495.1 | 13660.1 | 12710.5 | 7779.2 |
| 47.5° | 12525.2 | 12569.4 | 13048.8 | 13988.2 | 14767.7 | 15163.0 | 15054.2 | 15117.1 | 14741.4 | 13378.7 | 7961.1 |
| 50° | 11335.9 | 11390.3 | 12206.4 | 13747.6 | 15339.0 | 16845.3 | 16788.4 | 16773.9 | 15613.6 | 13868.3 | 8059.7 |
| 52.5° | 9862.7 | 9905.2 | 10578.5 | 12497.1 | 14919.9 | 17775.3 | 18298.1 | 18223.3 | 16388.8 | 14234.7 | 8078.4 |
| 55° | 7619.3 | 7685.6 | 8330.9 | 10001.3 | 13224.8 | 17420.0 | 19408.4 | 19341.2 | 17095.3 | 14426.8 | 8056.3 |
| 57° | 5416.8 | 5486.5 | 6127.4 | 7632.9 | 11125.1 | 16189.9 | 19518.9 | 19590.3 | 17477.0 | 14459.1 | 8080.9 |
| 57.5° | 4833.6 | 4905.0 | 5540.0 | 7002.2 | 10470.5 | 15745.3 | 19423.7 | 19542.7 | 17545.8 | 14454.0 | 8094.5 |
| 60° | 2433.8 | 2461.0 | 2865.6 | 3908.7 | 6618.8 | 12729.2 | 18181.7 | 18488.6 | 17607.9 | 14204.1 | 8153.2 |
| 62.5° | 1513.2 | 1493.6 | 1480.9 | 1800.5 | 3220.1 | 8441.4 | 15618.7 | 16209.5 | 16420.3 | 13598.9 | 8011.2 |
| 65° | 1330.4 | 1293.8 | 1153.6 | 1128.1 | 1422.2 | 4100.0 | 11761.8 | 12497.1 | 13882.8 | 12645.1 | 7672.9 |
| 67.5° | 1249.6 | 1213.9 | 1055.8 | 960.6 | 961.4 | 1625.4 | 7302.3 | 8130.2 | 10814.8 | 11032.4 | 6874.7 |
| 70° | 1166.3 | 1134.0 | 986.1 | 873.9 | 818.6 | 900.2 | 3359.5 | 3987.8 | 7049.8 | 8671.7 | 5745.7 |
| 72.5° | 1059.2 | 1037.1 | 896.8 | 781.2 | 722.6 | 674.1 | 1286.2 | 1519.1 | 4081.3 | 5824.0 | 3990.3 |
| 75° | 947.0 | 926.6 | 806.7 | 696.2 | 624.8 | 530.5 | 724.3 | 780.4 | 2073.4 | 2979.6 | 1964.6 |
| 77.5° | 823.7 | 811.8 | 717.5 | 615.5 | 558.5 | 439.5 | 512.6 | 539.8 | 889.2 | 1277.7 | 985.3 |
| 80° | 655.4 | 678.4 | 627.4 | 548.3 | 495.6 | 351.9 | 363.0 | 380.8 | 517.7 | 624.0 | 559.4 |
| 82.5° | 426.7 | 466.7 | 491.4 | 445.4 | 408.0 | 277.1 | 261.0 | 268.6 | 337.5 | 380.8 | 243.1 |
| 85° | 177.7 | 199.8 | 323.0 | 291.6 | 271.2 | 202.3 | 175.1 | 178.5 | 209.1 | 216.8 | 99.5 |
| 87.5° | 79.1 | 84.2 | 142.0 | 133.5 | 114.8 | 69.7 | 74.8 | 81.6 | 111.4 | 105.4 | 38.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P362439
 CATALOG NUMBER: NVN-SA5B-727-U-AFL

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 | 5486.5 |
| 2.5° | 5491.6 | 5420.2 | 5297.7 | 5162.6 | 5052.1 | 4963.7 | 4874.4 | 4813.2 | 4741.8 | 4703.5 | 4684.0 |
| 5° | 5495.8 | 5355.6 | 5098.0 | 4833.6 | 4597.3 | 4381.4 | 4175.6 | 4017.5 | 3869.6 | 3789.7 | 3767.6 |
| 7.5° | 5513.7 | 5302.8 | 4886.3 | 4451.1 | 4031.1 | 3647.7 | 3351.9 | 3166.6 | 3033.1 | 2973.6 | 2956.6 |
| 10° | 5528.1 | 5240.8 | 4624.5 | 3980.1 | 3408.9 | 3020.4 | 2790.8 | 2687.1 | 2641.2 | 2633.6 | 2625.9 |
| 12.5° | 5562.1 | 5177.0 | 4349.0 | 3488.8 | 2925.2 | 2656.5 | 2576.6 | 2569.8 | 2582.6 | 2601.3 | 2601.3 |
| 15° | 5615.7 | 5114.1 | 4034.5 | 3067.1 | 2617.4 | 2523.1 | 2539.2 | 2576.6 | 2611.5 | 2640.4 | 2644.6 |
| 17.5° | 5654.8 | 5036.8 | 3696.2 | 2729.6 | 2453.4 | 2478.9 | 2536.7 | 2589.4 | 2625.1 | 2653.1 | 2655.7 |
| 20° | 5682.8 | 4916.9 | 3334.9 | 2472.1 | 2359.0 | 2438.1 | 2510.3 | 2557.1 | 2581.7 | 2609.8 | 2614.0 |
| 22.5° | 5668.4 | 4756.2 | 3014.4 | 2287.6 | 2282.5 | 2378.5 | 2447.4 | 2503.5 | 2484.8 | 2457.6 | 2475.5 |
| 25° | 5598.7 | 4535.2 | 2684.6 | 2149.9 | 2201.7 | 2298.6 | 2383.6 | 2346.2 | 2283.3 | 2271.4 | 2278.2 |
| 27.5° | 5474.6 | 4253.0 | 2379.4 | 2022.4 | 2108.2 | 2224.7 | 2219.6 | 2182.2 | 2160.1 | 2144.8 | 2154.1 |
| 30° | 5341.1 | 3947.0 | 2112.5 | 1911.0 | 2004.5 | 2100.6 | 2081.0 | 2080.2 | 2058.1 | 2033.4 | 2045.3 |
| 32.5° | 5209.3 | 3639.2 | 1900.8 | 1819.2 | 1926.3 | 1939.1 | 1981.6 | 1994.3 | 1951.0 | 1899.1 | 1895.7 |
| 35° | 5094.6 | 3348.5 | 1740.1 | 1735.9 | 1831.9 | 1833.6 | 1895.7 | 1877.8 | 1769.9 | 1716.3 | 1716.3 |
| 37.5° | 5008.7 | 3058.6 | 1617.7 | 1661.1 | 1707.8 | 1752.0 | 1783.5 | 1709.5 | 1691.7 | 1661.9 | 1661.1 |
| 40° | 4971.3 | 2803.6 | 1541.2 | 1604.1 | 1620.3 | 1676.4 | 1595.6 | 1624.5 | 1633.0 | 1617.7 | 1617.7 |
| 42.5° | 4932.2 | 2581.7 | 1474.9 | 1560.8 | 1558.2 | 1550.6 | 1509.8 | 1547.2 | 1581.2 | 1582.0 | 1579.5 |
| 45° | 4893.1 | 2390.4 | 1416.2 | 1468.1 | 1503.8 | 1421.3 | 1429.0 | 1469.0 | 1516.6 | 1533.6 | 1533.6 |
| 47.5° | 4849.8 | 2239.1 | 1362.7 | 1370.3 | 1425.6 | 1370.3 | 1364.4 | 1395.0 | 1451.1 | 1478.3 | 1484.3 |
| 50° | 4754.5 | 2103.1 | 1301.5 | 1284.5 | 1299.8 | 1318.5 | 1323.6 | 1338.0 | 1400.1 | 1443.4 | 1453.7 |
| 52.5° | 4622.8 | 1981.6 | 1223.3 | 1205.4 | 1205.4 | 1276.0 | 1299.8 | 1304.0 | 1356.7 | 1408.6 | 1418.8 |
| 55° | 4513.1 | 1904.2 | 1142.5 | 1139.1 | 1135.7 | 1230.9 | 1271.7 | 1278.5 | 1315.1 | 1355.9 | 1361.0 |
| 57° | 4520.8 | 1898.2 | 1080.5 | 1083.9 | 1083.0 | 1185.0 | 1245.4 | 1259.8 | 1278.5 | 1313.4 | 1319.3 |
| 57.5° | 4525.0 | 1902.5 | 1066.9 | 1068.6 | 1067.7 | 1172.3 | 1237.7 | 1253.9 | 1268.3 | 1304.9 | 1310.8 |
| 60° | 4588.8 | 1913.5 | 1011.6 | 992.9 | 997.2 | 1104.3 | 1194.4 | 1214.8 | 1224.1 | 1272.6 | 1280.2 |
| 62.5° | 4494.4 | 1864.2 | 967.4 | 922.3 | 922.3 | 1032.9 | 1134.0 | 1166.3 | 1180.8 | 1246.2 | 1259.0 |
| 65° | 4220.7 | 1725.7 | 915.5 | 842.4 | 850.9 | 961.4 | 1061.8 | 1114.5 | 1136.6 | 1218.2 | 1231.8 |
| 67.5° | 3798.2 | 1565.0 | 860.3 | 771.0 | 779.5 | 886.6 | 987.0 | 1043.9 | 1078.8 | 1187.6 | 1198.6 |
| 70° | 3248.2 | 1368.6 | 785.5 | 695.4 | 705.6 | 805.0 | 898.5 | 963.1 | 1015.0 | 1158.7 | 1162.1 |
| 72.5° | 2394.7 | 1122.1 | 680.9 | 612.1 | 623.1 | 709.8 | 809.3 | 884.1 | 953.8 | 1086.4 | 1084.7 |
| 75° | 1423.9 | 877.3 | 565.3 | 527.9 | 535.6 | 616.3 | 728.5 | 819.5 | 924.0 | 1058.4 | 1074.5 |
| 77.5° | 863.7 | 660.5 | 460.7 | 442.0 | 451.4 | 533.9 | 670.7 | 767.6 | 911.3 | 998.0 | 992.9 |
| 80° | 522.0 | 471.8 | 368.1 | 356.2 | 365.5 | 456.5 | 620.6 | 728.5 | 796.5 | 852.6 | 852.6 |
| 82.5° | 272.9 | 288.2 | 270.3 | 261.0 | 273.7 | 370.6 | 564.5 | 635.9 | 703.9 | 604.4 | 564.5 |
| 85° | 111.4 | 150.5 | 164.1 | 163.2 | 170.9 | 256.7 | 487.1 | 544.1 | 453.9 | 431.0 | 441.2 |
| 87.5° | 37.4 | 63.8 | 79.9 | 68.9 | 72.3 | 161.5 | 337.5 | 262.7 | 312.0 | 217.6 | 206.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)