

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P359754

Luminaire Tested: NVN-SA2C-730-U-T3R-HSS

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P359754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-11)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA2C-730-U-T3R-HSS
Description: NAVION ROADWAY AND AREA LUMINAIRE
(2) 70 CRI, 3000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
ROADWAY OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10086 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G2


Input Watts (W): 113
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P359754
 CATALOG NUMBER: NVN-SA2C-730-U-T3R-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5 fc
 Type III - Medium - N/A

REPORT NUMBER: P359754
CATALOG NUMBER: NVN-SA2C-730-U-T3R-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 55-Deg Lateral - - - Horizontal Cone Through 71-Deg Vertical

REPORT NUMBER: P359754
 CATALOG NUMBER: NVN-SA2C-730-U-T3R-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 798.5 | 0.0 | 798.5 |
| | % Fixture | 7.9 | 0.0 | 7.9 |
| Street Side | Lumens | 9287.5 | 0.0 | 9287.5 |
| | % Fixture | 92.1 | 0.0 | 92.1 |
| Total | Lumens | 10086.0 | 0.0 | 10086.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 165.8 | 1.6 |
| 10°-20° | 374.4 | 3.7 |
| 20°-30° | 601.7 | 6.0 |
| 30°-40° | 1022.3 | 10.1 |
| 40°-50° | 1586.8 | 15.7 |
| 50°-60° | 2133.3 | 21.2 |
| 60°-70° | 2609.8 | 25.9 |
| 70°-80° | 1525.9 | 15.1 |
| 80°-90° | 66.0 | 0.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 10086.0 | 100.0 |
| 0°-180° | 10086.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P359754
 CATALOG NUMBER: NVN-SA2C-730-U-T3R-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 782.5 | 7.8 | | | |
| FM (30°-60°) | 4411.3 | 43.7 | | | |
| FH (60°-80°) | 4028.7 | 39.9 | | | G2/5000 |
| FVH (80°-90°) | 64.9 | 0.6 | | | G1/100 |
| BL (0°-30°) | 359.4 | 3.6 | B1/500 | | |
| BM (30°-60°) | 331.1 | 3.3 | B1/1000 | | |
| BH (60°-80°) | 107.0 | 1.1 | B0/110 | | G0/110 |
| BVH (80°-90°) | 1.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type III Medium





REPORT NUMBER: P359754

CATALOG NUMBER: NVN-SA2C-730-U-T3R-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 54° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 |
| 2.5° | 1888.1 | 1890.3 | 1898.5 | 1902.1 | 1910.7 | 1925.2 | 1932.4 | 1932.9 | 1944.7 | 1949.2 | 1952.8 |
| 5° | 1754.5 | 1768.0 | 1781.6 | 1796.1 | 1822.4 | 1857.3 | 1891.7 | 1894.9 | 1932.9 | 1961.0 | 1975.9 |
| 7.5° | 1639.4 | 1651.7 | 1668.0 | 1691.1 | 1728.2 | 1783.0 | 1840.5 | 1847.3 | 1919.3 | 1983.2 | 2016.7 |
| 10° | 1521.2 | 1531.2 | 1554.7 | 1588.7 | 1639.9 | 1713.2 | 1790.7 | 1802.0 | 1907.1 | 2013.1 | 2071.9 |
| 12.5° | 1394.9 | 1400.8 | 1429.3 | 1478.2 | 1553.4 | 1646.7 | 1748.6 | 1763.5 | 1899.4 | 2047.5 | 2137.1 |
| 15° | 1298.9 | 1301.6 | 1328.8 | 1379.5 | 1465.5 | 1586.9 | 1716.0 | 1734.1 | 1901.2 | 2088.7 | 2208.2 |
| 17.5° | 1274.4 | 1275.8 | 1290.3 | 1325.1 | 1401.2 | 1533.5 | 1690.1 | 1712.3 | 1906.6 | 2129.0 | 2279.8 |
| 20° | 1373.6 | 1364.1 | 1349.1 | 1343.7 | 1376.3 | 1501.3 | 1674.8 | 1699.7 | 1913.9 | 2164.8 | 2344.1 |
| 22.5° | 1645.8 | 1617.7 | 1555.6 | 1472.8 | 1422.5 | 1503.6 | 1678.8 | 1703.7 | 1937.0 | 2208.7 | 2418.4 |
| 25° | 2049.7 | 2010.8 | 1905.3 | 1742.2 | 1585.5 | 1568.8 | 1712.8 | 1738.2 | 1981.8 | 2261.2 | 2489.5 |
| 27.5° | 2509.4 | 2470.9 | 2341.8 | 2109.1 | 1841.9 | 1697.8 | 1790.7 | 1814.2 | 2048.4 | 2307.9 | 2543.8 |
| 30° | 2949.6 | 2938.7 | 2786.6 | 2522.1 | 2164.3 | 1907.1 | 1891.2 | 1911.2 | 2097.7 | 2336.0 | 2586.9 |
| 32.5° | 3322.8 | 3305.6 | 3183.3 | 2926.1 | 2533.4 | 2158.4 | 2009.4 | 2015.3 | 2134.9 | 2372.2 | 2643.0 |
| 35° | 3668.8 | 3647.5 | 3540.2 | 3297.0 | 2912.0 | 2465.5 | 2191.5 | 2182.9 | 2215.9 | 2445.1 | 2724.5 |
| 37.5° | 3970.9 | 3990.3 | 3871.2 | 3639.8 | 3251.7 | 2784.8 | 2436.9 | 2411.1 | 2342.8 | 2563.8 | 2842.7 |
| 40° | 4223.6 | 4223.6 | 4161.5 | 3968.6 | 3618.5 | 3114.9 | 2714.6 | 2680.6 | 2533.4 | 2746.7 | 2992.6 |
| 42.5° | 4314.6 | 4334.1 | 4357.2 | 4248.0 | 3946.9 | 3458.2 | 3023.9 | 2988.6 | 2802.0 | 3006.2 | 3181.9 |
| 45° | 4320.0 | 4350.8 | 4469.0 | 4468.6 | 4243.5 | 3799.2 | 3372.6 | 3355.8 | 3146.2 | 3339.5 | 3416.5 |
| 47.5° | 4243.5 | 4282.0 | 4476.7 | 4587.2 | 4478.5 | 4116.7 | 3753.9 | 3733.1 | 3550.6 | 3748.0 | 3662.0 |
| 50° | 4125.3 | 4167.9 | 4394.3 | 4633.9 | 4638.4 | 4392.9 | 4155.6 | 4124.4 | 3995.8 | 4215.0 | 3915.6 |
| 52.5° | 3913.8 | 3996.2 | 4320.5 | 4644.7 | 4743.5 | 4631.6 | 4537.9 | 4524.3 | 4493.9 | 4664.7 | 4117.6 |
| 55° | 3461.4 | 3552.8 | 4135.3 | 4648.4 | 4840.8 | 4843.1 | 4896.1 | 4899.7 | 4960.9 | 5084.9 | 4267.9 |
| 57.5° | 3247.6 | 3299.2 | 3811.9 | 4665.6 | 4985.3 | 5083.1 | 5261.1 | 5289.2 | 5383.8 | 5483.9 | 4439.6 |
| 60° | 3113.1 | 3174.2 | 3652.5 | 4642.0 | 5212.2 | 5397.9 | 5599.4 | 5608.9 | 5710.4 | 5895.6 | 4671.9 |
| 62.5° | 3005.8 | 3066.0 | 3551.9 | 4551.4 | 5467.2 | 5776.5 | 5930.0 | 5930.9 | 6007.0 | 6386.1 | 4935.9 |
| 65° | 2740.8 | 2791.6 | 3348.6 | 4449.5 | 5635.6 | 6151.0 | 6314.1 | 6308.2 | 6370.2 | 6903.3 | 5242.5 |
| 67.5° | 2357.7 | 2396.6 | 2933.3 | 4063.2 | 5572.2 | 6491.6 | 6893.7 | 6874.3 | 6799.1 | 7350.2 | 5363.0 |
| 70° | 1822.8 | 1836.9 | 2312.0 | 3386.2 | 4978.1 | 6622.5 | 7454.0 | 7444.0 | 7062.2 | 7270.1 | 4921.5 |
| 71° | 1506.7 | 1552.9 | 2037.5 | 2988.6 | 4580.0 | 6501.6 | 7508.3 | 7514.2 | 6996.1 | 7051.8 | 4617.6 |
| 72.5° | 875.0 | 914.4 | 1476.8 | 2295.2 | 3888.4 | 5997.0 | 7226.6 | 7269.2 | 6687.2 | 6414.1 | 3944.1 |
| 75° | 187.5 | 200.6 | 547.5 | 1110.9 | 2139.0 | 4203.2 | 5704.0 | 5855.7 | 5450.4 | 4363.5 | 2377.2 |
| 77.5° | 130.4 | 140.8 | 234.6 | 504.1 | 706.9 | 2076.9 | 3543.3 | 3714.5 | 3256.2 | 1639.9 | 760.8 |
| 80° | 103.3 | 115.0 | 183.0 | 249.1 | 191.1 | 669.8 | 1659.8 | 1764.4 | 1086.0 | 365.9 | 128.2 |
| 82.5° | 57.5 | 68.4 | 142.7 | 134.5 | 73.4 | 127.3 | 464.7 | 525.3 | 217.4 | 73.8 | 30.3 |
| 85° | 16.8 | 20.4 | 91.9 | 97.8 | 31.2 | 24.5 | 79.3 | 98.3 | 41.2 | 19.5 | 13.6 |
| 87.5° | 0.0 | 0.0 | 44.4 | 37.6 | 9.1 | 3.6 | 7.2 | 8.2 | 8.2 | 8.2 | 9.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P359754

CATALOG NUMBER: NVN-SA2C-730-U-T3R-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 | 1945.1 |
| 2.5° | 1952.8 | 1956.0 | 1944.7 | 1929.7 | 1913.9 | 1894.4 | 1874.0 | 1858.2 | 1857.7 | 1850.0 | 1842.3 |
| 5° | 1976.8 | 1975.0 | 1943.8 | 1896.2 | 1840.1 | 1781.6 | 1725.9 | 1663.0 | 1642.1 | 1616.3 | 1607.7 |
| 7.5° | 2021.2 | 2008.5 | 1942.4 | 1838.2 | 1715.1 | 1592.8 | 1466.4 | 1339.2 | 1284.8 | 1235.9 | 1227.3 |
| 10° | 2076.9 | 2052.9 | 1933.8 | 1751.3 | 1525.3 | 1299.8 | 1109.1 | 936.1 | 860.0 | 801.6 | 798.9 |
| 12.5° | 2134.9 | 2098.2 | 1909.8 | 1620.0 | 1276.7 | 959.7 | 740.0 | 569.7 | 506.3 | 465.6 | 469.2 |
| 15° | 2195.6 | 2140.8 | 1858.2 | 1442.9 | 993.6 | 651.2 | 454.7 | 354.6 | 329.2 | 318.8 | 321.5 |
| 17.5° | 2257.6 | 2170.2 | 1786.2 | 1229.6 | 714.2 | 420.3 | 314.8 | 286.7 | 286.7 | 288.9 | 289.8 |
| 20° | 2311.5 | 2186.1 | 1680.2 | 990.4 | 484.1 | 306.1 | 275.4 | 271.3 | 273.5 | 277.2 | 277.6 |
| 22.5° | 2364.9 | 2187.0 | 1542.1 | 748.2 | 338.8 | 268.1 | 262.2 | 260.4 | 261.8 | 265.8 | 266.3 |
| 25° | 2408.4 | 2176.1 | 1369.1 | 532.1 | 270.4 | 252.7 | 250.0 | 249.1 | 250.0 | 255.0 | 255.0 |
| 27.5° | 2426.1 | 2136.7 | 1158.0 | 374.1 | 242.3 | 235.5 | 234.6 | 235.5 | 236.9 | 240.5 | 240.9 |
| 30° | 2427.9 | 2067.9 | 928.0 | 270.8 | 219.6 | 212.4 | 214.2 | 217.4 | 216.0 | 215.1 | 216.0 |
| 32.5° | 2432.4 | 1988.1 | 703.8 | 222.8 | 200.6 | 189.3 | 187.0 | 187.0 | 181.6 | 178.4 | 176.6 |
| 35° | 2447.4 | 1894.4 | 510.4 | 200.2 | 181.2 | 168.0 | 159.4 | 149.5 | 139.0 | 133.6 | 132.2 |
| 37.5° | 2470.9 | 1796.1 | 365.5 | 185.2 | 163.9 | 149.0 | 132.7 | 115.0 | 100.1 | 96.0 | 96.0 |
| 40° | 2513.9 | 1694.7 | 270.4 | 173.5 | 150.4 | 131.8 | 107.3 | 84.2 | 70.6 | 68.4 | 68.4 |
| 42.5° | 2581.9 | 1587.8 | 215.6 | 163.0 | 138.6 | 114.1 | 82.0 | 61.1 | 51.2 | 49.8 | 49.4 |
| 45° | 2652.5 | 1470.0 | 188.4 | 153.1 | 125.9 | 93.7 | 60.7 | 45.3 | 39.4 | 38.0 | 38.0 |
| 47.5° | 2723.2 | 1344.6 | 175.3 | 143.6 | 113.7 | 72.9 | 45.3 | 35.8 | 33.1 | 33.1 | 33.5 |
| 50° | 2783.0 | 1213.7 | 165.8 | 133.1 | 97.8 | 55.3 | 35.8 | 30.3 | 29.4 | 31.2 | 31.7 |
| 52.5° | 2797.9 | 1085.1 | 154.0 | 120.0 | 78.3 | 42.1 | 29.4 | 26.7 | 26.7 | 26.7 | 26.7 |
| 55° | 2788.8 | 985.5 | 138.6 | 103.7 | 58.0 | 33.5 | 25.4 | 23.5 | 23.1 | 23.1 | 23.1 |
| 57.5° | 2819.6 | 926.6 | 111.0 | 80.6 | 41.7 | 27.2 | 22.2 | 20.8 | 19.9 | 19.5 | 19.5 |
| 60° | 2881.7 | 888.1 | 79.3 | 58.0 | 31.2 | 22.6 | 19.0 | 17.7 | 16.3 | 15.4 | 15.4 |
| 62.5° | 2964.1 | 854.6 | 58.9 | 43.0 | 24.0 | 18.1 | 15.9 | 14.5 | 12.7 | 11.8 | 11.8 |
| 65° | 3027.5 | 794.8 | 44.8 | 32.2 | 18.1 | 14.5 | 12.2 | 11.8 | 9.1 | 8.2 | 7.7 |
| 67.5° | 2930.6 | 663.5 | 36.2 | 23.5 | 13.6 | 11.3 | 9.5 | 9.1 | 5.4 | 4.5 | 4.5 |
| 70° | 2513.5 | 461.9 | 29.0 | 17.2 | 10.0 | 9.1 | 7.7 | 5.9 | 4.1 | 3.6 | 3.6 |
| 71° | 2279.3 | 385.9 | 26.3 | 14.5 | 8.6 | 8.6 | 7.2 | 5.0 | 3.6 | 3.2 | 3.2 |
| 72.5° | 1893.5 | 274.0 | 22.2 | 11.3 | 7.7 | 9.1 | 7.7 | 4.5 | 3.6 | 3.2 | 2.7 |
| 75° | 1099.1 | 114.6 | 15.4 | 7.7 | 5.9 | 10.9 | 10.0 | 4.1 | 2.7 | 2.3 | 2.3 |
| 77.5° | 330.6 | 42.1 | 8.6 | 5.0 | 4.5 | 9.5 | 11.3 | 3.6 | 1.4 | 0.5 | 0.5 |
| 80° | 60.2 | 18.1 | 5.4 | 3.2 | 3.2 | 5.9 | 8.6 | 1.8 | 0.0 | 0.0 | 0.0 |
| 82.5° | 21.3 | 9.1 | 3.2 | 1.8 | 1.4 | 2.7 | 4.1 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 12.2 | 6.3 | 1.8 | 0.9 | 0.0 | 0.5 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 8.2 | 1.8 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 2993 | CRI (Ra): | 71.8 | R9: | -38.3 |
| CIE u': | 0.2508 | R1: | 67.5 | R10: | 62.5 |
| CIE v': | 0.5215 | R2: | 82.9 | R11: | 63.7 |
| Duv: | 0.0000 | R3: | 94.7 | R12: | 57.8 |
| CIE x: | 0.4374 | R4: | 67.7 | R13: | 70.4 |
| CIE y: | 0.4043 | R5: | 67.9 | R14: | 97.3 |
| CIE z: | 0.1583 | R6: | 77.6 | | |
| Peak Wavelength (nm): | 593 | R7: | 76.0 | | |
| Dominant Wavelength (nm): | 582 | R8: | 40.5 | | |
| Purity: | 53 | | | | |
| Rf: | 75.7 | | | | |
| Rg: | 93.9 | | | | |



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength




#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength




Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)