

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P359168

Luminaire Tested: NVN-SA4A-730-U-T3R

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P359168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA4A-730-U-T3R
Description: NAVION ROADWAY AND AREA LUMINAIRE
(4) 70 CRI, 3000K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
ROADWAY OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17693 lumens
Efficiency: N/A
Efficacy: 137.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 129
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P359168
 CATALOG NUMBER: NVN-SA4A-730-U-T3R

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5 fc
 Type IV - Medium - N/A

REPORT NUMBER: P359168
CATALOG NUMBER: NVN-SA4A-730-U-T3R

Luminous Intensity Polar Plot



— Vertical Plane Through 55-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P359168
 CATALOG NUMBER: NVN-SA4A-730-U-T3R


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3288.5 | 0.0 | 3288.5 |
| | % Fixture | 18.6 | 0.0 | 18.6 |
| Street Side | Lumens | 14404.4 | 0.0 | 14404.4 |
| | % Fixture | 81.4 | 0.0 | 81.4 |
| Total | Lumens | 17693.0 | 0.0 | 17693.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 282.4 | 1.6 |
| 10°-20° | 751.8 | 4.2 |
| 20°-30° | 1239.5 | 7.0 |
| 30°-40° | 1833.6 | 10.4 |
| 40°-50° | 2559.3 | 14.5 |
| 50°-60° | 3332.3 | 18.8 |
| 60°-70° | 4095.3 | 23.1 |
| 70°-80° | 3210.2 | 18.1 |
| 80°-90° | 388.5 | 2.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 17693.0 | 100.0 |
| 0°-180° | 17693.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P359168
 CATALOG NUMBER: NVN-SA4A-730-U-T3R

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1368.9 | 7.7 | | | |
| FM (30°-60°) | 6260.1 | 35.4 | | | |
| FH (60°-80°) | 6475.0 | 36.6 | | | G3/7500 |
| FVH (80°-90°) | 300.4 | 1.7 | | | G3/500 |
| BL (0°-30°) | 904.8 | 5.1 | B2/1000 | | |
| BM (30°-60°) | 1465.1 | 8.3 | B2/2500 | | |
| BH (60°-80°) | 830.5 | 4.7 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 88.1 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G3
 Type IV Medium





REPORT NUMBER: P359168

CATALOG NUMBER: NVN-SA4A-730-U-T3R

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 54° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|--------|
| 0° | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 |
| 2.5° | 3019.1 | 3011.9 | 3020.9 | 3033.4 | 3047.2 | 3065.7 | 3076.4 | 3081.2 | 3099.7 | 3106.9 | 3122.5 |
| 5° | 2879.2 | 2875.6 | 2890.6 | 2912.1 | 2942.6 | 2985.6 | 3020.3 | 3026.8 | 3075.8 | 3110.5 | 3142.2 |
| 7.5° | 2777.6 | 2777.6 | 2795.0 | 2820.7 | 2854.7 | 2912.7 | 2961.7 | 2970.7 | 3053.7 | 3128.4 | 3187.0 |
| 10° | 2697.0 | 2700.0 | 2720.3 | 2750.8 | 2790.8 | 2852.3 | 2917.5 | 2927.6 | 3047.8 | 3170.3 | 3263.5 |
| 12.5° | 2643.2 | 2650.4 | 2668.9 | 2696.4 | 2746.0 | 2820.7 | 2903.1 | 2916.9 | 3060.3 | 3230.0 | 3355.5 |
| 15° | 2677.2 | 2689.2 | 2691.0 | 2702.3 | 2729.8 | 2811.1 | 2911.5 | 2925.8 | 3087.2 | 3291.0 | 3460.1 |
| 17.5° | 2826.6 | 2830.8 | 2812.3 | 2788.4 | 2775.3 | 2827.2 | 2936.6 | 2951.5 | 3119.5 | 3351.3 | 3560.5 |
| 20° | 3053.7 | 3051.3 | 3011.3 | 2946.8 | 2879.8 | 2888.2 | 2977.8 | 2993.4 | 3163.1 | 3404.5 | 3660.9 |
| 22.5° | 3340.6 | 3332.2 | 3270.7 | 3151.7 | 3037.6 | 2989.8 | 3050.1 | 3063.3 | 3228.8 | 3480.4 | 3768.5 |
| 25° | 3688.4 | 3669.9 | 3588.6 | 3429.0 | 3261.1 | 3138.0 | 3158.9 | 3171.5 | 3324.4 | 3565.3 | 3867.1 |
| 27.5° | 4055.3 | 4036.8 | 3933.4 | 3740.4 | 3516.9 | 3325.0 | 3308.9 | 3319.7 | 3433.2 | 3628.0 | 3940.0 |
| 30° | 4439.0 | 4419.2 | 4324.8 | 4108.5 | 3788.2 | 3518.7 | 3448.7 | 3452.9 | 3509.7 | 3662.1 | 3999.7 |
| 32.5° | 4824.4 | 4805.9 | 4700.1 | 4449.1 | 4082.8 | 3726.6 | 3549.7 | 3544.4 | 3555.7 | 3697.3 | 4067.3 |
| 35° | 5215.3 | 5222.4 | 5098.7 | 4820.8 | 4409.1 | 3957.9 | 3669.3 | 3657.9 | 3632.8 | 3769.7 | 4162.9 |
| 37.5° | 5633.6 | 5628.8 | 5468.6 | 5178.2 | 4750.3 | 4208.9 | 3840.8 | 3839.0 | 3752.3 | 3906.5 | 4312.9 |
| 40° | 5913.2 | 5916.2 | 5818.8 | 5543.9 | 5095.1 | 4486.8 | 4060.7 | 4056.5 | 3943.0 | 4111.5 | 4509.5 |
| 42.5° | 6022.6 | 6042.3 | 6067.4 | 5892.9 | 5456.1 | 4808.9 | 4323.0 | 4317.1 | 4208.9 | 4405.5 | 4740.8 |
| 45° | 6030.4 | 6069.8 | 6225.2 | 6203.1 | 5821.8 | 5177.6 | 4658.3 | 4641.6 | 4563.9 | 4796.3 | 5016.8 |
| 47.5° | 5963.4 | 6004.1 | 6262.2 | 6387.7 | 6148.7 | 5566.6 | 5050.3 | 5037.2 | 4970.2 | 5285.2 | 5315.6 |
| 50° | 5817.0 | 5855.9 | 6185.8 | 6478.0 | 6417.6 | 5940.7 | 5502.1 | 5467.4 | 5431.6 | 5849.9 | 5657.5 |
| 52.5° | 5542.7 | 5617.4 | 6083.6 | 6499.5 | 6578.4 | 6273.0 | 5977.2 | 5954.5 | 5974.2 | 6445.7 | 5999.9 |
| 55° | 4893.1 | 4976.8 | 5820.0 | 6481.6 | 6697.3 | 6552.1 | 6452.3 | 6451.1 | 6553.3 | 7070.8 | 6367.4 |
| 57.5° | 4529.2 | 4588.4 | 5283.4 | 6451.1 | 6838.3 | 6829.4 | 6922.6 | 6933.9 | 7132.9 | 7751.5 | 6752.3 |
| 60° | 4323.6 | 4385.8 | 5011.5 | 6338.1 | 7057.1 | 7187.9 | 7402.5 | 7425.2 | 7722.2 | 8505.0 | 7215.4 |
| 62.5° | 4136.6 | 4204.7 | 4842.9 | 6108.1 | 7314.6 | 7700.7 | 7977.4 | 7997.7 | 8346.1 | 9279.5 | 7663.0 |
| 65° | 3816.9 | 3894.0 | 4596.1 | 5956.9 | 7548.9 | 8369.4 | 8708.2 | 8722.0 | 9062.6 | 10091.1 | 8005.4 |
| 67.5° | 3365.1 | 3435.6 | 4130.6 | 5622.8 | 7722.2 | 9181.5 | 9679.9 | 9687.7 | 9773.1 | 10664.2 | 8180.5 |
| 70° | 2837.4 | 2864.3 | 3467.3 | 4933.2 | 7517.2 | 9941.1 | 10744.8 | 10746.6 | 10420.9 | 11031.1 | 8151.9 |
| 72.5° | 1993.6 | 2056.9 | 2517.1 | 3734.4 | 6460.1 | 9848.4 | 11297.6 | 11317.9 | 10722.1 | 10845.8 | 7500.5 |
| 75° | 1222.7 | 1289.6 | 1578.9 | 2263.1 | 4098.3 | 7745.5 | 10438.3 | 10579.3 | 10157.4 | 9670.4 | 6127.2 |
| 77.5° | 817.5 | 842.6 | 1030.3 | 1319.5 | 1856.7 | 4456.3 | 8025.2 | 8290.5 | 8438.1 | 7052.3 | 3918.5 |
| 80° | 456.0 | 503.8 | 683.1 | 819.9 | 825.9 | 1770.7 | 4811.9 | 4874.0 | 4694.7 | 2808.1 | 1208.9 |
| 82.5° | 241.4 | 267.7 | 456.0 | 481.7 | 450.6 | 592.8 | 1793.4 | 1795.2 | 1500.0 | 753.0 | 359.2 |
| 85° | 187.0 | 209.2 | 312.5 | 294.0 | 230.1 | 262.9 | 591.6 | 623.9 | 510.3 | 308.4 | 117.1 |
| 87.5° | 93.2 | 115.9 | 212.1 | 186.5 | 90.2 | 75.3 | 211.6 | 225.9 | 201.4 | 120.7 | 42.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P359168

CATALOG NUMBER: NVN-SA4A-730-U-T3R

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 | 3120.7 |
| 2.5° | 3128.4 | 3133.8 | 3140.4 | 3133.2 | 3130.8 | 3121.3 | 3105.1 | 3101.5 | 3093.2 | 3093.8 | 3098.6 |
| 5° | 3155.9 | 3164.9 | 3161.3 | 3133.8 | 3100.9 | 3054.9 | 3007.1 | 2966.5 | 2939.6 | 2937.8 | 2936.0 |
| 7.5° | 3208.5 | 3214.5 | 3186.4 | 3108.1 | 3016.1 | 2909.7 | 2809.3 | 2721.5 | 2668.3 | 2655.1 | 2652.1 |
| 10° | 3291.0 | 3289.8 | 3212.7 | 3054.9 | 2871.5 | 2681.4 | 2520.1 | 2398.2 | 2327.1 | 2306.1 | 2300.8 |
| 12.5° | 3383.0 | 3369.3 | 3221.7 | 2958.1 | 2667.1 | 2403.5 | 2199.2 | 2063.5 | 1989.4 | 1965.5 | 1959.5 |
| 15° | 3478.0 | 3444.0 | 3199.5 | 2813.5 | 2416.1 | 2104.1 | 1889.6 | 1764.1 | 1724.1 | 1710.9 | 1708.5 |
| 17.5° | 3566.5 | 3500.7 | 3136.2 | 2617.5 | 2129.8 | 1805.9 | 1638.6 | 1588.4 | 1598.0 | 1615.3 | 1615.9 |
| 20° | 3653.1 | 3539.0 | 3034.6 | 2370.1 | 1828.1 | 1560.3 | 1503.6 | 1540.6 | 1586.0 | 1621.3 | 1626.1 |
| 22.5° | 3738.6 | 3565.9 | 2903.7 | 2084.4 | 1557.9 | 1422.3 | 1462.3 | 1529.9 | 1581.8 | 1620.1 | 1626.7 |
| 25° | 3810.3 | 3572.4 | 2723.3 | 1779.7 | 1370.3 | 1370.3 | 1442.6 | 1506.5 | 1557.9 | 1595.6 | 1602.2 |
| 27.5° | 3836.6 | 3528.2 | 2468.7 | 1497.6 | 1275.9 | 1346.4 | 1415.1 | 1468.3 | 1511.9 | 1552.0 | 1559.1 |
| 30° | 3846.7 | 3446.4 | 2174.7 | 1271.1 | 1237.0 | 1320.7 | 1378.1 | 1423.5 | 1464.7 | 1502.4 | 1508.9 |
| 32.5° | 3848.5 | 3347.8 | 1862.7 | 1142.6 | 1210.1 | 1293.8 | 1332.0 | 1372.1 | 1416.3 | 1431.3 | 1433.6 |
| 35° | 3859.9 | 3231.2 | 1534.0 | 1076.9 | 1185.0 | 1268.7 | 1299.2 | 1327.9 | 1256.2 | 1261.5 | 1266.3 |
| 37.5° | 3892.8 | 3115.9 | 1259.1 | 1039.8 | 1168.9 | 1255.6 | 1292.0 | 1188.0 | 1131.9 | 1118.7 | 1116.9 |
| 40° | 3954.3 | 2992.8 | 1055.4 | 1009.9 | 1162.9 | 1262.1 | 1246.0 | 1109.1 | 1012.3 | 940.0 | 929.3 |
| 42.5° | 4039.8 | 2860.1 | 925.1 | 990.2 | 1167.1 | 1293.8 | 1182.1 | 1033.2 | 872.5 | 825.9 | 819.9 |
| 45° | 4136.0 | 2720.9 | 854.6 | 976.5 | 1181.5 | 1318.3 | 1168.9 | 932.3 | 807.4 | 772.1 | 769.1 |
| 47.5° | 4229.2 | 2550.6 | 818.1 | 970.5 | 1201.2 | 1298.6 | 1113.3 | 901.2 | 776.3 | 757.8 | 759.5 |
| 50° | 4336.2 | 2397.0 | 796.0 | 963.9 | 1218.5 | 1286.0 | 1050.6 | 885.0 | 764.3 | 787.0 | 810.9 |
| 52.5° | 4426.4 | 2238.0 | 776.3 | 950.8 | 1225.1 | 1263.9 | 1034.4 | 888.0 | 764.3 | 808.0 | 830.7 |
| 55° | 4533.4 | 2117.9 | 753.6 | 923.3 | 1212.5 | 1201.2 | 1023.1 | 906.0 | 773.3 | 745.8 | 748.2 |
| 57.5° | 4671.4 | 2078.5 | 728.5 | 880.3 | 1170.7 | 1109.7 | 1017.7 | 923.3 | 767.9 | 750.6 | 756.6 |
| 60° | 4862.7 | 2120.3 | 718.3 | 824.1 | 1105.6 | 1038.0 | 1018.3 | 914.3 | 730.3 | 700.4 | 701.0 |
| 62.5° | 5044.9 | 2166.9 | 717.7 | 788.8 | 1025.5 | 974.1 | 1004.6 | 885.0 | 711.1 | 693.8 | 700.4 |
| 65° | 5104.7 | 2119.7 | 689.0 | 749.4 | 935.2 | 897.6 | 979.5 | 854.0 | 696.8 | 670.5 | 669.3 |
| 67.5° | 5024.6 | 1973.3 | 631.1 | 685.4 | 831.9 | 808.6 | 946.6 | 816.9 | 674.1 | 652.6 | 649.0 |
| 70° | 4786.8 | 1646.4 | 559.4 | 601.2 | 714.1 | 708.2 | 894.6 | 773.9 | 643.6 | 625.1 | 609.6 |
| 72.5° | 4146.7 | 1173.1 | 471.5 | 500.2 | 581.5 | 600.6 | 822.9 | 717.7 | 600.6 | 560.5 | 536.6 |
| 75° | 3405.7 | 868.3 | 387.2 | 393.2 | 441.6 | 493.6 | 724.3 | 652.0 | 549.8 | 481.7 | 463.1 |
| 77.5° | 2085.6 | 531.3 | 308.4 | 310.8 | 316.7 | 393.8 | 596.4 | 578.5 | 485.3 | 401.6 | 388.4 |
| 80° | 675.3 | 289.8 | 222.9 | 234.3 | 216.3 | 288.6 | 461.3 | 492.4 | 416.5 | 335.9 | 321.5 |
| 82.5° | 257.0 | 169.1 | 150.6 | 158.4 | 150.0 | 193.6 | 336.4 | 394.4 | 341.2 | 276.1 | 224.7 |
| 85° | 124.3 | 95.6 | 89.0 | 99.8 | 92.6 | 99.2 | 215.1 | 290.4 | 258.8 | 179.9 | 167.3 |
| 87.5° | 44.2 | 42.4 | 34.1 | 46.0 | 39.4 | 35.3 | 65.7 | 146.4 | 170.9 | 123.7 | 110.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 2993 | CRI (Ra): | 71.8 | R9: | -38.3 |
| CIE u': | 0.2508 | R1: | 67.5 | R10: | 62.5 |
| CIE v': | 0.5215 | R2: | 82.9 | R11: | 63.7 |
| Duv: | 0.0000 | R3: | 94.7 | R12: | 57.8 |
| CIE x: | 0.4374 | R4: | 67.7 | R13: | 70.4 |
| CIE y: | 0.4043 | R5: | 67.9 | R14: | 97.3 |
| CIE z: | 0.1583 | R6: | 77.6 | | |
| Peak Wavelength (nm): | 593 | R7: | 76.0 | | |
| Dominant Wavelength (nm): | 582 | R8: | 40.5 | | |
| Purity: | 53 | | | | |
| Rf: | 75.7 | | | | |
| Rg: | 93.9 | | | | |



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)