

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P359970

Luminaire Tested: NVN-SA2C-740-U-T4W-HSS

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P359970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-19)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA2C-740-U-T4W-HSS
Description: NAVION ROADWAY AND AREA LUMINAIRE
(2) 70 CRI, 4000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10439 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 113
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P359970
 CATALOG NUMBER: NVN-SA2C-740-U-T4W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 3.8 fc
 Type IV - Short - N/A

REPORT NUMBER: P359970
CATALOG NUMBER: NVN-SA2C-740-U-T4W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 46-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P359970
 CATALOG NUMBER: NVN-SA2C-740-U-T4W-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1071.3 | 0.0 | 1071.3 |
| | % Fixture | 10.3 | 0.0 | 10.3 |
| Street Side | Lumens | 9367.7 | 0.0 | 9367.7 |
| | % Fixture | 89.7 | 0.0 | 89.7 |
| Total | Lumens | 10439.0 | 0.0 | 10439.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 104.1 | 1.0 |
| 10°-20° | 315.8 | 3.0 |
| 20°-30° | 496.7 | 4.8 |
| 30°-40° | 712.3 | 6.8 |
| 40°-50° | 1231.1 | 11.8 |
| 50°-60° | 2432.1 | 23.3 |
| 60°-70° | 3399.1 | 32.6 |
| 70°-80° | 1642.2 | 15.7 |
| 80°-90° | 105.6 | 1.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 10439.0 | 100.0 |
| 0°-180° | 10439.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P359970
 CATALOG NUMBER: NVN-SA2C-740-U-T4W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 634.3 | 6.1 | | | |
| FM (30°-60°) | 3838.6 | 36.8 | | | |
| FH (60°-80°) | 4790.1 | 45.9 | | | G2/5000 |
| FVH (80°-90°) | 104.7 | 1.0 | | | G2/225 |
| BL (0°-30°) | 282.4 | 2.7 | B1/500 | | |
| BM (30°-60°) | 536.9 | 5.1 | B1/1000 | | |
| BH (60°-80°) | 251.2 | 2.4 | B1/500 | | G1/500 |
| BVH (80°-90°) | 0.9 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type IV Short





REPORT NUMBER: P359970

CATALOG NUMBER: NVN-SA2C-740-U-T4W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 46° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 |
| 2.5° | 1161.9 | 1160.5 | 1153.6 | 1150.7 | 1134.0 | 1124.3 | 1120.3 | 1108.1 | 1090.5 | 1072.9 | 1053.3 |
| 5° | 1294.1 | 1293.6 | 1280.9 | 1268.6 | 1237.3 | 1208.0 | 1202.6 | 1174.2 | 1134.5 | 1097.3 | 1060.1 |
| 7.5° | 1429.2 | 1422.8 | 1410.1 | 1386.6 | 1341.1 | 1294.1 | 1289.7 | 1249.6 | 1193.3 | 1139.4 | 1086.1 |
| 10° | 1543.7 | 1539.8 | 1523.2 | 1487.4 | 1434.1 | 1380.7 | 1375.3 | 1325.9 | 1262.3 | 1196.2 | 1128.2 |
| 12.5° | 1632.8 | 1629.9 | 1607.8 | 1563.3 | 1506.5 | 1451.2 | 1443.9 | 1399.8 | 1331.8 | 1257.9 | 1177.6 |
| 15° | 1687.1 | 1685.7 | 1658.7 | 1611.3 | 1555.5 | 1507.5 | 1501.1 | 1462.5 | 1399.3 | 1322.0 | 1231.4 |
| 17.5° | 1699.9 | 1700.3 | 1672.4 | 1624.5 | 1578.5 | 1544.2 | 1539.3 | 1509.9 | 1457.1 | 1380.2 | 1285.3 |
| 20° | 1671.5 | 1677.3 | 1652.4 | 1610.8 | 1582.4 | 1564.3 | 1560.4 | 1542.7 | 1498.2 | 1425.8 | 1328.4 |
| 22.5° | 1631.3 | 1634.3 | 1617.1 | 1589.2 | 1577.5 | 1580.9 | 1579.0 | 1569.2 | 1531.5 | 1464.9 | 1370.9 |
| 25° | 1606.9 | 1606.9 | 1596.6 | 1573.1 | 1580.9 | 1602.0 | 1602.5 | 1600.5 | 1570.6 | 1512.9 | 1422.8 |
| 27.5° | 1605.9 | 1602.9 | 1591.2 | 1573.6 | 1595.1 | 1627.4 | 1629.4 | 1642.6 | 1624.0 | 1571.1 | 1487.4 |
| 30° | 1645.0 | 1641.6 | 1616.6 | 1593.6 | 1621.0 | 1655.8 | 1660.7 | 1689.6 | 1680.3 | 1634.3 | 1559.4 |
| 32.5° | 1736.6 | 1724.3 | 1669.0 | 1631.3 | 1651.9 | 1693.5 | 1699.9 | 1745.9 | 1760.5 | 1712.1 | 1628.9 |
| 35° | 1861.9 | 1823.2 | 1743.4 | 1702.8 | 1704.7 | 1748.3 | 1754.2 | 1821.7 | 1865.3 | 1783.5 | 1682.7 |
| 37.5° | 2034.6 | 2015.5 | 1885.8 | 1777.2 | 1786.0 | 1852.1 | 1869.2 | 1942.6 | 1930.4 | 1822.7 | 1743.9 |
| 40° | 2413.5 | 2383.6 | 2245.6 | 1985.7 | 1863.8 | 1936.3 | 1941.6 | 1980.8 | 1981.8 | 1911.3 | 1871.2 |
| 42.5° | 2929.3 | 2917.1 | 2771.7 | 2364.0 | 2017.0 | 1992.5 | 2002.3 | 2068.4 | 2142.3 | 2098.3 | 2096.3 |
| 45° | 3500.5 | 3494.2 | 3340.0 | 2866.2 | 2326.8 | 2177.1 | 2189.3 | 2277.9 | 2419.3 | 2429.1 | 2491.3 |
| 47.5° | 3960.1 | 3957.2 | 3868.6 | 3426.6 | 2801.1 | 2489.8 | 2493.7 | 2587.7 | 2836.3 | 2959.2 | 3058.6 |
| 50° | 4379.1 | 4393.3 | 4323.3 | 4033.0 | 3447.2 | 2979.8 | 2970.5 | 3033.1 | 3432.5 | 3633.7 | 3757.0 |
| 52.5° | 4961.5 | 4981.6 | 4785.3 | 4598.8 | 4125.1 | 3587.6 | 3580.3 | 3645.9 | 4149.0 | 4299.8 | 4321.8 |
| 55° | 5475.9 | 5441.7 | 5286.5 | 5232.7 | 4951.7 | 4338.5 | 4336.5 | 4394.3 | 4842.1 | 4906.2 | 4946.8 |
| 57.5° | 5703.0 | 5689.8 | 5764.7 | 5888.1 | 5817.6 | 5225.8 | 5221.4 | 5177.4 | 5462.2 | 5469.1 | 5593.9 |
| 60° | 5846.4 | 5862.6 | 6092.1 | 6472.5 | 6648.2 | 6180.7 | 6152.4 | 5883.6 | 6054.5 | 6039.3 | 6172.9 |
| 62.5° | 5738.8 | 5770.6 | 6183.7 | 6817.5 | 7269.8 | 7014.3 | 6974.1 | 6530.7 | 6560.6 | 6508.2 | 6632.5 |
| 65° | 5167.1 | 5216.5 | 5893.4 | 6752.4 | 7578.1 | 7665.7 | 7625.1 | 7101.9 | 6962.4 | 6876.2 | 6807.2 |
| 67.5° | 4195.5 | 4224.9 | 4931.7 | 6186.1 | 7439.1 | 8054.3 | 8046.0 | 7602.6 | 7265.8 | 6814.1 | 6278.6 |
| 69° | 3467.2 | 3496.1 | 4176.5 | 5590.0 | 7133.2 | 8137.6 | 8153.7 | 7763.1 | 7208.1 | 6436.2 | 5563.1 |
| 70° | 2936.7 | 2967.5 | 3601.4 | 5079.0 | 6778.4 | 8098.9 | 8127.8 | 7748.0 | 7042.7 | 5998.7 | 4935.1 |
| 72.5° | 1540.3 | 1566.7 | 2217.2 | 3499.1 | 5525.9 | 7436.7 | 7524.3 | 7093.1 | 5969.8 | 4356.6 | 2918.1 |
| 75° | 484.1 | 499.2 | 865.8 | 1829.1 | 3783.4 | 5782.3 | 5802.4 | 5564.0 | 4239.1 | 2396.3 | 1215.3 |
| 77.5° | 184.5 | 180.1 | 288.3 | 674.0 | 1912.8 | 3641.0 | 3763.8 | 3477.0 | 2224.5 | 847.2 | 280.5 |
| 80° | 99.4 | 99.8 | 149.8 | 279.0 | 818.4 | 1871.2 | 1974.9 | 1685.2 | 790.5 | 264.3 | 64.6 |
| 82.5° | 43.1 | 45.0 | 84.2 | 147.8 | 375.9 | 690.1 | 742.0 | 617.7 | 302.0 | 177.7 | 24.0 |
| 85° | 9.3 | 10.3 | 40.6 | 80.3 | 153.2 | 193.8 | 203.1 | 200.2 | 192.4 | 138.0 | 9.3 |
| 87.5° | 0.0 | 0.0 | 18.1 | 28.9 | 38.7 | 44.1 | 38.7 | 50.4 | 106.2 | 93.0 | 4.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P359970
 CATALOG NUMBER: NVN-SA2C-740-U-T4W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 | 1045.9 |
| 2.5° | 1046.9 | 1038.1 | 1022.9 | 1006.3 | 994.6 | 982.3 | 972.5 | 968.1 | 963.2 | 959.8 | 964.2 |
| 5° | 1045.0 | 1027.8 | 998.5 | 970.1 | 949.5 | 932.9 | 919.2 | 913.8 | 908.4 | 904.5 | 904.0 |
| 7.5° | 1062.1 | 1038.1 | 993.1 | 951.5 | 919.7 | 897.2 | 878.6 | 870.7 | 864.4 | 861.4 | 859.0 |
| 10° | 1094.9 | 1064.1 | 1003.9 | 949.5 | 908.4 | 870.2 | 830.1 | 799.3 | 779.2 | 769.9 | 766.5 |
| 12.5° | 1137.5 | 1098.8 | 1024.4 | 959.8 | 900.1 | 826.7 | 741.5 | 668.1 | 620.6 | 605.0 | 595.7 |
| 15° | 1187.4 | 1139.4 | 1051.3 | 973.0 | 869.7 | 735.6 | 591.3 | 495.3 | 451.3 | 442.5 | 432.7 |
| 17.5° | 1235.4 | 1182.5 | 1083.6 | 975.5 | 803.2 | 587.8 | 433.2 | 368.1 | 350.9 | 356.8 | 358.3 |
| 20° | 1277.5 | 1225.1 | 1115.5 | 953.9 | 682.3 | 441.0 | 335.3 | 319.1 | 325.5 | 336.7 | 338.7 |
| 22.5° | 1320.0 | 1266.2 | 1144.8 | 897.2 | 527.6 | 334.8 | 302.0 | 305.9 | 312.3 | 323.5 | 325.5 |
| 25° | 1371.9 | 1316.1 | 1172.2 | 792.9 | 396.0 | 284.9 | 286.8 | 292.7 | 299.1 | 309.3 | 310.3 |
| 27.5° | 1431.6 | 1379.3 | 1190.3 | 657.3 | 293.7 | 261.9 | 268.2 | 277.0 | 283.4 | 293.2 | 295.1 |
| 30° | 1510.9 | 1462.5 | 1196.2 | 516.9 | 246.2 | 241.3 | 244.2 | 255.0 | 264.3 | 273.1 | 274.6 |
| 32.5° | 1585.3 | 1544.7 | 1176.6 | 390.1 | 228.1 | 222.2 | 222.2 | 228.6 | 239.3 | 247.7 | 249.6 |
| 35° | 1653.8 | 1627.4 | 1114.0 | 285.3 | 214.4 | 204.6 | 199.7 | 199.7 | 206.5 | 213.4 | 215.4 |
| 37.5° | 1744.4 | 1743.4 | 1012.7 | 227.6 | 201.2 | 189.9 | 179.6 | 171.8 | 169.3 | 170.8 | 171.8 |
| 40° | 1899.5 | 1901.0 | 880.5 | 204.1 | 189.9 | 174.7 | 159.1 | 144.9 | 131.7 | 127.3 | 126.8 |
| 42.5° | 2141.8 | 2119.8 | 742.0 | 192.8 | 180.1 | 159.1 | 135.6 | 116.5 | 95.9 | 89.6 | 89.1 |
| 45° | 2526.5 | 2395.8 | 595.2 | 182.6 | 169.8 | 141.5 | 112.1 | 86.1 | 69.5 | 64.6 | 64.6 |
| 47.5° | 3086.9 | 2758.5 | 461.1 | 171.3 | 156.1 | 121.4 | 84.7 | 62.2 | 50.9 | 48.5 | 48.9 |
| 50° | 3666.4 | 3113.9 | 353.4 | 157.1 | 139.5 | 100.3 | 62.6 | 45.0 | 38.7 | 38.7 | 39.2 |
| 52.5° | 4180.4 | 3374.2 | 275.6 | 141.9 | 118.9 | 78.8 | 47.5 | 35.2 | 32.3 | 31.8 | 32.3 |
| 55° | 4661.5 | 3542.1 | 211.0 | 124.3 | 94.5 | 58.7 | 36.2 | 28.9 | 26.9 | 25.9 | 25.5 |
| 57.5° | 5125.5 | 3625.3 | 158.1 | 100.3 | 68.5 | 42.6 | 28.9 | 24.5 | 22.5 | 21.0 | 20.6 |
| 60° | 5434.3 | 3557.8 | 108.7 | 73.9 | 47.5 | 30.8 | 24.0 | 21.0 | 18.6 | 17.1 | 16.6 |
| 62.5° | 5608.6 | 3373.3 | 70.0 | 53.3 | 33.8 | 23.0 | 19.1 | 17.6 | 14.2 | 12.7 | 12.7 |
| 65° | 5538.1 | 3068.8 | 48.9 | 38.2 | 24.5 | 17.1 | 14.2 | 14.2 | 10.3 | 8.3 | 7.8 |
| 67.5° | 4907.7 | 2592.6 | 37.2 | 28.4 | 17.6 | 12.7 | 10.8 | 12.2 | 6.4 | 3.9 | 3.9 |
| 69° | 4222.5 | 2148.7 | 31.8 | 23.5 | 14.7 | 10.3 | 9.3 | 11.3 | 4.4 | 2.9 | 2.4 |
| 70° | 3669.9 | 1853.5 | 28.9 | 20.6 | 12.2 | 8.8 | 8.3 | 10.8 | 4.4 | 2.4 | 2.0 |
| 72.5° | 2195.7 | 1033.7 | 22.0 | 14.7 | 7.8 | 6.9 | 6.9 | 12.2 | 4.4 | 2.4 | 2.0 |
| 75° | 887.4 | 364.1 | 16.2 | 10.3 | 5.9 | 5.9 | 8.3 | 15.7 | 3.9 | 2.0 | 1.5 |
| 77.5° | 201.2 | 79.8 | 9.3 | 6.4 | 3.9 | 5.9 | 9.8 | 12.2 | 2.4 | 1.0 | 0.0 |
| 80° | 48.9 | 19.6 | 5.9 | 3.9 | 2.4 | 4.4 | 7.3 | 6.9 | 0.5 | 0.0 | 0.0 |
| 82.5° | 16.2 | 6.9 | 2.4 | 2.0 | 0.5 | 1.5 | 3.4 | 2.0 | 0.0 | 0.0 | 0.0 |
| 85° | 6.9 | 3.9 | 1.0 | 0.5 | 0.0 | 0.0 | 0.5 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 4.4 | 1.5 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021


Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions

Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2 M/P: 0.55

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)