

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P360117

Luminaire Tested: NVN-SA5C-740-U-SL4-HSS

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P360117  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: NVN-SA5C-740-U-SL4-HSS  
Description: NAVION ROADWAY AND AREA LUMINAIRE  
(5) 70 CRI, 4000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV  
SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 29108 lumens  
Efficiency: N/A  
Efficacy: 104.3 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G5


Input Watts (W): 279  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P360117  
 CATALOG NUMBER: NVN-SA5C-740-U-SL4-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9 fc  
 Type IV - Short - N/A

REPORT NUMBER: P360117  
CATALOG NUMBER: NVN-SA5C-740-U-SL4-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 38-Deg Lateral    - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P360117  
 CATALOG NUMBER: NVN-SA5C-740-U-SL4-HSS

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 2449.5   | 0.0    | 2449.5  |
|                    | % Fixture | 8.4      | 0.0    | 8.4     |
| <b>Street Side</b> | Lumens    | 26658.4  | 0.0    | 26658.4 |
|                    | % Fixture | 91.6     | 0.0    | 91.6    |
| <b>Total</b>       | Lumens    | 29108.0  | 0.0    | 29108.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 456.2   | 1.6       |
| 10°-20°   | 1115.4  | 3.8       |
| 20°-30°   | 1774.1  | 6.1       |
| 30°-40°   | 2667.1  | 9.2       |
| 40°-50°   | 4068.9  | 14.0      |
| 50°-60°   | 5750.7  | 19.8      |
| 60°-70°   | 7213.3  | 24.8      |
| 70°-80°   | 5393.5  | 18.5      |
| 80°-90°   | 668.8   | 2.3       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 29108.0 | 100.0     |
| 0°-180°   | 29108.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P360117  
 CATALOG NUMBER: NVN-SA5C-740-U-SL4-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |        |
|----------------|---------|-----------|-------------------------|------|--------|
|                |         |           | B                       | U    | G      |
| FL (0°-30°)    | 2473.5  | 8.5       |                         |      |        |
| FM (30°-60°)   | 11242.8 | 38.6      |                         |      |        |
| FH (60°-80°)   | 12279.6 | 42.2      |                         |      | G5     |
| FVH (80°-90°)  | 662.5   | 2.3       |                         |      | G4/750 |
| BL (0°-30°)    | 872.2   | 3.0       | B2/1000                 |      |        |
| BM (30°-60°)   | 1243.9  | 4.3       | B2/2500                 |      |        |
| BH (60°-80°)   | 327.2   | 1.1       | B1/500                  |      | G1/500 |
| BVH (80°-90°)  | 6.2     | 0.0       |                         |      | G0/10  |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |        |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |        |

**BUG Rating: B2-U0-G5**

Type IV Short





REPORT NUMBER: P360117

CATALOG NUMBER: NVN-SA5C-740-U-SL4-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 38°     | 45°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 5352.9  | 5352.9  | 5352.9  | 5352.9  | 5352.9  | 5352.9  | 5352.9  | 5352.9  | 5352.9  | 5352.9  | 5352.9  |
| 2.5°  | 5681.7  | 5682.9  | 5669.6  | 5647.8  | 5620.0  | 5605.5  | 5581.3  | 5542.7  | 5501.6  | 5427.8  | 5348.0  |
| 5°    | 5797.7  | 5797.7  | 5780.8  | 5751.8  | 5707.1  | 5693.8  | 5647.8  | 5586.2  | 5501.6  | 5381.9  | 5247.7  |
| 7.5°  | 5785.6  | 5788.1  | 5765.1  | 5734.9  | 5690.1  | 5678.1  | 5622.4  | 5553.5  | 5448.4  | 5303.3  | 5131.6  |
| 10°   | 5722.8  | 5728.8  | 5710.7  | 5696.2  | 5655.1  | 5641.8  | 5589.8  | 5520.9  | 5415.7  | 5261.0  | 5063.9  |
| 12.5° | 5658.7  | 5664.8  | 5670.8  | 5684.1  | 5658.7  | 5653.9  | 5612.8  | 5554.7  | 5454.4  | 5293.6  | 5071.2  |
| 15°   | 5617.6  | 5629.7  | 5673.2  | 5725.2  | 5731.2  | 5726.4  | 5699.8  | 5645.4  | 5543.9  | 5377.0  | 5123.2  |
| 17.5° | 5617.6  | 5636.9  | 5727.6  | 5826.7  | 5861.8  | 5865.4  | 5842.5  | 5766.3  | 5645.4  | 5466.5  | 5171.5  |
| 20°   | 5664.8  | 5691.3  | 5832.8  | 5973.0  | 6031.0  | 6031.0  | 5986.3  | 5879.9  | 5738.5  | 5547.5  | 5204.2  |
| 22.5° | 5785.6  | 5820.7  | 5998.4  | 6160.4  | 6222.0  | 6208.7  | 6148.3  | 5993.6  | 5835.2  | 5639.4  | 5245.3  |
| 25°   | 6023.8  | 6050.4  | 6235.3  | 6398.5  | 6436.0  | 6405.8  | 6329.6  | 6131.4  | 5958.5  | 5763.9  | 5320.2  |
| 27.5° | 6330.8  | 6334.5  | 6525.5  | 6663.3  | 6640.3  | 6619.8  | 6524.3  | 6304.2  | 6136.2  | 5941.6  | 5449.6  |
| 30°   | 6668.1  | 6668.1  | 6836.1  | 6941.3  | 6871.2  | 6854.3  | 6758.8  | 6513.4  | 6363.5  | 6183.4  | 5633.3  |
| 32.5° | 6994.5  | 7009.0  | 7145.6  | 7212.1  | 7133.5  | 7116.6  | 7023.5  | 6778.1  | 6665.7  | 6552.1  | 5919.8  |
| 35°   | 7310.0  | 7320.9  | 7450.3  | 7486.5  | 7411.6  | 7416.4  | 7349.9  | 7142.0  | 7099.7  | 7085.2  | 6351.4  |
| 37.5° | 7615.9  | 7618.3  | 7750.0  | 7773.0  | 7735.5  | 7776.6  | 7782.7  | 7598.9  | 7677.5  | 7794.8  | 6959.5  |
| 40°   | 7895.1  | 7897.5  | 8028.1  | 8087.3  | 8151.4  | 8204.6  | 8251.7  | 8153.8  | 8413.7  | 8685.7  | 7683.6  |
| 42.5° | 8118.8  | 8144.1  | 8309.8  | 8422.2  | 8591.4  | 8693.0  | 8821.1  | 8816.3  | 9290.1  | 9698.7  | 8558.8  |
| 45°   | 8315.8  | 8359.3  | 8590.2  | 8787.3  | 9077.4  | 9239.4  | 9440.0  | 9597.2  | 10276.6 | 10826.6 | 9444.9  |
| 47.5° | 8575.7  | 8616.8  | 8880.3  | 9203.1  | 9589.9  | 9802.7  | 10135.1 | 10474.8 | 11360.9 | 11933.9 | 10310.4 |
| 50°   | 8942.0  | 8923.9  | 9183.8  | 9646.8  | 10143.6 | 10422.9 | 10896.7 | 11405.7 | 12436.8 | 12898.6 | 10819.4 |
| 52.5° | 9332.5  | 9325.2  | 9517.4  | 10129.1 | 10796.4 | 11122.8 | 11749.0 | 12367.9 | 13465.6 | 13563.5 | 11052.7 |
| 55°   | 9816.0  | 9764.0  | 9926.0  | 10679.1 | 11571.3 | 11921.9 | 12659.3 | 13320.5 | 14285.2 | 13938.2 | 11169.9 |
| 57.5° | 10322.5 | 10236.7 | 10391.4 | 11292.0 | 12445.3 | 12859.9 | 13667.5 | 14248.9 | 14830.4 | 14194.5 | 11168.7 |
| 60°   | 10846.0 | 10744.4 | 10928.2 | 12058.5 | 13530.9 | 14010.8 | 14760.3 | 14876.3 | 15339.3 | 14323.9 | 11086.5 |
| 62.5° | 11283.6 | 11223.1 | 11496.3 | 12878.1 | 14743.3 | 15214.8 | 15585.9 | 15446.9 | 15768.5 | 14424.2 | 10894.3 |
| 65°   | 11746.6 | 11750.2 | 12191.4 | 13834.3 | 16032.0 | 16349.9 | 16381.4 | 16186.7 | 16127.5 | 14403.7 | 10243.9 |
| 67.5° | 12372.8 | 12430.8 | 13167.0 | 15132.6 | 17285.6 | 17531.0 | 17528.6 | 16988.2 | 16389.8 | 13586.5 | 8801.8  |
| 70°   | 13035.2 | 13171.8 | 14291.2 | 16618.3 | 18654.0 | 18903.1 | 18774.9 | 17498.4 | 15432.4 | 10986.2 | 6229.3  |
| 72.5° | 12924.0 | 13160.9 | 14916.2 | 17555.2 | 19636.8 | 19826.6 | 18993.7 | 16244.8 | 12197.5 | 6385.2  | 2652.3  |
| 75°   | 9970.7  | 10245.2 | 13677.1 | 16626.8 | 18605.7 | 18435.2 | 16319.7 | 12641.1 | 6665.7  | 1781.9  | 597.2   |
| 77.5° | 5267.0  | 5413.3  | 9035.1  | 12666.5 | 14507.6 | 14151.0 | 11496.3 | 7012.6  | 2032.1  | 441.2   | 268.4   |
| 80°   | 2758.6  | 2792.5  | 3937.3  | 7186.7  | 8954.1  | 8956.5  | 6813.2  | 3080.2  | 837.7   | 226.1   | 180.1   |
| 82.5° | 1477.2  | 1506.2  | 2080.5  | 3320.8  | 4691.6  | 4252.8  | 2608.7  | 1694.8  | 487.2   | 128.1   | 172.9   |
| 85°   | 355.4   | 361.5   | 1179.9  | 1517.1  | 1844.7  | 1317.7  | 774.9   | 1422.8  | 131.8   | 74.9    | 140.2   |
| 87.5° | 136.6   | 139.0   | 437.6   | 656.4   | 470.2   | 304.6   | 362.7   | 530.7   | 16.9    | 29.0    | 21.8    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P360117  
 CATALOG NUMBER: NVN-SA5C-740-U-SL4-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 5352.9 | 5352.9 | 5352.9 | 5352.9 | 5352.9 | 5352.9 | 5352.9 | 5352.9 | 5352.9 | 5352.9 | 5352.9 |
| 2.5°  | 5299.7 | 5268.2 | 5190.9 | 5093.0 | 5005.9 | 4943.1 | 4848.8 | 4787.1 | 4746.0 | 4744.8 | 4729.1 |
| 5°    | 5165.5 | 5101.4 | 4934.6 | 4736.3 | 4556.2 | 4394.2 | 4203.2 | 4052.1 | 3939.7 | 3921.6 | 3882.9 |
| 7.5°  | 5021.6 | 4916.5 | 4660.2 | 4350.7 | 4048.5 | 3741.4 | 3384.8 | 3163.6 | 2973.8 | 2883.1 | 2873.5 |
| 10°   | 4933.4 | 4785.9 | 4422.0 | 3974.8 | 3500.9 | 3001.6 | 2535.0 | 2212.2 | 1978.9 | 1912.4 | 1862.9 |
| 12.5° | 4915.3 | 4720.6 | 4238.3 | 3621.8 | 2944.8 | 2284.8 | 1768.6 | 1425.3 | 1239.1 | 1179.9 | 1164.1 |
| 15°   | 4933.4 | 4690.4 | 4083.6 | 3272.4 | 2381.5 | 1621.1 | 1187.1 | 987.6  | 917.5  | 900.6  | 899.4  |
| 17.5° | 4944.3 | 4654.1 | 3908.3 | 2884.4 | 1835.1 | 1158.1 | 909.1  | 851.0  | 840.2  | 839.0  | 841.4  |
| 20°   | 4943.1 | 4598.5 | 3699.1 | 2451.6 | 1364.8 | 910.3  | 822.0  | 809.9  | 807.5  | 808.7  | 807.5  |
| 22.5° | 4934.6 | 4533.3 | 3469.4 | 2005.5 | 1031.2 | 813.6  | 784.6  | 777.3  | 776.1  | 776.1  | 776.1  |
| 25°   | 4950.3 | 4481.3 | 3216.8 | 1578.8 | 849.8  | 768.8  | 750.7  | 744.7  | 743.5  | 743.5  | 741.0  |
| 27.5° | 5007.1 | 4452.3 | 2940.0 | 1214.9 | 767.6  | 728.9  | 714.4  | 713.2  | 709.6  | 708.4  | 710.8  |
| 30°   | 5099.0 | 4452.3 | 2636.5 | 945.3  | 718.1  | 687.8  | 677.0  | 674.5  | 673.3  | 672.1  | 673.3  |
| 32.5° | 5261.0 | 4486.1 | 2305.3 | 785.8  | 670.9  | 641.9  | 634.7  | 638.3  | 634.7  | 634.7  | 634.7  |
| 35°   | 5553.5 | 4587.7 | 1958.4 | 685.4  | 621.4  | 597.2  | 589.9  | 594.8  | 592.3  | 592.3  | 591.1  |
| 37.5° | 5980.3 | 4776.2 | 1609.0 | 625.0  | 577.8  | 552.5  | 542.8  | 550.0  | 547.6  | 547.6  | 546.4  |
| 40°   | 6500.1 | 5050.6 | 1276.6 | 579.0  | 535.5  | 508.9  | 500.5  | 504.1  | 498.1  | 498.1  | 500.5  |
| 42.5° | 7142.0 | 5398.8 | 986.4  | 534.3  | 493.2  | 467.8  | 463.0  | 459.4  | 448.5  | 442.4  | 443.7  |
| 45°   | 7855.2 | 5761.5 | 768.8  | 490.8  | 453.3  | 432.8  | 425.5  | 415.9  | 397.7  | 385.6  | 386.8  |
| 47.5° | 8492.3 | 6040.7 | 625.0  | 448.5  | 417.1  | 401.3  | 390.5  | 372.3  | 345.7  | 331.2  | 332.4  |
| 50°   | 8827.2 | 6083.0 | 531.9  | 406.2  | 383.2  | 367.5  | 351.8  | 324.0  | 292.5  | 276.8  | 275.6  |
| 52.5° | 8913.0 | 5884.8 | 463.0  | 367.5  | 349.4  | 331.2  | 310.7  | 273.2  | 238.1  | 221.2  | 218.8  |
| 55°   | 8944.4 | 5582.6 | 401.3  | 331.2  | 313.1  | 292.5  | 266.0  | 223.6  | 191.0  | 174.1  | 172.9  |
| 57.5° | 8840.4 | 5131.6 | 353.0  | 298.6  | 276.8  | 251.4  | 218.8  | 178.9  | 147.5  | 134.2  | 134.2  |
| 60°   | 8609.6 | 4521.2 | 315.5  | 263.5  | 239.4  | 210.3  | 176.5  | 139.0  | 110.0  | 99.1   | 99.1   |
| 62.5° | 8149.0 | 3730.6 | 280.5  | 227.3  | 204.3  | 174.1  | 142.6  | 105.2  | 77.4   | 71.3   | 72.5   |
| 65°   | 7279.8 | 2830.0 | 245.4  | 194.6  | 174.1  | 143.9  | 111.2  | 74.9   | 52.0   | 52.0   | 54.4   |
| 67.5° | 5936.7 | 1965.6 | 209.1  | 165.6  | 149.9  | 117.3  | 84.6   | 52.0   | 36.3   | 41.1   | 45.9   |
| 70°   | 3930.0 | 1102.5 | 178.9  | 136.6  | 128.1  | 93.1   | 62.9   | 35.1   | 29.0   | 38.7   | 47.1   |
| 72.5° | 1483.3 | 429.1  | 149.9  | 110.0  | 111.2  | 71.3   | 44.7   | 26.6   | 26.6   | 42.3   | 55.6   |
| 75°   | 413.4  | 210.3  | 107.6  | 81.0   | 87.0   | 52.0   | 32.6   | 23.0   | 25.4   | 48.4   | 65.3   |
| 77.5° | 243.0  | 154.7  | 70.1   | 47.1   | 59.2   | 36.3   | 21.8   | 18.1   | 21.8   | 41.1   | 62.9   |
| 80°   | 195.8  | 82.2   | 41.1   | 24.2   | 32.6   | 20.6   | 14.5   | 10.9   | 6.0    | 15.7   | 32.6   |
| 82.5° | 195.8  | 49.6   | 19.3   | 16.9   | 16.9   | 10.9   | 7.3    | 4.8    | 1.2    | 0.0    | 8.5    |
| 85°   | 131.8  | 20.6   | 12.1   | 10.9   | 8.5    | 3.6    | 2.4    | 1.2    | 0.0    | 0.0    | 0.0    |
| 87.5° | 21.8   | 8.5    | 4.8    | 2.4    | 1.2    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

**Spectral Parameters**

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 | R9:  | -29.7 |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R10: | 46.2  |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R11: | 68.8  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R12: | 45.6  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R13: | 69.5  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R14: | 90.7  |
| CIE z:                    | 0.2385  | R6:       | 68.3 |      |       |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



**Test Conditions**

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3905K  
 CIE x = 0.3841  
 CIE y = 0.3774  
 Duv = -0.0008

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 2.7           | 620    | 97577         | 25.4          | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 4.8           | 625    | 90158         | 19.9          | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 8.0           | 630    | 82240         | 14.9          | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 13.3          | 635    | 74361         | 11.2          | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 20.2          | 640    | 66994         | 8.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 28.5          | 645    | 60405         | 5.8           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 37.4          | 650    | 53806         | 3.9           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 44.9          | 655    | 47610         | 2.7           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 52.6          | 660    | 42018         | 1.8           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 58.4          | 665    | 36742         | 1.2           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.0           | 540    | 96845         | 63.1          | 670    | 32105         | 0.7           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.0           | 545    | 100829        | 67.1          | 675    | 27946         | 0.5           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 0.1           | 550    | 105648        | 71.8          | 680    | 24146         | 0.3           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 0.2           | 555    | 110017        | 75.1          | 685    | 21191         | 0.2           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 0.5           | 560    | 114586        | 77.9          | 690    | 18544         | 0.1           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 1.2           | 565    | 118987        | 79.1          | 695    | 16058         | 0.1           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 2.1           | 570    | 122326        | 79.5          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 2.9           | 575    | 125968        | 78.4          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 2.7           | 580    | 127613        | 75.8          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 2.0           | 585    | 129466        | 71.9          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 1.5           | 590    | 128813        | 66.6          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 1.3           | 595    | 126387        | 59.9          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 1.0           | 600    | 123477        | 53.2          | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 1.1           | 605    | 118718        | 46.0          | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 1.2           | 610    | 112091        | 38.5          | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 1.7           | 615    | 105039        | 31.7          | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 10425.8 S/P: 1.47**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 29.3          | 620    | 97577         | 1.2           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 43.0          | 625    | 90158         | 0.8           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 60.8          | 630    | 82240         | 0.5           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 81.1          | 635    | 74361         | 0.3           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 99.6          | 640    | 66994         | 0.2           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 113.9         | 645    | 60405         | 0.1           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 122.6         | 650    | 53806         | 0.1           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 125.0         | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 123.1         | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.1           | 535    | 94097         | 117.3         | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 107.0         | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.9           | 545    | 100829        | 96.7          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 3.0           | 550    | 105648        | 86.4          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 9.3           | 555    | 110017        | 75.2          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 23.0          | 560    | 114586        | 64.0          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 45.7          | 565    | 118987        | 53.4          | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 75.5          | 570    | 122326        | 43.2          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 93.8          | 575    | 125968        | 34.3          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 79.3          | 580    | 127613        | 26.3          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 51.3          | 585    | 129466        | 19.8          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 35.6          | 590    | 128813        | 14.3          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 26.0          | 595    | 126387        | 10.1          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 19.3          | 600    | 123477        | 7.0           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 16.8          | 605    | 118718        | 4.7           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 17.7          | 610    | 112091        | 3.0           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 21.4          | 615    | 105039        | 1.9           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 3927.2 M/P: 0.55**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 15.8          | 620    | 97577         | 0.1           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 22.0          | 625    | 90158         | 0.0           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 29.2          | 630    | 82240         | 0.0           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 36.6          | 635    | 74361         | 0.0           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 42.2          | 640    | 66994         | 0.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 44.9          | 645    | 60405         | 0.0           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 44.9          | 650    | 53806         | 0.0           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 42.4          | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 38.6          | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 33.9          | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 28.3          | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.6           | 545    | 100829        | 23.4          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 2.1           | 550    | 105648        | 19.0          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 5.9           | 555    | 110017        | 14.8          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 14.3          | 560    | 114586        | 11.3          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 27.3          | 565    | 118987        | 8.4           | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 45.1          | 570    | 122326        | 6.0           | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 55.3          | 575    | 125968        | 4.2           | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 47.2          | 580    | 127613        | 2.9           | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 30.8          | 585    | 129466        | 1.9           | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 21.7          | 590    | 128813        | 1.3           | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 16.1          | 595    | 126387        | 0.8           | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 12.0          | 600    | 123477        | 0.5           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 10.3          | 605    | 118718        | 0.3           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 10.5          | 610    | 112091        | 0.2           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 12.1          | 615    | 105039        | 0.1           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

**Summary**

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$



**Color Vector Graphics**





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)