

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P364249

Luminaire Tested: NVN-SA3D-827-U-AFL-HSS

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P364249
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA3D-827-U-AFL-HSS
Description: NAVION ROADWAY AND AREA LUMINAIRE
(3) 80 CRI, 2700K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE
FRONTLINE OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14569 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 191
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P364249
 CATALOG NUMBER: NVN-SA3D-827-U-AFL-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 12.5 fc
 Type II - Short - N/A

REPORT NUMBER: P364249
CATALOG NUMBER: NVN-SA3D-827-U-AFL-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 54-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P364249
 CATALOG NUMBER: NVN-SA3D-827-U-AFL-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 726.9 | 0.0 | 726.9 |
| | % Fixture | 5.0 | 0.0 | 5.0 |
| Street Side | Lumens | 13842.1 | 0.0 | 13842.1 |
| | % Fixture | 95.0 | 0.0 | 95.0 |
| Total | Lumens | 14569.0 | 0.0 | 14569.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 300.5 | 2.1 |
| 10°-20° | 824.1 | 5.7 |
| 20°-30° | 1406.9 | 9.7 |
| 30°-40° | 2257.9 | 15.5 |
| 40°-50° | 3608.1 | 24.8 |
| 50°-60° | 3866.2 | 26.5 |
| 60°-70° | 1985.0 | 13.6 |
| 70°-80° | 300.7 | 2.1 |
| 80°-90° | 19.6 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 14569.0 | 100.0 |
| 0°-180° | 14569.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P364249
 CATALOG NUMBER: NVN-SA3D-827-U-AFL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2177.8 | 14.9 | | | |
| FM (30°-60°) | 9426.8 | 64.7 | | | |
| FH (60°-80°) | 2218.7 | 15.2 | | | G2/5000 |
| FVH (80°-90°) | 18.8 | 0.1 | | | G1/100 |
| BL (0°-30°) | 353.7 | 2.4 | B1/500 | | |
| BM (30°-60°) | 305.5 | 2.1 | B1/1000 | | |
| BH (60°-80°) | 67.0 | 0.5 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.8 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type II Short





REPORT NUMBER: P364249
 CATALOG NUMBER: NVN-SA3D-827-U-AFL-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 54° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|--------|
| 0° | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 |
| 2.5° | 4094.6 | 4033.6 | 4035.5 | 4007.8 | 3906.5 | 3827.2 | 3744.8 | 3725.3 | 3597.0 | 3462.3 | 3332.7 |
| 5° | 4802.4 | 4757.8 | 4747.1 | 4693.6 | 4552.7 | 4403.6 | 4243.7 | 4206.6 | 3955.6 | 3680.0 | 3408.8 |
| 7.5° | 5166.1 | 5166.7 | 5157.9 | 5138.4 | 5050.3 | 4905.6 | 4710.6 | 4671.6 | 4329.9 | 3916.6 | 3488.1 |
| 10° | 5060.4 | 5084.3 | 5133.4 | 5198.2 | 5265.5 | 5247.3 | 5100.7 | 5065.4 | 4694.2 | 4167.0 | 3576.2 |
| 12.5° | 4813.8 | 4816.9 | 4871.7 | 4978.0 | 5171.8 | 5370.6 | 5373.1 | 5361.2 | 5042.2 | 4428.7 | 3673.1 |
| 15° | 4691.1 | 4703.0 | 4723.2 | 4791.8 | 4975.5 | 5293.8 | 5521.6 | 5538.6 | 5361.2 | 4706.8 | 3776.3 |
| 17.5° | 4771.6 | 4788.6 | 4771.6 | 4779.8 | 4886.1 | 5172.4 | 5547.4 | 5590.8 | 5639.9 | 4981.8 | 3873.8 |
| 20° | 4989.9 | 5005.7 | 4975.5 | 4942.1 | 4962.9 | 5137.2 | 5529.1 | 5587.7 | 5858.2 | 5225.9 | 3955.6 |
| 22.5° | 5284.4 | 5290.7 | 5244.8 | 5190.0 | 5174.9 | 5256.7 | 5544.2 | 5604.6 | 6033.1 | 5446.7 | 4007.2 |
| 25° | 5608.4 | 5614.1 | 5556.8 | 5493.9 | 5458.0 | 5491.4 | 5668.2 | 5713.5 | 6187.2 | 5657.5 | 4036.7 |
| 27.5° | 5961.4 | 5966.4 | 5894.7 | 5817.3 | 5775.8 | 5777.0 | 5872.7 | 5921.1 | 6351.5 | 5897.8 | 4060.7 |
| 30° | 6334.5 | 6332.0 | 6265.9 | 6158.3 | 6105.5 | 6104.2 | 6167.1 | 6216.2 | 6589.3 | 6206.1 | 4093.4 |
| 32.5° | 6753.5 | 6748.5 | 6654.7 | 6521.3 | 6461.6 | 6470.4 | 6526.4 | 6554.7 | 6884.4 | 6534.6 | 4151.9 |
| 35° | 7305.3 | 7290.8 | 7149.2 | 6983.8 | 6873.7 | 6870.5 | 6917.7 | 6940.4 | 7260.6 | 6932.2 | 4249.4 |
| 37.5° | 8021.3 | 8008.1 | 7816.2 | 7575.8 | 7421.1 | 7363.2 | 7419.2 | 7448.1 | 7797.3 | 7442.4 | 4406.1 |
| 40° | 8727.2 | 8714.0 | 8600.1 | 8379.9 | 8141.4 | 8002.4 | 8046.4 | 8077.3 | 8467.4 | 8061.5 | 4603.6 |
| 42.5° | 9214.2 | 9225.5 | 9265.1 | 9283.4 | 9060.0 | 8768.1 | 8788.2 | 8820.3 | 9171.4 | 8723.4 | 4829.5 |
| 45° | 9342.5 | 9367.1 | 9591.1 | 10030.8 | 10114.5 | 9886.8 | 9676.0 | 9693.6 | 9886.8 | 9385.3 | 5055.4 |
| 47.5° | 8956.9 | 9002.2 | 9434.4 | 10252.3 | 10960.8 | 11121.8 | 10722.9 | 10699.7 | 10573.2 | 9920.7 | 5215.8 |
| 50° | 8080.4 | 8121.9 | 8681.9 | 9891.8 | 11217.5 | 12300.9 | 11977.5 | 11908.9 | 11175.3 | 10241.0 | 5272.4 |
| 52.5° | 6812.0 | 6862.3 | 7317.2 | 8756.8 | 10733.6 | 12826.9 | 13165.4 | 13108.1 | 11617.0 | 10266.2 | 5281.9 |
| 55° | 4810.6 | 4871.7 | 5353.0 | 6711.3 | 9200.3 | 12408.5 | 13586.3 | 13569.3 | 11983.8 | 10199.5 | 5302.0 |
| 57.5° | 2703.5 | 2747.6 | 3266.6 | 4302.3 | 6738.4 | 10807.9 | 13146.5 | 13259.1 | 12205.3 | 10083.7 | 5332.2 |
| 60° | 1200.5 | 1212.4 | 1481.1 | 2141.7 | 3944.9 | 8259.7 | 11887.5 | 12077.5 | 12015.2 | 9928.9 | 5383.2 |
| 62.5° | 665.7 | 655.6 | 655.6 | 890.3 | 1714.5 | 5113.3 | 9693.6 | 10007.6 | 11204.2 | 9745.8 | 5385.7 |
| 65° | 521.6 | 512.1 | 485.1 | 488.9 | 653.1 | 2269.4 | 6712.6 | 7270.7 | 9664.0 | 9209.1 | 5204.5 |
| 67.5° | 442.3 | 434.1 | 407.1 | 396.4 | 405.8 | 748.7 | 3688.2 | 4267.7 | 7333.0 | 7814.3 | 4508.0 |
| 70° | 373.7 | 368.1 | 354.2 | 341.0 | 317.1 | 370.0 | 1411.2 | 1805.1 | 4518.7 | 5198.2 | 3077.3 |
| 72.5° | 300.7 | 298.2 | 303.3 | 291.9 | 263.0 | 246.6 | 482.6 | 584.5 | 2029.7 | 2319.7 | 1267.8 |
| 75° | 259.2 | 258.0 | 260.5 | 249.2 | 216.4 | 171.8 | 245.4 | 268.0 | 572.5 | 567.5 | 256.7 |
| 77.5° | 168.6 | 170.5 | 215.8 | 210.8 | 186.2 | 114.5 | 127.1 | 137.2 | 173.7 | 130.2 | 78.0 |
| 80° | 107.6 | 106.3 | 109.5 | 174.9 | 167.4 | 87.5 | 63.5 | 66.7 | 83.7 | 64.2 | 37.8 |
| 82.5° | 65.4 | 64.2 | 71.7 | 81.8 | 84.3 | 61.0 | 39.0 | 39.6 | 52.2 | 41.5 | 20.1 |
| 85° | 5.7 | 7.6 | 43.4 | 40.3 | 28.9 | 18.9 | 18.9 | 20.1 | 27.7 | 24.5 | 11.3 |
| 87.5° | 0.0 | 0.0 | 7.6 | 11.3 | 6.3 | 6.9 | 6.9 | 7.6 | 10.7 | 10.7 | 5.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P364249

CATALOG NUMBER: NVN-SA3D-827-U-AFL-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 | 3262.9 |
| 2.5° | 3265.4 | 3200.0 | 3067.8 | 2940.7 | 2833.1 | 2729.3 | 2611.1 | 2494.0 | 2439.3 | 2417.3 | 2394.6 |
| 5° | 3271.1 | 3136.4 | 2864.0 | 2589.7 | 2305.3 | 2049.2 | 1830.9 | 1606.9 | 1494.9 | 1445.8 | 1423.2 |
| 7.5° | 3278.6 | 3073.5 | 2633.1 | 2172.5 | 1714.5 | 1367.2 | 1063.9 | 868.9 | 784.6 | 771.4 | 738.6 |
| 10° | 3279.9 | 2997.4 | 2365.0 | 1712.0 | 1149.5 | 824.2 | 634.2 | 533.5 | 496.4 | 490.1 | 479.4 |
| 12.5° | 3282.4 | 2907.4 | 2067.4 | 1267.8 | 766.3 | 551.2 | 458.7 | 425.3 | 415.3 | 414.6 | 414.6 |
| 15° | 3289.9 | 2813.0 | 1758.5 | 913.6 | 550.5 | 436.6 | 402.7 | 389.5 | 385.7 | 387.6 | 386.9 |
| 17.5° | 3289.9 | 2701.7 | 1455.3 | 680.8 | 444.8 | 392.6 | 373.7 | 364.9 | 363.7 | 365.5 | 366.2 |
| 20° | 3266.0 | 2566.4 | 1177.2 | 529.8 | 394.5 | 364.3 | 347.3 | 339.1 | 336.0 | 337.2 | 337.9 |
| 22.5° | 3208.8 | 2400.3 | 950.7 | 438.5 | 361.1 | 338.5 | 320.2 | 307.7 | 302.6 | 303.3 | 303.3 |
| 25° | 3119.4 | 2203.4 | 743.7 | 379.4 | 334.1 | 310.8 | 289.4 | 274.9 | 271.8 | 271.2 | 272.4 |
| 27.5° | 3004.9 | 1985.7 | 592.0 | 334.1 | 302.0 | 280.0 | 258.6 | 246.6 | 244.1 | 244.7 | 245.4 |
| 30° | 2892.3 | 1759.8 | 466.8 | 295.7 | 266.1 | 245.4 | 229.0 | 223.4 | 223.4 | 225.2 | 225.9 |
| 32.5° | 2789.1 | 1542.7 | 369.3 | 262.4 | 234.1 | 215.2 | 205.7 | 205.1 | 208.3 | 209.5 | 210.1 |
| 35° | 2700.4 | 1342.0 | 305.8 | 236.6 | 208.9 | 192.5 | 189.4 | 191.9 | 195.7 | 198.2 | 198.8 |
| 37.5° | 2637.5 | 1162.7 | 267.4 | 215.2 | 189.4 | 176.2 | 175.5 | 180.6 | 185.6 | 191.3 | 192.5 |
| 40° | 2611.1 | 1011.1 | 241.0 | 196.3 | 173.7 | 163.6 | 161.7 | 168.6 | 178.1 | 186.2 | 187.5 |
| 42.5° | 2589.0 | 887.1 | 218.3 | 178.1 | 161.1 | 146.6 | 146.0 | 154.8 | 166.1 | 174.3 | 176.2 |
| 45° | 2570.2 | 787.7 | 197.6 | 158.6 | 144.7 | 125.8 | 127.7 | 139.0 | 147.9 | 156.7 | 158.6 |
| 47.5° | 2531.1 | 705.9 | 174.9 | 137.8 | 119.5 | 107.6 | 111.4 | 121.4 | 128.4 | 141.6 | 143.5 |
| 50° | 2461.3 | 639.2 | 151.6 | 112.6 | 97.5 | 93.1 | 98.8 | 105.7 | 114.5 | 125.8 | 127.1 |
| 52.5° | 2414.1 | 588.9 | 131.5 | 94.4 | 80.5 | 81.8 | 87.5 | 90.0 | 95.0 | 99.4 | 98.2 |
| 55° | 2387.1 | 561.2 | 115.1 | 81.8 | 68.6 | 72.4 | 73.6 | 70.5 | 68.0 | 63.5 | 61.7 |
| 57.5° | 2383.9 | 536.1 | 102.6 | 71.1 | 60.4 | 62.3 | 57.9 | 47.2 | 38.4 | 33.3 | 32.1 |
| 60° | 2378.9 | 505.2 | 92.5 | 59.8 | 53.5 | 51.0 | 41.5 | 25.8 | 18.2 | 17.0 | 17.0 |
| 62.5° | 2324.2 | 457.4 | 84.9 | 50.3 | 45.3 | 38.4 | 23.9 | 12.0 | 10.1 | 10.7 | 10.7 |
| 65° | 2149.9 | 390.7 | 77.4 | 40.9 | 35.9 | 27.7 | 12.0 | 6.9 | 3.8 | 4.4 | 4.4 |
| 67.5° | 1827.7 | 311.4 | 69.2 | 31.5 | 27.1 | 17.6 | 6.9 | 3.1 | 0.0 | 0.0 | 0.0 |
| 70° | 1223.7 | 193.2 | 58.5 | 22.0 | 17.6 | 10.7 | 5.0 | 0.6 | 0.0 | 0.0 | 0.0 |
| 72.5° | 469.4 | 104.4 | 47.2 | 13.2 | 11.3 | 7.6 | 3.1 | 0.0 | 0.0 | 0.0 | 0.0 |
| 75° | 105.7 | 68.6 | 32.7 | 9.4 | 8.2 | 5.0 | 1.3 | 0.0 | 0.0 | 0.0 | 0.0 |
| 77.5° | 40.3 | 49.7 | 18.9 | 6.3 | 5.7 | 3.1 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 19.5 | 29.6 | 8.8 | 3.8 | 3.1 | 1.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 10.1 | 11.3 | 3.8 | 1.9 | 1.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 5.7 | 5.7 | 1.9 | 1.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 3.1 | 1.9 | 0.6 | 0.6 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 2764K
 CIE x = 0.4581
 CIE y = 0.4156
 Duv = 0.0020

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)