

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P361946

Luminaire Tested: NVN-SA4D-827-U-SL3

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P361946
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-22)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA4D-827-U-SL3
Description: NAVION ROADWAY AND AREA LUMINAIRE
(4) 80 CRI, 2700K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
SPILL LIGHT ELIMINATOR OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23347 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B3 - U0 - G4


Input Watts (W): 258
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P361946
 CATALOG NUMBER: NVN-SA4D-827-U-SL3

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 10.3 fc
 Type III - Medium - N/A

REPORT NUMBER: P361946
CATALOG NUMBER: NVN-SA4D-827-U-SL3

Luminous Intensity Polar Plot



— Vertical Plane Through 58-Deg Lateral - - - Horizontal Cone Through 71-Deg Vertical

REPORT NUMBER: P361946
 CATALOG NUMBER: NVN-SA4D-827-U-SL3

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3490.5 | 0.0 | 3490.5 |
| | % Fixture | 15.0 | 0.0 | 15.0 |
| Street Side | Lumens | 19856.5 | 0.0 | 19856.5 |
| | % Fixture | 85.0 | 0.0 | 85.0 |
| Total | Lumens | 23347.0 | 0.0 | 23347.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 558.1 | 2.4 |
| 10°-20° | 1240.9 | 5.3 |
| 20°-30° | 1577.1 | 6.8 |
| 30°-40° | 2008.8 | 8.6 |
| 40°-50° | 2848.6 | 12.2 |
| 50°-60° | 4408.4 | 18.9 |
| 60°-70° | 6001.5 | 25.7 |
| 70°-80° | 4003.7 | 17.1 |
| 80°-90° | 700.0 | 3.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 23347.0 | 100.0 |
| 0°-180° | 23347.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P361946
 CATALOG NUMBER: NVN-SA4D-827-U-SL3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 2238.2 | 9.6 | | | |
| FM (30°-60°) | 7985.8 | 34.2 | | | |
| FH (60°-80°) | 8990.6 | 38.5 | | | G4/12000 |
| FVH (80°-90°) | 641.8 | 2.7 | | | G4/750 |
| BL (0°-30°) | 1137.8 | 4.9 | B3/2500 | | |
| BM (30°-60°) | 1280.1 | 5.5 | B2/2500 | | |
| BH (60°-80°) | 1014.5 | 4.3 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 58.2 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G4
 Type III Medium





REPORT NUMBER: P361946

CATALOG NUMBER: NVN-SA4D-827-U-SL3

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 58° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 |
| 2.5° | 6640.3 | 6631.3 | 6634.6 | 6628.1 | 6612.6 | 6597.2 | 6574.4 | 6578.5 | 6546.8 | 6499.6 | 6441.0 |
| 5° | 6515.0 | 6511.8 | 6536.2 | 6550.0 | 6561.4 | 6552.4 | 6545.9 | 6554.1 | 6507.7 | 6442.7 | 6341.0 |
| 7.5° | 6252.4 | 6216.6 | 6247.5 | 6293.8 | 6337.7 | 6371.1 | 6415.0 | 6420.7 | 6391.4 | 6323.1 | 6189.7 |
| 10° | 5879.1 | 5844.9 | 5890.5 | 5962.8 | 6050.7 | 6130.4 | 6219.0 | 6235.3 | 6241.0 | 6179.2 | 6017.3 |
| 12.5° | 5492.0 | 5465.9 | 5511.5 | 5613.1 | 5758.7 | 5881.5 | 6023.0 | 6047.4 | 6097.8 | 6056.4 | 5857.9 |
| 15° | 5145.5 | 5135.7 | 5191.0 | 5291.1 | 5458.6 | 5646.5 | 5850.6 | 5895.3 | 5980.7 | 5966.9 | 5733.5 |
| 17.5° | 4846.2 | 4843.8 | 4886.1 | 4991.0 | 5176.4 | 5413.9 | 5679.0 | 5754.6 | 5881.5 | 5897.8 | 5631.0 |
| 20° | 4623.4 | 4618.5 | 4647.8 | 4725.0 | 4916.2 | 5185.4 | 5493.6 | 5597.7 | 5780.7 | 5837.6 | 5525.3 |
| 22.5° | 4503.8 | 4503.0 | 4503.8 | 4540.4 | 4696.6 | 4947.1 | 5313.0 | 5439.9 | 5682.3 | 5789.6 | 5408.2 |
| 25° | 4483.5 | 4481.1 | 4463.2 | 4459.1 | 4547.8 | 4747.8 | 5134.1 | 5274.0 | 5588.7 | 5756.3 | 5296.8 |
| 27.5° | 4536.4 | 4539.6 | 4516.0 | 4477.8 | 4495.7 | 4616.9 | 4978.8 | 5128.4 | 5513.9 | 5749.8 | 5219.5 |
| 30° | 4646.2 | 4644.5 | 4624.2 | 4584.4 | 4549.4 | 4568.1 | 4868.2 | 5017.8 | 5463.5 | 5778.2 | 5166.6 |
| 32.5° | 4767.3 | 4776.3 | 4772.2 | 4750.3 | 4698.2 | 4623.4 | 4834.8 | 4981.2 | 5448.9 | 5846.5 | 5143.9 |
| 35° | 4912.9 | 4922.7 | 4951.9 | 4969.0 | 4908.0 | 4787.7 | 4906.4 | 5033.3 | 5491.1 | 5975.0 | 5180.5 |
| 37.5° | 5051.2 | 5076.4 | 5158.5 | 5230.9 | 5178.8 | 5044.7 | 5096.7 | 5187.0 | 5622.1 | 6177.5 | 5278.9 |
| 40° | 5210.6 | 5232.5 | 5366.7 | 5520.4 | 5512.3 | 5373.2 | 5403.3 | 5463.5 | 5853.0 | 6467.9 | 5457.0 |
| 42.5° | 5367.5 | 5411.4 | 5605.8 | 5823.8 | 5886.4 | 5763.6 | 5811.6 | 5843.3 | 6178.3 | 6852.5 | 5767.6 |
| 45° | 5576.5 | 5623.7 | 5893.7 | 6156.4 | 6302.8 | 6233.6 | 6310.1 | 6322.3 | 6587.4 | 7376.3 | 6219.0 |
| 47.5° | 5892.9 | 5946.6 | 6261.3 | 6537.0 | 6760.6 | 6768.0 | 6894.0 | 6889.1 | 7098.1 | 7975.7 | 6787.5 |
| 50° | 6385.7 | 6463.0 | 6720.8 | 6978.6 | 7250.2 | 7401.5 | 7569.8 | 7546.3 | 7710.5 | 8614.1 | 7442.2 |
| 52.5° | 7031.5 | 7067.2 | 7258.4 | 7448.7 | 7786.2 | 8125.3 | 8366.8 | 8345.7 | 8405.1 | 9270.4 | 8185.5 |
| 55° | 7700.8 | 7727.6 | 7806.5 | 7910.6 | 8364.4 | 8917.4 | 9428.1 | 9394.8 | 9244.3 | 9951.9 | 8919.8 |
| 57.5° | 8302.6 | 8357.1 | 8411.6 | 8454.7 | 8946.7 | 9745.3 | 10513.8 | 10516.3 | 10155.2 | 10687.1 | 9678.6 |
| 60° | 8396.1 | 8444.1 | 8804.4 | 9144.3 | 9942.9 | 10849.7 | 11676.0 | 11651.6 | 11097.8 | 11484.9 | 10524.4 |
| 62.5° | 7421.8 | 7530.0 | 8131.8 | 9036.1 | 10902.6 | 12869.9 | 13158.6 | 13128.5 | 12224.9 | 12468.1 | 11509.3 |
| 65° | 5318.7 | 5441.5 | 6167.8 | 7526.7 | 10437.4 | 15095.8 | 15834.2 | 15429.2 | 13762.0 | 13677.4 | 12662.5 |
| 67.5° | 3068.4 | 3097.7 | 3412.4 | 4503.8 | 7947.2 | 15212.1 | 19916.0 | 19349.1 | 16148.9 | 15049.4 | 13226.9 |
| 70° | 2269.0 | 2268.2 | 2343.0 | 2771.6 | 4300.5 | 12415.2 | 21857.2 | 22365.5 | 18661.9 | 15500.8 | 12429.1 |
| 71° | 2051.9 | 2054.3 | 2138.1 | 2522.7 | 3405.9 | 10391.9 | 21444.9 | 22557.4 | 19323.9 | 15277.9 | 11851.7 |
| 72.5° | 1755.0 | 1763.2 | 1879.4 | 2262.5 | 2865.1 | 7166.5 | 19668.7 | 21405.8 | 19637.8 | 14728.2 | 10948.1 |
| 75° | 1331.3 | 1350.0 | 1511.0 | 1907.1 | 2618.7 | 3634.5 | 14435.4 | 17093.1 | 17445.3 | 12995.9 | 8135.1 |
| 77.5° | 949.9 | 971.0 | 1153.2 | 1603.8 | 2489.4 | 2739.1 | 9667.2 | 12468.1 | 12838.1 | 8328.6 | 3669.4 |
| 80° | 600.2 | 625.4 | 762.8 | 1276.0 | 2338.9 | 2600.8 | 6075.1 | 8380.7 | 7000.6 | 2665.1 | 933.6 |
| 82.5° | 352.1 | 371.7 | 473.3 | 833.6 | 1910.4 | 2504.8 | 3574.3 | 4645.3 | 2724.4 | 805.1 | 424.5 |
| 85° | 204.1 | 213.1 | 295.2 | 531.1 | 1387.4 | 2364.2 | 2626.0 | 2596.7 | 1182.5 | 393.6 | 200.9 |
| 87.5° | 95.2 | 105.7 | 174.9 | 277.3 | 770.2 | 1713.5 | 2075.4 | 1793.2 | 735.2 | 184.6 | 94.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P361946
 CATALOG NUMBER: NVN-SA4D-827-U-SL3

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 | 6468.7 |
| 2.5° | 6412.6 | 6398.7 | 6341.0 | 6289.8 | 6236.1 | 6166.1 | 6088.9 | 6079.1 | 6032.0 | 6040.9 | 6024.6 |
| 5° | 6285.7 | 6250.7 | 6111.7 | 5985.6 | 5836.8 | 5703.4 | 5558.6 | 5492.0 | 5396.0 | 5389.5 | 5365.1 |
| 7.5° | 6104.3 | 6039.3 | 5823.8 | 5584.7 | 5345.6 | 5117.9 | 4892.6 | 4744.6 | 4593.3 | 4529.1 | 4523.4 |
| 10° | 5900.2 | 5789.6 | 5472.4 | 5118.7 | 4773.8 | 4441.2 | 4119.2 | 3880.9 | 3666.2 | 3564.5 | 3560.5 |
| 12.5° | 5706.7 | 5543.2 | 5108.1 | 4626.6 | 4155.0 | 3723.9 | 3282.3 | 2969.2 | 2700.0 | 2609.8 | 2571.5 |
| 15° | 5542.4 | 5312.2 | 4753.5 | 4137.9 | 3565.3 | 2966.8 | 2464.2 | 2134.8 | 1886.0 | 1799.7 | 1783.5 |
| 17.5° | 5383.0 | 5086.9 | 4390.0 | 3644.2 | 2952.1 | 2294.2 | 1790.8 | 1546.0 | 1413.4 | 1378.5 | 1377.7 |
| 20° | 5224.4 | 4855.2 | 4010.2 | 3139.2 | 2359.3 | 1716.0 | 1376.9 | 1267.1 | 1222.3 | 1218.3 | 1211.8 |
| 22.5° | 5044.7 | 4609.6 | 3610.9 | 2632.5 | 1841.2 | 1349.2 | 1170.3 | 1126.4 | 1120.7 | 1135.3 | 1135.3 |
| 25° | 4876.3 | 4365.6 | 3205.9 | 2136.4 | 1432.2 | 1125.6 | 1045.0 | 1036.1 | 1051.5 | 1077.6 | 1080.0 |
| 27.5° | 4719.4 | 4130.6 | 2810.6 | 1695.6 | 1147.5 | 991.4 | 958.0 | 968.6 | 996.2 | 1026.3 | 1027.1 |
| 30° | 4590.0 | 3908.5 | 2426.8 | 1336.2 | 969.4 | 891.3 | 885.6 | 906.8 | 936.9 | 960.5 | 966.2 |
| 32.5° | 4490.0 | 3719.0 | 2055.9 | 1074.3 | 853.1 | 816.5 | 821.4 | 839.3 | 858.0 | 871.0 | 879.9 |
| 35° | 4443.7 | 3556.4 | 1713.5 | 906.0 | 779.1 | 758.8 | 765.3 | 775.0 | 783.2 | 792.9 | 800.2 |
| 37.5° | 4451.8 | 3430.3 | 1407.8 | 801.1 | 729.5 | 718.9 | 718.9 | 718.9 | 718.9 | 723.8 | 724.6 |
| 40° | 4527.4 | 3358.0 | 1158.9 | 734.4 | 696.2 | 684.8 | 675.8 | 667.7 | 661.2 | 664.4 | 662.8 |
| 42.5° | 4721.0 | 3351.4 | 976.7 | 692.1 | 669.3 | 650.6 | 632.7 | 621.3 | 613.2 | 616.5 | 618.1 |
| 45° | 5049.5 | 3432.8 | 853.9 | 662.0 | 644.1 | 615.6 | 592.9 | 580.7 | 575.0 | 585.5 | 587.2 |
| 47.5° | 5474.9 | 3610.1 | 779.1 | 640.0 | 620.5 | 583.1 | 558.7 | 547.3 | 549.0 | 564.4 | 568.5 |
| 50° | 6023.0 | 3898.0 | 743.3 | 626.2 | 604.3 | 555.5 | 530.2 | 520.5 | 525.4 | 547.3 | 552.2 |
| 52.5° | 6624.8 | 4312.7 | 747.4 | 622.1 | 593.7 | 535.1 | 508.3 | 496.9 | 505.0 | 525.4 | 529.4 |
| 55° | 7319.4 | 4811.3 | 814.9 | 627.8 | 578.2 | 522.1 | 490.4 | 470.9 | 477.4 | 496.1 | 499.3 |
| 57.5° | 8091.1 | 5382.2 | 950.7 | 626.2 | 558.7 | 509.9 | 471.7 | 442.4 | 447.3 | 458.7 | 461.9 |
| 60° | 8894.6 | 6071.8 | 1161.3 | 631.1 | 549.8 | 495.3 | 446.5 | 409.9 | 408.3 | 418.0 | 419.6 |
| 62.5° | 9859.2 | 6869.6 | 1402.1 | 634.3 | 555.5 | 476.6 | 413.1 | 377.4 | 372.5 | 374.9 | 376.5 |
| 65° | 10853.0 | 7447.0 | 1311.8 | 621.3 | 573.3 | 461.1 | 383.9 | 345.6 | 336.7 | 335.1 | 335.9 |
| 67.5° | 10883.9 | 6828.1 | 919.8 | 595.3 | 580.7 | 453.0 | 361.9 | 318.8 | 304.2 | 298.5 | 297.7 |
| 70° | 9760.8 | 5547.3 | 716.5 | 567.7 | 551.4 | 440.0 | 341.6 | 296.8 | 274.9 | 265.9 | 265.1 |
| 71° | 9212.6 | 5106.5 | 679.1 | 553.8 | 529.4 | 427.0 | 332.6 | 287.1 | 264.3 | 254.6 | 252.9 |
| 72.5° | 8353.0 | 4577.8 | 633.5 | 531.9 | 487.1 | 393.6 | 315.5 | 273.3 | 249.7 | 238.3 | 235.8 |
| 75° | 5994.5 | 2993.6 | 544.1 | 474.1 | 403.4 | 313.9 | 276.5 | 245.6 | 225.3 | 211.4 | 209.8 |
| 77.5° | 2309.7 | 1191.4 | 411.5 | 394.4 | 309.0 | 245.6 | 227.7 | 212.3 | 197.6 | 183.8 | 183.0 |
| 80° | 714.0 | 532.7 | 300.1 | 296.8 | 223.6 | 183.0 | 177.3 | 173.2 | 167.5 | 152.9 | 149.6 |
| 82.5° | 381.4 | 305.8 | 206.6 | 191.9 | 146.4 | 122.0 | 128.5 | 130.1 | 130.9 | 115.5 | 113.9 |
| 85° | 182.2 | 161.8 | 116.3 | 109.0 | 85.4 | 68.3 | 78.9 | 85.4 | 86.2 | 70.8 | 65.9 |
| 87.5° | 87.0 | 84.6 | 54.5 | 41.5 | 31.7 | 22.8 | 27.7 | 34.2 | 37.4 | 26.8 | 23.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)