

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P363804

Luminaire Tested: NVN-SA2B-827-U-SL4-HSS

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P363804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-25)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA2B-827-U-SL4-HSS
Description: NAVION ROADWAY AND AREA LUMINAIRE
(2) 80 CRI, 2700K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV SPILL
LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7003 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 85
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P363804
 CATALOG NUMBER: NVN-SA2B-827-U-SL4-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 13.6 fc
 Type IV - Short - N/A

REPORT NUMBER: P363804
CATALOG NUMBER: NVN-SA2B-827-U-SL4-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 38-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P363804
 CATALOG NUMBER: NVN-SA2B-827-U-SL4-HSS

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 589.3 | 0.0 | 589.3 |
| | % Fixture | 8.4 | 0.0 | 8.4 |
| Street Side | Lumens | 6413.7 | 0.0 | 6413.7 |
| | % Fixture | 91.6 | 0.0 | 91.6 |
| Total | Lumens | 7003.0 | 0.0 | 7003.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 109.7 | 1.6 |
| 10°-20° | 268.4 | 3.8 |
| 20°-30° | 426.8 | 6.1 |
| 30°-40° | 641.7 | 9.2 |
| 40°-50° | 978.9 | 14.0 |
| 50°-60° | 1383.5 | 19.8 |
| 60°-70° | 1735.4 | 24.8 |
| 70°-80° | 1297.6 | 18.5 |
| 80°-90° | 160.9 | 2.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 7003.0 | 100.0 |
| 0°-180° | 7003.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P363804
 CATALOG NUMBER: NVN-SA2B-827-U-SL4-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 595.1 | 8.5 | | | |
| FM (30°-60°) | 2704.9 | 38.6 | | | |
| FH (60°-80°) | 2954.3 | 42.2 | | | G2/5000 |
| FVH (80°-90°) | 159.4 | 2.3 | | | G2/225 |
| BL (0°-30°) | 209.8 | 3.0 | B1/500 | | |
| BM (30°-60°) | 299.3 | 4.3 | B1/1000 | | |
| BH (60°-80°) | 78.7 | 1.1 | B0/110 | | G0/110 |
| BVH (80°-90°) | 1.5 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type IV Short





REPORT NUMBER: P363804

CATALOG NUMBER: NVN-SA2B-827-U-SL4-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 38° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 |
| 2.5° | 1366.9 | 1367.2 | 1364.0 | 1358.8 | 1352.1 | 1348.6 | 1342.8 | 1333.5 | 1323.6 | 1305.9 | 1286.7 |
| 5° | 1394.9 | 1394.9 | 1390.8 | 1383.8 | 1373.0 | 1369.8 | 1358.8 | 1344.0 | 1323.6 | 1294.8 | 1262.5 |
| 7.5° | 1391.9 | 1392.5 | 1387.0 | 1379.7 | 1369.0 | 1366.1 | 1352.7 | 1336.1 | 1310.8 | 1275.9 | 1234.6 |
| 10° | 1376.8 | 1378.3 | 1373.9 | 1370.4 | 1360.5 | 1357.3 | 1344.8 | 1328.3 | 1303.0 | 1265.7 | 1218.3 |
| 12.5° | 1361.4 | 1362.9 | 1364.3 | 1367.5 | 1361.4 | 1360.2 | 1350.4 | 1336.4 | 1312.3 | 1273.6 | 1220.1 |
| 15° | 1351.5 | 1354.4 | 1364.9 | 1377.4 | 1378.9 | 1377.7 | 1371.3 | 1358.2 | 1333.8 | 1293.6 | 1232.6 |
| 17.5° | 1351.5 | 1356.2 | 1378.0 | 1401.8 | 1410.3 | 1411.1 | 1405.6 | 1387.3 | 1358.2 | 1315.2 | 1244.2 |
| 20° | 1362.9 | 1369.3 | 1403.3 | 1437.0 | 1451.0 | 1451.0 | 1440.2 | 1414.6 | 1380.6 | 1334.7 | 1252.1 |
| 22.5° | 1391.9 | 1400.4 | 1443.1 | 1482.1 | 1496.9 | 1493.7 | 1479.2 | 1442.0 | 1403.9 | 1356.8 | 1261.9 |
| 25° | 1449.2 | 1455.6 | 1500.1 | 1539.4 | 1548.4 | 1541.1 | 1522.8 | 1475.1 | 1433.5 | 1386.7 | 1280.0 |
| 27.5° | 1523.1 | 1524.0 | 1569.9 | 1603.1 | 1597.6 | 1592.6 | 1569.7 | 1516.7 | 1476.3 | 1429.5 | 1311.1 |
| 30° | 1604.3 | 1604.3 | 1644.7 | 1670.0 | 1653.1 | 1649.0 | 1626.1 | 1567.0 | 1531.0 | 1487.6 | 1355.3 |
| 32.5° | 1682.8 | 1686.3 | 1719.1 | 1735.1 | 1716.2 | 1712.2 | 1689.8 | 1630.7 | 1603.7 | 1576.3 | 1424.2 |
| 35° | 1758.7 | 1761.3 | 1792.4 | 1801.2 | 1783.1 | 1784.3 | 1768.3 | 1718.3 | 1708.1 | 1704.6 | 1528.1 |
| 37.5° | 1832.3 | 1832.9 | 1864.6 | 1870.1 | 1861.1 | 1871.0 | 1872.4 | 1828.2 | 1847.1 | 1875.3 | 1674.4 |
| 40° | 1899.5 | 1900.0 | 1931.5 | 1945.7 | 1961.1 | 1973.9 | 1985.3 | 1961.7 | 2024.2 | 2089.7 | 1848.6 |
| 42.5° | 1953.3 | 1959.4 | 1999.2 | 2026.3 | 2067.0 | 2091.4 | 2122.2 | 2121.1 | 2235.1 | 2333.4 | 2059.1 |
| 45° | 2000.7 | 2011.1 | 2066.7 | 2114.1 | 2183.9 | 2222.9 | 2271.2 | 2309.0 | 2472.4 | 2604.7 | 2272.3 |
| 47.5° | 2063.2 | 2073.1 | 2136.5 | 2214.1 | 2307.2 | 2358.4 | 2438.4 | 2520.1 | 2733.3 | 2871.1 | 2480.6 |
| 50° | 2151.3 | 2147.0 | 2209.5 | 2320.9 | 2440.4 | 2507.6 | 2621.6 | 2744.1 | 2992.1 | 3103.2 | 2603.0 |
| 52.5° | 2245.3 | 2243.5 | 2289.8 | 2436.9 | 2597.5 | 2676.0 | 2826.7 | 2975.6 | 3239.6 | 3263.2 | 2659.1 |
| 55° | 2361.6 | 2349.1 | 2388.1 | 2569.3 | 2783.9 | 2868.2 | 3045.7 | 3204.7 | 3436.8 | 3353.4 | 2687.3 |
| 57.5° | 2483.5 | 2462.8 | 2500.0 | 2716.7 | 2994.2 | 3093.9 | 3288.2 | 3428.1 | 3568.0 | 3415.0 | 2687.0 |
| 60° | 2609.4 | 2585.0 | 2629.2 | 2901.1 | 3255.3 | 3370.8 | 3551.1 | 3579.0 | 3690.4 | 3446.1 | 2667.3 |
| 62.5° | 2714.7 | 2700.1 | 2765.9 | 3098.3 | 3547.1 | 3660.5 | 3749.8 | 3716.3 | 3793.7 | 3470.3 | 2621.0 |
| 65° | 2826.1 | 2826.9 | 2933.1 | 3328.3 | 3857.1 | 3933.6 | 3941.1 | 3894.3 | 3880.1 | 3465.3 | 2464.6 |
| 67.5° | 2976.7 | 2990.7 | 3167.8 | 3640.7 | 4158.7 | 4217.7 | 4217.1 | 4087.1 | 3943.2 | 3268.7 | 2117.6 |
| 70° | 3136.1 | 3169.0 | 3438.3 | 3998.1 | 4487.9 | 4547.8 | 4517.0 | 4209.9 | 3712.8 | 2643.1 | 1498.7 |
| 72.5° | 3109.3 | 3166.3 | 3588.6 | 4223.5 | 4724.4 | 4770.0 | 4569.6 | 3908.3 | 2934.6 | 1536.2 | 638.1 |
| 75° | 2398.8 | 2464.8 | 3290.5 | 4000.2 | 4476.3 | 4435.3 | 3926.3 | 3041.3 | 1603.7 | 428.7 | 143.7 |
| 77.5° | 1267.2 | 1302.4 | 2173.7 | 3047.4 | 3490.3 | 3404.5 | 2765.9 | 1687.1 | 488.9 | 106.2 | 64.6 |
| 80° | 663.7 | 671.8 | 947.3 | 1729.0 | 2154.2 | 2154.8 | 1639.2 | 741.1 | 201.6 | 54.4 | 43.3 |
| 82.5° | 355.4 | 362.4 | 500.5 | 798.9 | 1128.7 | 1023.2 | 627.6 | 407.8 | 117.2 | 30.8 | 41.6 |
| 85° | 85.5 | 87.0 | 283.9 | 365.0 | 443.8 | 317.0 | 186.4 | 342.3 | 31.7 | 18.0 | 33.7 |
| 87.5° | 32.9 | 33.4 | 105.3 | 157.9 | 113.1 | 73.3 | 87.3 | 127.7 | 4.1 | 7.0 | 5.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P363804
 CATALOG NUMBER: NVN-SA2B-827-U-SL4-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 | 1287.8 |
| 2.5° | 1275.0 | 1267.5 | 1248.9 | 1225.3 | 1204.4 | 1189.2 | 1166.5 | 1151.7 | 1141.8 | 1141.5 | 1137.8 |
| 5° | 1242.7 | 1227.3 | 1187.2 | 1139.5 | 1096.2 | 1057.2 | 1011.2 | 974.9 | 947.8 | 943.5 | 934.2 |
| 7.5° | 1208.1 | 1182.8 | 1121.2 | 1046.7 | 974.0 | 900.1 | 814.3 | 761.1 | 715.5 | 693.6 | 691.3 |
| 10° | 1186.9 | 1151.4 | 1063.9 | 956.3 | 842.3 | 722.1 | 609.9 | 532.2 | 476.1 | 460.1 | 448.2 |
| 12.5° | 1182.5 | 1135.7 | 1019.7 | 871.3 | 708.5 | 549.7 | 425.5 | 342.9 | 298.1 | 283.9 | 280.1 |
| 15° | 1186.9 | 1128.4 | 982.4 | 787.3 | 572.9 | 390.0 | 285.6 | 237.6 | 220.7 | 216.7 | 216.4 |
| 17.5° | 1189.5 | 1119.7 | 940.3 | 693.9 | 441.5 | 278.6 | 218.7 | 204.7 | 202.1 | 201.8 | 202.4 |
| 20° | 1189.2 | 1106.3 | 890.0 | 589.8 | 328.4 | 219.0 | 197.8 | 194.9 | 194.3 | 194.6 | 194.3 |
| 22.5° | 1187.2 | 1090.6 | 834.7 | 482.5 | 248.1 | 195.7 | 188.8 | 187.0 | 186.7 | 186.7 | 186.7 |
| 25° | 1191.0 | 1078.1 | 773.9 | 379.8 | 204.5 | 185.0 | 180.6 | 179.2 | 178.9 | 178.9 | 178.3 |
| 27.5° | 1204.6 | 1071.2 | 707.3 | 292.3 | 184.7 | 175.4 | 171.9 | 171.6 | 170.7 | 170.4 | 171.0 |
| 30° | 1226.8 | 1071.2 | 634.3 | 227.4 | 172.8 | 165.5 | 162.9 | 162.3 | 162.0 | 161.7 | 162.0 |
| 32.5° | 1265.7 | 1079.3 | 554.6 | 189.0 | 161.4 | 154.4 | 152.7 | 153.6 | 152.7 | 152.7 | 152.7 |
| 35° | 1336.1 | 1103.7 | 471.2 | 164.9 | 149.5 | 143.7 | 141.9 | 143.1 | 142.5 | 142.5 | 142.2 |
| 37.5° | 1438.8 | 1149.1 | 387.1 | 150.4 | 139.0 | 132.9 | 130.6 | 132.3 | 131.7 | 131.7 | 131.5 |
| 40° | 1563.8 | 1215.1 | 307.1 | 139.3 | 128.8 | 122.4 | 120.4 | 121.3 | 119.8 | 119.8 | 120.4 |
| 42.5° | 1718.3 | 1298.9 | 237.3 | 128.6 | 118.7 | 112.6 | 111.4 | 110.5 | 107.9 | 106.4 | 106.7 |
| 45° | 1889.9 | 1386.1 | 185.0 | 118.1 | 109.1 | 104.1 | 102.4 | 100.0 | 95.7 | 92.8 | 93.1 |
| 47.5° | 2043.1 | 1453.3 | 150.4 | 107.9 | 100.3 | 96.6 | 93.9 | 89.6 | 83.2 | 79.7 | 80.0 |
| 50° | 2123.7 | 1463.5 | 128.0 | 97.7 | 92.2 | 88.4 | 84.6 | 77.9 | 70.4 | 66.6 | 66.3 |
| 52.5° | 2144.3 | 1415.8 | 111.4 | 88.4 | 84.1 | 79.7 | 74.7 | 65.7 | 57.3 | 53.2 | 52.6 |
| 55° | 2151.9 | 1343.1 | 96.6 | 79.7 | 75.3 | 70.4 | 64.0 | 53.8 | 46.0 | 41.9 | 41.6 |
| 57.5° | 2126.9 | 1234.6 | 84.9 | 71.8 | 66.6 | 60.5 | 52.6 | 43.0 | 35.5 | 32.3 | 32.3 |
| 60° | 2071.3 | 1087.7 | 75.9 | 63.4 | 57.6 | 50.6 | 42.5 | 33.4 | 26.5 | 23.8 | 23.8 |
| 62.5° | 1960.5 | 897.5 | 67.5 | 54.7 | 49.2 | 41.9 | 34.3 | 25.3 | 18.6 | 17.2 | 17.5 |
| 65° | 1751.4 | 680.9 | 59.0 | 46.8 | 41.9 | 34.6 | 26.8 | 18.0 | 12.5 | 12.5 | 13.1 |
| 67.5° | 1428.3 | 472.9 | 50.3 | 39.8 | 36.1 | 28.2 | 20.4 | 12.5 | 8.7 | 9.9 | 11.1 |
| 70° | 945.5 | 265.2 | 43.0 | 32.9 | 30.8 | 22.4 | 15.1 | 8.4 | 7.0 | 9.3 | 11.3 |
| 72.5° | 356.9 | 103.2 | 36.1 | 26.5 | 26.8 | 17.2 | 10.8 | 6.4 | 6.4 | 10.2 | 13.4 |
| 75° | 99.5 | 50.6 | 25.9 | 19.5 | 20.9 | 12.5 | 7.9 | 5.5 | 6.1 | 11.6 | 15.7 |
| 77.5° | 58.5 | 37.2 | 16.9 | 11.3 | 14.3 | 8.7 | 5.2 | 4.4 | 5.2 | 9.9 | 15.1 |
| 80° | 47.1 | 19.8 | 9.9 | 5.8 | 7.9 | 4.9 | 3.5 | 2.6 | 1.5 | 3.8 | 7.9 |
| 82.5° | 47.1 | 11.9 | 4.7 | 4.1 | 4.1 | 2.6 | 1.7 | 1.2 | 0.3 | 0.0 | 2.0 |
| 85° | 31.7 | 4.9 | 2.9 | 2.6 | 2.0 | 0.9 | 0.6 | 0.3 | 0.0 | 0.0 | 0.0 |
| 87.5° | 5.2 | 2.0 | 1.2 | 0.6 | 0.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)