

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P970299

Luminaire Tested: **NVN-SB6B-727-U-SLR-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P970299
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: NVN-SB6B-727-U-SLR-HSS
Description: NAVION ROADWAY AND AREA HIGH DENSITY LED LUMINAIRE
(6) 70 CRI, 2700K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24776.3 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G4


Input Watts (W): 220.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P970299
 CATALOG NUMBER: NVN-SB6B-727-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.6 fc
 Type IV - Short - N/A

REPORT NUMBER: P970299
CATALOG NUMBER: NVN-SB6B-727-U-SLR-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P970299
 CATALOG NUMBER: NVN-SB6B-727-U-SLR-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3469.7	0.0	3469.7
	% Fixture	14.0	0.0	14.0
Street Side	Lumens	21306.6	0.0	21306.6
	% Fixture	86.0	0.0	86.0
Total	Lumens	24776.3	0.0	24776.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.8	1.4
10°-20°	1012.5	4.1
20°-30°	1491.7	6.0
30°-40°	1916.4	7.7
40°-50°	3099.3	12.5
50°-60°	5435.0	21.9
60°-70°	6800.7	27.4
70°-80°	3974.0	16.0
80°-90°	709.0	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	24776.3	100.0
0°-180°	24776.3	100.0

Coefficient of Utilization




REPORT NUMBER: P970299
 CATALOG NUMBER: NVN-SB6B-727-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1932.5	7.8			
FM (30°-60°)	8683.8	35.0			
FH (60°-80°)	10008.5	40.4			G4/12000
FVH (80°-90°)	681.8	2.8			G4/750
BL (0°-30°)	909.5	3.7	B2/1000		
BM (30°-60°)	1766.9	7.1	B2/2500		
BH (60°-80°)	766.1	3.1	B2/1000		G2/1000
BVH (80°-90°)	27.2	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G4
 Type IV Short



REPORT NUMBER: P970299
 CATALOG NUMBER: NVN-SB6B-727-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7
2.5°	3876.2	3809.6	3770.4	3673.1	3575.8	3497.3	3391.4	3321.5	3237.9	3157.6	3086.0
5°	4320.0	4212.4	4082.8	3905.2	3743.1	3577.6	3417.0	3258.4	3091.1	2937.4	2843.6
7.5°	4695.5	4540.1	4311.5	4075.9	3869.4	3669.7	3481.9	3272.0	3068.8	2828.2	2700.2
10°	4982.2	4784.3	4483.9	4174.9	3937.6	3736.2	3553.6	3376.1	3171.2	2881.2	2720.7
12.5°	5156.4	4944.7	4588.0	4226.1	3954.8	3729.5	3587.7	3509.2	3429.0	3140.6	2952.8
15°	5284.4	5055.6	4661.4	4262.0	3915.5	3639.0	3534.8	3613.3	3705.5	3521.2	3304.4
17.5°	5417.4	5176.8	4756.9	4277.3	3809.6	3463.2	3418.8	3621.9	3835.2	3826.7	3611.7
20°	5543.8	5304.8	4840.6	4267.1	3639.0	3249.8	3289.0	3548.4	3796.0	3900.1	3784.0
22.5°	5688.9	5436.3	4920.8	4227.8	3417.0	3050.1	3173.0	3432.4	3649.2	3772.1	3736.2
25°	5866.4	5601.8	5033.5	4169.8	3178.1	2884.6	3055.2	3297.6	3473.4	3558.7	3557.1
27.5°	6057.5	5799.8	5183.6	4139.1	2985.2	2766.8	2922.1	3137.1	3294.1	3353.9	3353.9
30°	6294.8	6030.2	5361.2	4104.9	2858.9	2698.5	2783.8	2951.1	3104.7	3164.5	3164.5
32.5°	6554.3	6286.2	5531.8	4023.0	2782.2	2647.3	2649.0	2754.8	2894.8	2966.5	2976.7
35°	6878.5	6593.5	5714.5	3843.7	2720.7	2587.5	2517.6	2568.8	2684.9	2770.2	2792.4
37.5°	7341.0	6996.2	5938.0	3587.7	2630.3	2495.4	2379.3	2391.2	2480.0	2573.9	2608.0
40°	7979.4	7537.3	6200.9	3321.5	2500.5	2365.7	2227.4	2222.3	2287.2	2379.3	2416.8
42.5°	8843.1	8252.5	6516.6	3067.2	2376.0	2208.7	2067.0	2058.4	2109.7	2189.8	2229.1
45°	9983.2	9167.4	6904.1	2848.7	2278.6	2055.0	1915.1	1911.6	1954.4	2024.3	2065.3
47.5°	11442.6	10439.0	7291.5	2700.2	2227.4	1933.9	1790.5	1797.3	1834.9	1898.0	1927.0
50°	13332.1	12096.3	7409.3	2625.1	2227.4	1869.0	1679.6	1713.7	1744.3	1792.2	1809.2
52.5°	15597.0	13687.0	7020.2	2556.9	2241.1	1877.5	1585.7	1659.1	1681.2	1722.2	1729.0
55°	17696.4	14467.1	6035.3	2463.0	2244.4	1930.4	1505.4	1614.7	1655.6	1671.0	1669.3
57.5°	18915.0	14199.1	4879.8	2304.2	2230.8	1966.3	1454.2	1560.0	1638.6	1648.8	1633.4
60°	18683.0	13258.7	3592.8	2183.0	2130.2	1952.6	1438.9	1476.4	1601.0	1616.3	1595.9
62.5°	16894.2	11681.5	2493.7	2089.2	1908.2	1892.9	1433.8	1345.0	1519.0	1556.7	1527.7
65°	13579.5	9196.4	1761.5	1799.0	1672.7	1763.1	1406.4	1208.5	1420.0	1471.3	1426.9
67.5°	9851.8	6223.1	1271.6	1457.7	1515.7	1553.2	1345.0	1109.5	1307.4	1375.7	1317.6
70°	6322.1	3360.8	892.7	962.7	1276.7	1319.4	1239.1	1020.7	1193.1	1271.6	1208.5
72.5°	4494.1	1985.0	641.8	674.2	1025.8	1099.2	1090.7	921.7	1060.0	1155.5	1080.5
75°	3101.3	1094.1	433.6	481.3	744.2	892.7	841.4	792.0	897.8	995.1	921.7
77.5°	1944.1	489.8	259.4	334.6	488.1	701.5	576.9	612.7	699.8	790.3	713.5
80°	1082.1	189.4	145.0	221.9	266.3	510.3	319.2	394.3	515.5	580.4	518.9
82.5°	235.5	23.9	64.9	95.6	104.1	296.9	169.0	228.7	324.3	319.2	276.5
85°	0.0	0.0	12.0	13.6	6.9	128.0	61.4	75.1	105.8	99.0	75.1
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	3.4	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P970299
 CATALOG NUMBER: NVN-SB6B-727-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°	185°
0°	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7
2.5°	3072.3	2988.7	2927.2	2896.4	2870.9	2894.8	2908.4	2908.4	2966.5	3000.6	3014.2
5°	2783.8	2633.6	2519.2	2442.5	2396.3	2411.7	2428.8	2447.6	2521.0	2570.5	2602.9
7.5°	2584.1	2353.7	2179.7	2072.1	2015.8	2024.3	2036.3	2051.6	2123.3	2172.8	2215.4
10°	2546.6	2215.4	1969.6	1828.0	1759.7	1747.8	1741.0	1735.8	1778.5	1816.1	1850.2
12.5°	2700.2	2222.3	1879.2	1706.8	1623.2	1587.3	1546.4	1513.9	1520.8	1544.7	1587.3
15°	2975.0	2309.3	1850.2	1643.7	1539.6	1479.8	1432.0	1392.8	1384.3	1392.8	1399.6
17.5°	3289.0	2427.1	1846.7	1589.1	1459.3	1397.9	1358.6	1322.8	1310.9	1312.5	1321.1
20°	3497.3	2521.0	1836.6	1527.7	1382.5	1327.9	1293.8	1258.0	1246.0	1249.4	1251.1
22.5°	3517.8	2570.5	1821.2	1459.3	1305.7	1259.6	1225.5	1193.1	1191.4	1191.4	1201.6
25°	3406.8	2570.5	1788.7	1397.9	1232.4	1191.4	1160.6	1121.4	1128.2	1131.6	1145.2
27.5°	3234.5	2509.0	1727.3	1348.4	1169.2	1126.5	1095.8	1060.0	1068.5	1073.6	1089.0
30°	3063.7	2430.5	1653.9	1292.1	1109.5	1060.0	1037.7	1007.1	1010.4	1017.3	1034.3
32.5°	2905.1	2346.8	1566.9	1246.0	1049.7	1000.2	983.2	949.0	954.1	960.9	979.7
35°	2748.0	2254.7	1464.4	1191.4	995.1	945.6	931.9	892.7	896.1	906.3	926.8
37.5°	2579.0	2157.4	1380.8	1136.7	942.2	890.9	877.3	836.3	839.8	851.7	875.6
40°	2401.5	2061.9	1298.9	1078.7	885.8	834.7	822.7	778.3	781.8	795.4	821.0
42.5°	2222.3	1957.7	1235.7	1003.6	827.8	773.2	761.3	720.3	725.4	740.8	766.4
45°	2056.8	1833.1	1194.7	919.9	773.2	711.8	699.8	662.3	672.5	689.5	715.1
47.5°	1915.1	1705.1	1177.7	850.0	715.1	648.6	638.4	607.6	624.7	643.5	664.0
50°	1793.9	1582.2	1155.5	778.3	660.5	594.0	583.7	563.2	585.5	604.2	623.0
52.5°	1706.8	1442.3	1107.7	713.5	612.7	547.9	544.5	534.2	554.7	571.7	588.9
55°	1631.7	1297.2	1030.9	657.1	570.1	508.6	512.1	507.0	524.0	537.6	553.0
57.5°	1563.4	1170.9	933.7	612.7	524.0	474.5	484.7	478.0	486.5	495.0	513.7
60°	1481.5	1042.8	817.5	563.2	469.3	440.3	452.3	433.6	431.8	435.2	440.3
62.5°	1360.4	870.5	696.4	501.8	421.6	402.8	408.0	372.1	344.8	344.8	349.9
65°	1191.4	699.8	583.7	433.6	367.0	351.6	348.2	296.9	259.4	256.0	271.4
67.5°	995.1	575.2	484.7	365.3	305.6	295.3	298.7	261.2	223.6	220.2	237.3
70°	810.8	476.2	390.8	291.8	235.5	245.8	261.2	223.6	187.8	182.7	198.0
72.5°	658.9	378.9	305.6	223.6	174.1	203.2	221.9	182.7	148.5	145.0	158.8
75°	508.6	278.2	218.4	151.9	126.3	157.0	174.1	133.1	105.8	100.7	112.6
77.5°	339.7	172.4	122.9	95.6	75.1	107.5	116.0	70.0	61.4	59.8	68.3
80°	206.5	80.3	52.9	46.1	25.6	39.3	46.1	29.0	32.4	34.1	41.0
82.5°	104.1	22.1	8.5	1.7	0.0	0.0	13.6	6.9	13.6	17.1	25.6
85°	8.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	3.4	8.5	15.4
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P970299
 CATALOG NUMBER: NVN-SB6B-727-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°	285°
0°	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7
2.5°	3109.8	3181.5	3249.8	3359.0	3471.7	3582.7	3695.3	3804.5	3843.7	3872.8	3937.6
5°	2751.4	2886.3	3043.2	3260.0	3492.2	3731.1	3973.5	4195.4	4296.1	4364.3	4518.0
7.5°	2381.1	2556.9	2782.2	3108.1	3471.7	3852.4	4232.9	4582.9	4745.0	4876.4	5110.2
10°	2014.0	2205.2	2490.2	2862.3	3353.9	3900.1	4425.8	4907.1	5117.1	5282.6	5600.1
12.5°	1691.5	1870.7	2169.4	2580.7	3169.6	3862.5	4536.8	5115.4	5362.9	5548.9	5897.1
15°	1464.4	1590.8	1855.4	2299.1	2951.1	3741.4	4543.6	5214.4	5485.7	5680.3	5982.4
17.5°	1338.1	1380.8	1553.2	2012.4	2708.8	3582.7	4480.4	5248.5	5538.7	5719.6	5929.5
20°	1269.9	1276.7	1324.5	1640.3	2398.1	3434.2	4420.7	5282.6	5588.2	5740.1	5803.2
22.5°	1215.2	1215.2	1227.2	1341.5	1997.0	3256.6	4401.9	5342.4	5656.5	5750.4	5620.6
25°	1165.7	1165.7	1169.2	1199.9	1582.2	2985.2	4390.0	5434.5	5750.4	5775.9	5419.2
27.5°	1114.6	1116.2	1116.2	1133.3	1275.0	2616.5	4338.7	5554.1	5863.0	5810.0	5226.3
30°	1063.3	1066.7	1066.7	1078.7	1128.2	2184.8	4238.1	5697.4	6009.8	5854.4	5035.1
32.5°	1012.2	1015.6	1015.6	1025.8	1061.7	1744.3	4111.8	5828.9	6158.2	5873.1	4857.7
35°	959.2	964.3	960.9	974.6	1012.2	1387.6	3951.3	5960.3	6318.7	5932.9	4770.6
37.5°	906.3	909.8	908.0	921.7	964.3	1198.2	3765.2	6059.3	6537.1	6066.1	4874.7
40°	853.4	851.7	851.7	867.0	913.2	1143.6	3531.4	6216.3	6851.2	6299.9	5328.7
42.5°	798.8	798.8	795.4	812.4	868.8	1102.6	3307.9	6497.9	7308.7	6672.0	6134.3
45°	749.3	747.6	740.8	756.1	826.2	1030.9	3229.4	7023.6	7984.5	7274.5	7109.0
47.5°	701.5	699.8	682.8	696.4	774.9	966.1	3522.9	7883.9	8921.6	8160.3	8022.1
50°	658.9	660.5	628.1	640.0	723.6	916.6	4159.6	9000.1	10165.8	9353.4	8887.5
52.5°	619.6	619.6	576.9	583.7	660.5	872.2	4765.4	10210.2	11807.8	11017.6	9896.2
55°	580.4	576.9	529.1	532.5	597.4	809.0	4855.9	11391.3	14047.2	13521.5	11275.3
57.5°	536.0	529.1	484.7	484.7	539.4	762.9	4209.1	12299.4	16825.9	17201.4	13263.8
60°	481.3	476.2	447.2	438.7	493.2	803.9	2969.8	12405.3	18618.1	22094.9	17071.7
62.5°	411.3	418.2	402.8	390.8	448.8	834.7	1759.7	11553.5	18184.5	23651.6	21632.3
65°	324.3	351.6	348.2	339.7	493.2	703.3	1039.5	9918.4	16854.9	22395.3	20702.1
67.5°	276.5	295.3	290.2	290.2	517.2	534.2	653.7	7749.0	15025.2	20905.2	18491.8
70°	235.5	254.3	235.5	235.5	390.8	324.3	452.3	5410.7	13050.4	19256.5	17040.9
72.5°	194.5	213.3	192.9	179.2	312.3	242.4	331.1	3381.3	11176.3	17539.4	16047.6
75°	148.5	170.7	155.3	138.3	206.5	180.9	250.9	1964.5	9259.5	15006.4	14632.6
77.5°	93.9	122.9	116.0	97.3	151.9	131.4	180.9	1169.2	7144.8	11725.9	12586.2
80°	58.0	63.1	64.9	61.4	87.0	88.8	122.9	665.6	4890.1	8172.3	9833.0
82.5°	37.5	37.5	29.0	32.4	42.6	51.2	70.0	250.9	2874.3	4975.5	6844.3
85°	27.3	23.9	15.4	15.4	20.5	25.6	27.3	76.8	1165.7	1964.5	2676.3
87.5°	13.6	12.0	5.1	6.9	10.2	8.5	6.9	3.4	293.6	628.1	440.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P970299
 CATALOG NUMBER: NVN-SB6B-727-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	295°	305°	315°	325°	335°	345°	355°	360°
0°	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7	3430.7
2.5°	3971.8	4024.7	4028.1	4028.1	3982.0	3980.3	3886.5	3876.2
5°	4676.7	4710.8	4719.4	4702.3	4610.1	4541.9	4359.2	4320.0
7.5°	5321.9	5390.2	5390.2	5349.2	5199.0	5059.0	4794.4	4695.5
10°	5837.4	5915.9	5898.8	5815.1	5625.7	5432.8	5112.0	4982.2
12.5°	6088.3	6168.4	6124.1	6028.5	5844.1	5641.1	5303.1	5156.4
15°	6083.2	6060.9	6014.9	6002.9	5914.1	5760.5	5444.8	5284.4
17.5°	5866.4	5678.6	5642.7	5762.2	5874.9	5837.4	5567.7	5417.4
20°	5523.3	5195.6	5163.1	5391.9	5712.7	5876.6	5682.0	5543.8
22.5°	5161.5	4808.2	4733.0	4985.6	5468.7	5888.5	5827.1	5688.9
25°	4818.4	4463.4	4388.2	4623.8	5197.3	5868.1	5984.2	5866.4
27.5°	4531.6	4188.6	4118.6	4354.1	4936.2	5810.0	6141.2	6057.5
30°	4309.7	3992.3	3941.0	4168.1	4710.8	5738.4	6340.9	6294.8
32.5°	4180.1	3947.9	3966.6	4152.7	4589.6	5659.8	6532.0	6554.3
35°	4308.1	4318.3	4482.1	4558.9	4702.3	5647.9	6791.4	6878.5
37.5°	4944.7	5299.7	5639.3	5576.2	5253.6	5786.1	7178.9	7341.0
40°	6028.5	6757.3	7308.7	7068.0	6255.6	6209.4	7737.0	7979.4
42.5°	7353.0	8588.8	9496.8	8851.6	7547.6	6950.2	8534.2	8843.1
45°	8750.9	10846.9	12277.2	10935.6	8925.0	7987.9	9740.9	9983.2
47.5°	10223.9	13591.5	15441.6	13246.7	10201.7	9169.0	11386.2	11442.6
50°	11835.2	16600.6	18667.6	15556.0	11434.1	10522.5	13396.9	13332.1
52.5°	13369.6	19695.1	21825.2	17875.6	12516.2	12202.1	15730.2	15597.0
55°	14834.0	22787.9	25001.6	20104.8	13536.9	14421.0	18502.0	17696.4
57.5°	16532.3	25568.3	28275.3	22344.1	14963.8	17302.1	21601.6	18915.0
60°	19043.1	28727.7	31977.4	25412.9	17677.7	20330.1	22712.8	18683.0
62.5°	22248.5	31632.6	34669.1	28420.4	20403.4	20900.2	21075.9	16894.2
65°	22871.5	32368.3	34821.0	29224.3	20051.8	17728.8	17206.6	13579.5
67.5°	21219.2	31038.6	32697.7	27727.4	17737.3	13700.7	12912.1	9851.8
70°	19365.6	28504.0	28997.4	25182.5	15600.4	10077.1	8720.2	6322.1
72.5°	17466.0	25122.9	24102.2	21869.6	13710.9	7337.7	6289.7	4494.1
75°	15209.6	20676.5	18985.0	18170.9	11352.1	5758.9	4550.4	3101.3
77.5°	12180.0	14554.1	14101.8	14084.7	8530.8	4207.3	3036.5	1944.1
80°	8592.2	9445.6	9215.2	10607.9	5723.0	3051.8	1828.0	1082.1
82.5°	4159.6	5222.9	5361.2	6317.0	2783.8	1795.6	421.6	235.5
85°	1628.3	2519.2	2125.0	2398.1	781.8	500.1	10.2	0.0
87.5°	182.7	291.8	267.9	211.7	95.6	20.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)