

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P971353

Luminaire Tested: **NVN-SB6D-727-U-SLR-HSS**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P971353  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: NVN-SB6D-727-U-SLR-HSS  
Description: NAVION ROADWAY AND AREA HIGH DENSITY LED LUMINAIRE  
(6) 70 CRI, 2700K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 44774 lumens  
Efficiency: N/A  
Efficacy: 101.7 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5  
  
Input Watts (W): 440.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P971353  
 CATALOG NUMBER: NVN-SB6D-727-U-SLR-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 13.8 fc  
 Type IV - Short - N/A

REPORT NUMBER: P971353  
CATALOG NUMBER: NVN-SB6D-727-U-SLR-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral    - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P971353  
 CATALOG NUMBER: NVN-SB6D-727-U-SLR-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	6270.3	0.0	6270.3
	% Fixture	14.0	0.0	14.0
<b>Street Side</b>	Lumens	38503.8	0.0	38503.8
	% Fixture	86.0	0.0	86.0
<b>Total</b>	Lumens	44774.0	0.0	44774.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	610.4	1.4
10°-20°	1829.8	4.1
20°-30°	2695.6	6.0
30°-40°	3463.1	7.7
40°-50°	5600.9	12.5
50°-60°	9821.7	21.9
60°-70°	12289.7	27.4
70°-80°	7181.5	16.0
80°-90°	1281.3	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	44774.0	100.0
0°-180°	44774.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P971353  
 CATALOG NUMBER: NVN-SB6D-727-U-SLR-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3492.2	7.8			
FM (30°-60°)	15692.8	35.0			
FH (60°-80°)	18086.7	40.4			G5
FVH (80°-90°)	1232.1	2.8			G5
BL (0°-30°)	1643.5	3.7	B3/2500		
BM (30°-60°)	3193.0	7.1	B3/5000		
BH (60°-80°)	1384.5	3.1	B3/2500		G3/2500
BVH (80°-90°)	49.2	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G5**

Type IV Short



REPORT NUMBER: P971353  
 CATALOG NUMBER: NVN-SB6D-727-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8
2.5°	7004.8	6884.5	6813.6	6637.8	6461.9	6320.0	6128.8	6002.4	5851.2	5706.3	5576.7
5°	7806.8	7612.5	7378.1	7057.2	6764.2	6465.1	6175.1	5888.2	5585.9	5308.4	5138.7
7.5°	8485.4	8204.7	7791.3	7365.6	6992.4	6631.6	6292.3	5912.9	5545.9	5111.0	4879.6
10°	9003.6	8645.8	8102.9	7544.6	7115.9	6751.9	6421.8	6101.1	5731.0	5206.6	4916.6
12.5°	9318.2	8935.6	8291.0	7637.2	7146.7	6739.6	6483.5	6341.7	6196.7	5675.4	5336.2
15°	9549.5	9136.1	8423.7	7702.0	7075.8	6576.1	6387.9	6529.8	6696.3	6363.2	5971.5
17.5°	9790.1	9355.2	8596.4	7729.6	6884.5	6258.3	6178.2	6545.2	6930.7	6915.4	6526.7
20°	10018.3	9586.5	8747.6	7711.2	6576.1	5872.8	5943.8	6412.6	6859.8	7048.0	6838.3
22.5°	10280.5	9824.0	8892.5	7640.2	6175.1	5511.9	5734.1	6202.9	6594.5	6816.7	6751.9
25°	10601.3	10123.2	9096.1	7535.4	5743.3	5212.7	5521.2	5959.1	6276.9	6431.2	6428.0
27.5°	10946.8	10481.0	9367.5	7479.8	5394.7	5000.0	5280.6	5669.3	5953.0	6060.9	6060.9
30°	11375.6	10897.4	9688.3	7418.1	5166.5	4876.5	5030.8	5333.1	5610.6	5718.6	5718.6
32.5°	11844.4	11360.1	9996.7	7270.1	5027.7	4784.0	4787.1	4978.3	5231.3	5360.7	5379.3
35°	12430.4	11915.3	10326.8	6946.2	4916.6	4676.0	4549.6	4642.1	4851.8	5006.1	5046.2
37.5°	13266.3	12643.2	10730.8	6483.5	4753.1	4509.5	4299.8	4321.3	4481.7	4651.3	4713.1
40°	14419.9	13621.0	11205.8	6002.4	4518.7	4275.1	4025.2	4016.0	4133.2	4299.8	4367.6
42.5°	15980.6	14913.3	11776.5	5542.8	4293.6	3991.2	3735.3	3719.8	3812.4	3957.3	4028.4
45°	18041.0	16566.7	12476.6	5148.0	4117.7	3713.7	3460.8	3454.6	3531.7	3658.2	3732.2
47.5°	20678.2	18864.6	13176.8	4879.6	4025.2	3494.7	3235.6	3247.9	3315.8	3430.0	3482.3
50°	24092.7	21859.6	13389.7	4743.9	4025.2	3377.5	3035.1	3096.8	3152.3	3238.7	3269.5
52.5°	28185.9	24734.3	12686.4	4620.5	4049.9	3393.0	2865.5	2998.1	3038.2	3112.2	3124.6
55°	31979.7	26144.0	10906.6	4450.9	4056.0	3488.5	2720.5	2917.9	2992.0	3019.6	3016.6
57.5°	34182.0	25659.6	8818.5	4164.1	4031.4	3553.3	2628.0	2819.2	2961.1	2979.6	2951.8
60°	33762.6	23960.1	6492.8	3945.0	3849.4	3528.7	2600.2	2668.1	2893.3	2920.9	2883.9
62.5°	30530.0	21110.1	4506.4	3775.4	3448.4	3420.6	2591.0	2430.6	2745.2	2813.0	2760.6
65°	24540.0	16619.0	3183.1	3251.0	3022.7	3186.2	2541.6	2183.8	2566.3	2658.8	2578.6
67.5°	17803.5	11246.0	2297.9	2634.1	2739.0	2806.9	2430.6	2004.9	2362.7	2486.0	2381.2
70°	11424.9	6073.3	1613.1	1739.6	2307.2	2384.3	2239.3	1844.5	2156.1	2297.9	2183.8
72.5°	8121.4	3587.2	1159.8	1218.3	1853.7	1986.3	1971.0	1665.6	1915.4	2088.2	1952.4
75°	5604.5	1977.1	783.4	869.8	1344.8	1613.1	1520.7	1431.2	1622.5	1798.3	1665.6
77.5°	3513.2	885.3	468.8	604.5	882.1	1267.7	1042.5	1107.3	1264.6	1428.1	1289.3
80°	1955.6	342.3	262.2	401.0	481.1	922.3	576.8	712.5	931.5	1048.7	937.7
82.5°	425.7	43.2	117.3	172.7	188.2	536.7	305.3	413.3	586.1	576.8	499.7
85°	0.0	0.0	21.6	24.7	12.3	231.3	111.0	135.7	191.3	178.9	135.7
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	6.1	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P971353  
 CATALOG NUMBER: NVN-SB6D-727-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°	185°
0°	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8
2.5°	5552.0	5400.9	5289.8	5234.4	5188.0	5231.3	5255.9	5255.9	5360.7	5422.5	5447.2
5°	5030.8	4759.3	4552.6	4413.9	4330.6	4358.3	4389.2	4423.1	4555.7	4645.2	4703.8
7.5°	4669.9	4253.4	3938.9	3744.5	3642.7	3658.2	3679.7	3707.5	3837.1	3926.6	4003.6
10°	4602.0	4003.6	3559.5	3303.5	3180.1	3158.5	3146.1	3136.9	3214.0	3281.8	3343.6
12.5°	4879.6	4016.0	3396.0	3084.4	2933.3	2868.6	2794.6	2735.9	2748.2	2791.5	2868.6
15°	5376.2	4173.3	3343.6	2970.3	2782.2	2674.2	2587.8	2516.9	2501.5	2516.9	2529.3
17.5°	5943.8	4386.1	3337.4	2871.6	2637.2	2526.2	2455.2	2390.5	2368.9	2372.0	2387.3
20°	6320.0	4555.7	3318.8	2760.6	2498.4	2399.7	2338.0	2273.2	2251.6	2257.9	2260.9
22.5°	6357.0	4645.2	3291.2	2637.2	2359.7	2276.3	2214.6	2156.1	2152.9	2152.9	2171.5
25°	6156.6	4645.2	3232.5	2526.2	2227.0	2152.9	2097.5	2026.5	2038.8	2045.0	2069.7
27.5°	5845.1	4534.2	3121.4	2436.7	2112.8	2035.8	1980.2	1915.4	1930.9	1940.1	1967.9
30°	5536.6	4392.2	2988.8	2335.0	2004.9	1915.4	1875.3	1819.8	1826.0	1838.3	1869.2
32.5°	5249.7	4241.1	2831.6	2251.6	1897.0	1807.5	1776.6	1714.9	1724.3	1736.6	1770.5
35°	4966.0	4074.6	2646.4	2152.9	1798.3	1708.8	1684.1	1613.1	1619.3	1637.8	1674.8
37.5°	4660.7	3898.8	2495.4	2054.2	1702.6	1610.1	1585.4	1511.4	1517.5	1539.1	1582.3
40°	4339.8	3726.1	2347.2	1949.3	1600.8	1508.3	1486.8	1406.5	1412.7	1437.4	1483.6
42.5°	4016.0	3537.9	2233.2	1813.6	1496.0	1397.3	1375.7	1301.6	1310.9	1338.6	1384.9
45°	3716.8	3312.7	2159.2	1662.6	1397.3	1286.3	1264.6	1196.8	1215.2	1246.1	1292.4
47.5°	3460.8	3081.4	2128.3	1536.1	1292.4	1172.1	1153.6	1098.1	1128.9	1162.9	1199.9
50°	3241.8	2859.3	2088.2	1406.5	1193.7	1073.4	1054.9	1017.8	1058.0	1091.9	1125.9
52.5°	3084.4	2606.4	2001.8	1289.3	1107.3	990.1	983.9	965.4	1002.4	1033.3	1064.2
55°	2948.7	2344.2	1863.0	1187.6	1030.2	919.2	925.4	916.0	946.9	971.6	999.4
57.5°	2825.4	2115.9	1687.3	1107.3	946.9	857.5	876.0	863.7	879.0	894.5	928.4
60°	2677.3	1884.6	1477.4	1017.8	848.2	795.8	817.3	783.4	780.3	786.6	795.8
62.5°	2458.4	1573.1	1258.5	906.8	761.9	728.0	737.2	672.4	623.1	623.1	632.3
65°	2152.9	1264.6	1054.9	783.4	663.2	635.4	629.2	536.7	468.8	462.7	490.5
67.5°	1798.3	1039.5	876.0	660.1	552.2	533.6	539.8	471.9	404.1	397.9	428.8
70°	1465.1	860.6	706.3	527.5	425.7	444.1	471.9	404.1	339.3	330.0	357.8
72.5°	1190.6	684.7	552.2	404.1	314.6	367.1	401.0	330.0	268.3	262.2	286.9
75°	919.2	502.8	394.8	274.5	228.3	283.7	314.6	240.6	191.3	181.9	203.6
77.5°	613.8	311.5	222.1	172.7	135.7	194.3	209.7	126.5	111.0	107.9	123.4
80°	373.2	144.9	95.6	83.2	46.2	70.9	83.2	52.5	58.6	61.7	74.0
82.5°	188.2	40.1	15.4	3.1	0.0	0.0	24.7	12.3	24.7	30.9	46.2
85°	15.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	6.1	15.4	27.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	12.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P971353  
 CATALOG NUMBER: NVN-SB6D-727-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°	285°
0°	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8
2.5°	5619.9	5749.4	5872.8	6070.3	6273.8	6474.3	6677.9	6875.3	6946.2	6998.7	7115.9
5°	4972.2	5215.8	5499.6	5891.3	6310.8	6742.7	7180.6	7581.6	7763.6	7887.0	8164.5
7.5°	4302.8	4620.5	5027.7	5616.8	6273.8	6961.6	7649.5	8281.8	8574.8	8812.3	9234.8
10°	3639.7	3985.1	4500.3	5172.7	6060.9	7048.0	7998.0	8867.8	9247.2	9546.4	10120.1
12.5°	3056.8	3380.6	3920.3	4663.8	5727.8	6980.1	8198.5	9244.2	9691.4	10027.6	10656.8
15°	2646.4	2874.7	3352.8	4154.7	5333.1	6761.1	8210.9	9423.0	9913.5	10265.1	10811.1
17.5°	2418.2	2495.4	2806.9	3636.6	4895.1	6474.3	8096.7	9484.7	10009.1	10336.0	10715.5
20°	2294.9	2307.2	2393.6	2964.2	4333.7	6206.0	7988.7	9546.4	10098.5	10373.1	10487.2
22.5°	2196.2	2196.2	2217.7	2424.4	3608.8	5885.1	7954.8	9654.4	10221.9	10391.6	10157.1
25°	2106.7	2106.7	2112.8	2168.4	2859.3	5394.7	7933.2	9820.9	10391.6	10437.8	9793.2
27.5°	2014.1	2017.2	2017.2	2048.1	2304.1	4728.5	7840.7	10036.8	10595.1	10499.5	9444.7
30°	1921.7	1927.8	1927.8	1949.3	2038.8	3948.1	7658.7	10295.9	10860.4	10579.7	9099.1
32.5°	1829.1	1835.3	1835.3	1853.7	1918.5	3152.3	7430.4	10533.4	11128.7	10613.7	8778.4
35°	1733.5	1742.7	1736.6	1761.3	1829.1	2507.7	7140.6	10770.9	11418.7	10721.6	8621.1
37.5°	1637.8	1644.0	1640.9	1665.6	1742.7	2165.3	6804.4	10949.9	11813.5	10962.2	8809.3
40°	1542.2	1539.1	1539.1	1566.9	1650.1	2066.6	6381.8	11233.6	12381.1	11384.8	9629.7
42.5°	1443.5	1443.5	1437.4	1468.2	1570.0	1992.6	5977.7	11742.6	13207.6	12057.2	11085.6
45°	1354.1	1350.9	1338.6	1366.4	1492.9	1863.0	5835.8	12692.6	14429.1	13146.0	12846.8
47.5°	1267.7	1264.6	1233.8	1258.5	1400.4	1745.8	6366.4	14247.1	16122.5	14746.8	14497.0
50°	1190.6	1193.7	1135.1	1156.7	1307.8	1656.4	7516.8	16264.4	18371.1	16902.9	16060.8
52.5°	1119.7	1119.7	1042.5	1054.9	1193.7	1576.1	8611.8	18451.2	21338.3	19910.2	17883.7
55°	1048.7	1042.5	956.2	962.4	1079.5	1462.1	8775.3	20585.7	25385.1	24435.1	20376.0
57.5°	968.5	956.2	876.0	876.0	974.7	1378.7	7606.3	22226.6	30406.6	31085.3	23969.4
60°	869.8	860.6	808.1	792.7	891.4	1452.7	5367.0	22417.9	33645.3	39928.4	30850.9
62.5°	743.3	755.7	728.0	706.3	811.2	1508.3	3180.1	20878.7	32861.9	42741.4	39092.5
65°	586.1	635.4	629.2	613.8	891.4	1270.8	1878.4	17923.9	30459.1	40471.3	37411.5
67.5°	499.7	533.6	524.4	524.4	934.6	965.4	1181.3	14003.4	27152.6	37778.5	33417.0
70°	425.7	459.6	425.7	425.7	706.3	586.1	817.3	9777.8	23583.8	34799.0	30795.3
72.5°	351.7	385.6	348.5	323.9	564.5	438.0	598.4	6110.3	20197.1	31696.0	29000.1
75°	268.3	308.4	280.6	249.8	373.2	327.0	453.5	3550.2	16733.2	27118.6	26443.2
77.5°	169.6	222.1	209.7	175.8	274.5	237.5	327.0	2112.8	12911.6	21190.2	22744.9
80°	104.9	114.1	117.3	111.0	157.3	160.4	222.1	1202.9	8837.0	14768.4	17769.6
82.5°	67.9	67.9	52.5	58.6	77.1	92.6	126.5	453.5	5194.2	8991.2	12368.7
85°	49.3	43.2	27.8	27.8	37.0	46.2	49.3	138.8	2106.7	3550.2	4836.5
87.5°	24.7	21.6	9.2	12.3	18.6	15.4	12.3	6.1	530.5	1135.1	795.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P971353  
 CATALOG NUMBER: NVN-SB6D-727-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	295°	305°	315°	325°	335°	345°	355°	360°
0°	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8	6199.8
2.5°	7177.6	7273.2	7279.3	7279.3	7196.0	7192.9	7023.3	7004.8
5°	8451.4	8513.1	8528.5	8497.7	8331.1	8207.8	7877.7	7806.8
7.5°	9617.4	9740.8	9740.8	9666.7	9395.3	9142.4	8664.2	8485.4
10°	10548.9	10690.7	10659.9	10508.8	10166.4	9817.9	9238.0	9003.6
12.5°	11002.2	11147.3	11067.0	10894.3	10561.2	10194.1	9583.4	9318.2
15°	10993.0	10952.9	10869.6	10848.1	10687.7	10410.1	9839.5	9549.5
17.5°	10601.3	10262.0	10197.2	10413.2	10616.7	10548.9	10061.5	9790.1
20°	9981.3	9389.1	9330.5	9743.9	10323.7	10619.8	10268.1	10018.3
22.5°	9327.4	8688.9	8553.2	9009.8	9882.6	10641.4	10530.3	10280.5
25°	8707.5	8065.8	7930.1	8355.8	9392.2	10604.3	10814.2	10601.3
27.5°	8189.2	7569.3	7442.8	7868.5	8920.3	10499.5	11097.9	10946.8
30°	7788.3	7214.6	7122.0	7532.2	8513.1	10369.9	11458.8	11375.6
32.5°	7553.8	7134.4	7168.3	7504.5	8294.1	10228.1	11804.2	11844.4
35°	7785.2	7803.7	8099.8	8238.6	8497.7	10206.5	12273.0	12430.4
37.5°	8935.6	9577.3	10191.1	10077.0	9494.0	10456.3	12973.2	13266.3
40°	10894.3	12211.4	13207.6	12772.7	11304.5	11221.3	13981.9	14419.9
42.5°	13287.9	15521.1	17162.0	15996.0	13639.5	12559.9	15422.4	15980.6
45°	15814.0	19601.8	22186.5	19762.2	16128.7	14435.3	17603.0	18041.0
47.5°	18475.9	24561.6	27905.1	23938.6	18435.9	16569.7	20576.5	20678.2
50°	21387.6	29999.5	33734.8	28111.9	20662.9	19015.7	24210.0	24092.7
52.5°	24160.6	35591.6	39441.1	32303.6	22618.4	22050.8	28426.4	28185.9
55°	26807.0	41180.7	45181.3	36331.9	24462.9	26060.6	33435.6	31979.7
57.5°	29876.1	46205.3	51097.3	40378.7	27041.4	31267.2	39037.0	34182.0
60°	34413.4	51914.6	57787.4	45924.6	31945.8	36739.1	41045.0	33762.6
62.5°	40206.0	57164.4	62651.7	51359.4	36871.7	37769.3	38087.0	30530.0
65°	41331.8	58493.8	62926.2	52812.2	36236.3	32038.3	31094.5	24540.0
67.5°	38346.1	56091.0	59089.1	50107.1	32053.8	24759.0	23334.0	17803.5
70°	34996.4	51510.6	52402.0	45508.2	28192.0	18210.7	15758.6	11424.9
72.5°	31563.3	45400.2	43555.7	39521.2	24777.5	13260.1	11366.2	8121.4
75°	27485.7	37365.2	34308.5	32837.2	20514.8	10407.0	8223.2	5604.5
77.5°	22010.7	26301.2	25483.9	25453.0	15416.1	7603.2	5487.2	3513.2
80°	15527.2	17069.4	16653.1	19170.0	10342.2	5515.0	3303.5	1955.6
82.5°	7516.8	9438.5	9688.3	11415.6	5030.8	3244.8	761.9	425.7
85°	2942.6	4552.6	3840.2	4333.7	1412.7	903.7	18.6	0.0
87.5°	330.0	527.5	484.2	382.4	172.7	37.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)