

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P969308

Luminaire Tested: **NVN-SB5D-735-U-SLR**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P969308  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: NVN-SB5D-735-U-SLR  
Description: NAVION ROADWAY AND AREA HIGH DENSITY LED LUMINAIRE  
(5) 70 CRI, 3500K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR RIGHT OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 52499.5 lumens  
Efficiency: N/A  
Efficacy: 143.9 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B4 - U0 - G5  
  
Input Watts (W): 364.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P969308  
 CATALOG NUMBER: NVN-SB5D-735-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 14.3 fc  
 Type IV - Short - N/A

REPORT NUMBER: P969308  
CATALOG NUMBER: NVN-SB5D-735-U-SLR

### Luminous Intensity Polar Plot



REPORT NUMBER: P969308

CATALOG NUMBER: NVN-SB5D-735-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	13342.7	0.0	13342.7
	% Fixture	25.4	0.0	25.4
<b>Street Side</b>	Lumens	39156.8	0.0	39156.8
	% Fixture	74.6	0.0	74.6
<b>Total</b>	Lumens	52499.5	0.0	52499.5
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	716.1	1.4
10°-20°	2248.1	4.3
20°-30°	3472.5	6.6
30°-40°	4400.5	8.4
40°-50°	6637.1	12.6
50°-60°	10723.3	20.4
60°-70°	13368.3	25.5
70°-80°	8766.3	16.7
80°-90°	2167.2	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	52499.5	100.0
0°-180°	52499.5	100.0

**Coefficient of Utilization**



REPORT NUMBER: P969308


CATALOG NUMBER: NVN-SB5D-735-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3531.2	6.7			
FM (30°-60°)	15313.0	29.2			
FH (60°-80°)	18527.3	35.3			G5
FVH (80°-90°)	1785.3	3.4			G5
BL (0°-30°)	2905.5	5.5	B4/5000		
BM (30°-60°)	6448.0	12.3	B4/8500		
BH (60°-80°)	3607.3	6.9	B4/5000		G4/5000
BVH (80°-90°)	381.9	0.7			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B4-U0-G5**

Type IV Short



REPORT NUMBER: P969308

CATALOG NUMBER: NVN-SB5D-735-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2
2.5°	7763.5	7703.9	7644.3	7580.9	7517.8	7454.0	7390.4	7329.4	7268.5	7209.4	7143.7
5°	8348.0	8216.4	8084.8	7953.5	7822.5	7690.4	7558.5	7435.2	7311.9	7195.6	7080.6
7.5°	8935.2	8718.0	8501.1	8300.7	8100.1	7904.8	7709.4	7537.4	7365.4	7206.7	7057.9
10°	9385.4	9110.9	8836.3	8571.3	8306.4	8069.3	7831.9	7628.6	7424.7	7228.8	7069.0
12.5°	9661.0	9359.4	9058.0	8757.7	8457.4	8177.7	7897.8	7667.6	7437.4	7231.6	7082.9
15°	9828.6	9514.3	9199.8	8874.0	8548.3	8226.1	7903.9	7637.5	7371.0	7142.9	7023.8
17.5°	9922.8	9603.9	9285.2	8929.7	8574.3	8200.3	7826.4	7505.9	7185.4	6917.2	6843.7
20°	10026.8	9695.4	9363.8	8973.3	8582.6	8129.4	7676.2	7278.9	6881.7	6569.5	6550.2
22.5°	10147.2	9808.7	9469.9	9032.0	8593.7	8042.5	7491.2	7012.7	6534.4	6178.9	6216.8
25°	10302.4	9970.5	9638.9	9138.3	8637.5	7956.6	7276.0	6715.5	6155.3	5791.0	5893.5
27.5°	10512.9	10196.5	9879.9	9304.5	8728.9	7899.2	7069.5	6443.8	5818.0	5486.4	5611.1
30°	10796.8	10491.0	10185.4	9519.8	8854.1	7872.3	6890.0	6216.6	5543.2	5264.7	5362.6
32.5°	11132.0	10829.2	10526.7	9744.5	8962.1	7839.1	6715.5	6020.7	5325.7	5101.3	5144.8
35°	11539.2	11249.5	10959.4	10000.4	9041.3	7776.5	6512.1	5828.3	5144.3	4957.3	4939.3
37.5°	12224.9	11855.4	11485.7	10287.1	9088.5	7669.3	6250.1	5601.6	4953.1	4789.6	4723.7
40°	13260.9	12722.4	12183.9	10651.1	9118.1	7521.7	5925.4	5331.2	4737.0	4588.8	4487.8
42.5°	14635.0	13857.6	13080.3	11127.3	9174.4	7369.2	5564.7	5032.9	4501.0	4364.4	4237.0
45°	16331.7	15283.2	14234.7	11754.0	9273.3	7227.7	5182.5	4716.0	4249.4	4111.0	3987.7
47.5°	18453.7	16978.0	15502.0	12421.6	9341.1	7110.8	4880.5	4465.3	4050.0	3871.3	3765.2
50°	21234.9	19010.2	16785.2	13041.0	9296.8	6983.4	4670.0	4298.7	3927.6	3692.7	3569.4
52.5°	24427.6	21144.9	17862.3	13443.2	9023.9	6768.2	4512.7	4189.1	3865.8	3595.7	3423.4
55°	27826.6	23037.5	18248.7	13354.5	8460.1	6411.4	4362.5	4109.6	3856.7	3605.4	3345.8
57.5°	30918.2	24378.8	17839.5	12730.7	7622.2	5908.3	4194.1	4015.4	3836.7	3615.1	3299.3
60°	32786.7	24714.0	16641.1	11569.7	6498.3	5255.1	4011.7	3871.3	3730.9	3584.6	3255.5
62.5°	31837.8	23302.7	14767.4	9999.9	5232.3	4473.3	3714.3	3620.9	3527.8	3509.8	3204.6
65°	29938.9	21305.5	12672.3	8398.1	4124.3	3770.0	3415.6	3371.6	3327.6	3329.8	3097.0
67.5°	27394.5	18929.0	10463.6	6829.1	3194.6	3094.1	2993.2	3017.8	3042.2	3036.2	2905.4
70°	24337.6	16335.8	8334.2	5376.9	2419.7	2448.6	2477.1	2591.2	2705.1	2705.1	2662.1
72.5°	20694.8	13524.7	6354.8	4110.7	1866.5	1953.2	2040.3	2202.0	2363.5	2390.7	2391.2
75°	16086.6	10302.1	4517.6	2983.5	1449.4	1528.1	1606.7	1787.9	1969.0	2094.3	2083.7
77.5°	11493.5	7210.6	2927.5	2021.7	1115.8	1169.3	1223.0	1398.9	1574.8	1781.2	1775.7
80°	7522.5	4645.6	1768.7	1302.6	836.6	858.7	880.9	1029.9	1178.8	1425.3	1424.4
82.5°	4372.8	2688.8	1005.0	801.1	597.8	601.7	606.1	715.9	825.5	1036.1	1047.7
85°	1923.9	1209.5	495.3	428.2	361.5	359.6	357.3	437.7	518.0	674.6	689.8
87.5°	595.6	396.2	196.7	177.5	158.5	156.5	154.6	187.3	220.3	285.4	304.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P969308

CATALOG NUMBER: NVN-SB5D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2
2.5°	7090.6	7037.6	6989.8	6942.1	6900.3	6858.5	6816.4	6774.5	6742.1	6709.4	6683.1
5°	6980.4	6879.8	6795.5	6711.6	6637.4	6563.2	6495.8	6428.3	6376.4	6324.4	6288.1
7.5°	6924.4	6791.1	6680.3	6569.5	6476.2	6382.6	6300.0	6217.8	6155.9	6094.4	6051.2
10°	6928.3	6787.6	6676.7	6565.9	6465.4	6364.5	6271.8	6178.9	6105.2	6031.3	5983.0
12.5°	6967.6	6852.9	6779.2	6706.1	6626.8	6548.2	6452.1	6356.2	6262.0	6167.8	6105.5
15°	6968.7	6913.8	6923.9	6933.8	6913.3	6892.8	6809.4	6726.0	6592.0	6457.9	6363.1
17.5°	6864.0	6883.9	7004.7	7125.5	7189.8	7253.7	7186.5	7119.4	6941.8	6764.3	6624.7
20°	6644.4	6738.5	6948.2	7158.2	7292.6	7426.9	7395.9	7364.5	7161.5	6958.7	6787.6
22.5°	6356.2	6495.5	6734.9	6974.8	7149.6	7324.4	7343.2	7361.8	7167.9	6974.0	6797.8
25°	6054.3	6215.0	6430.1	6645.7	6817.7	6989.8	7054.0	7118.0	6959.0	6800.3	6643.4
27.5°	5766.1	5921.3	6098.3	6275.0	6413.0	6551.0	6622.4	6694.2	6580.9	6467.9	6346.3
30°	5485.5	5609.1	5755.9	5902.8	6017.2	6131.9	6190.0	6248.2	6162.0	6075.6	5988.6
32.5°	5217.7	5290.5	5407.7	5525.2	5634.8	5744.8	5809.4	5874.2	5794.9	5715.5	5645.9
35°	4959.2	4979.4	5068.9	5158.1	5266.7	5375.6	5453.1	5530.7	5474.2	5417.9	5353.7
37.5°	4701.6	4679.4	4743.7	4807.7	4916.0	5024.5	5120.4	5216.3	5190.2	5164.2	5105.2
40°	4437.5	4387.4	4433.7	4480.0	4584.7	4689.4	4799.7	4910.2	4916.5	4922.7	4872.5
42.5°	4170.5	4104.0	4141.7	4179.6	4278.9	4378.3	4497.4	4616.5	4648.4	4680.3	4637.8
45°	3922.9	3858.3	3889.9	3922.1	4016.3	4110.5	4234.0	4357.5	4403.2	4448.9	4410.7
47.5°	3710.9	3656.7	3686.6	3716.2	3808.5	3900.4	4022.3	4144.2	4196.9	4249.4	4222.9
50°	3521.2	3473.3	3519.8	3566.6	3653.6	3740.3	3849.5	3958.7	4026.2	4093.7	4092.1
52.5°	3375.7	3328.4	3398.5	3468.3	3548.0	3627.6	3729.3	3831.1	3911.2	3991.2	4005.7
55°	3270.5	3195.4	3294.9	3394.1	3479.9	3565.8	3654.9	3743.9	3828.7	3913.8	3933.6
57.5°	3189.6	3079.9	3186.8	3293.7	3394.6	3495.5	3583.5	3671.9	3757.4	3842.8	3863.0
60°	3113.4	2971.1	3065.0	3158.5	3274.4	3390.2	3479.7	3569.4	3655.3	3741.1	3763.3
62.5°	3026.7	2849.2	2908.7	2968.3	3103.2	3238.4	3333.9	3429.5	3508.2	3586.9	3608.2
65°	2908.1	2718.9	2742.0	2764.6	2909.3	3054.1	3145.5	3237.0	3306.2	3375.5	3397.4
67.5°	2748.0	2590.7	2583.5	2576.2	2709.8	2843.6	2930.3	3016.8	3076.5	3136.4	3157.7
70°	2550.2	2438.4	2413.4	2388.5	2505.9	2623.4	2698.2	2772.9	2827.0	2881.0	2901.5
72.5°	2314.4	2237.8	2201.2	2164.9	2257.5	2349.7	2417.3	2484.9	2537.8	2590.7	2615.1
75°	2024.8	1965.4	1930.6	1895.3	1964.1	2032.8	2094.0	2155.2	2203.4	2251.6	2277.1
77.5°	1728.4	1681.0	1645.5	1610.1	1666.0	1721.7	1774.3	1827.0	1877.6	1928.0	1951.9
80°	1384.8	1344.9	1315.3	1285.4	1331.9	1378.2	1422.5	1466.8	1505.3	1543.5	1575.1
82.5°	1028.3	1008.9	987.9	966.8	962.9	959.1	943.5	928.0	1010.0	1092.0	1145.7
85°	669.0	648.2	624.6	601.2	581.2	561.0	518.0	475.1	551.9	628.8	695.4
87.5°	296.4	288.1	283.6	279.2	278.4	277.6	244.9	212.0	244.1	276.4	303.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P969308  
 CATALOG NUMBER: NVN-SB5D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2
2.5°	6656.8	6636.3	6615.8	6596.9	6577.8	6554.3	6577.8	6596.9	6615.8	6636.3	6656.8
5°	6251.8	6226.1	6200.2	6180.5	6160.9	6141.5	6160.9	6180.5	6200.2	6226.1	6251.8
7.5°	6008.0	5978.3	5949.0	5931.3	5913.8	5900.5	5913.8	5931.3	5949.0	5978.3	6008.0
10°	5934.3	5906.4	5878.4	5863.4	5848.4	5842.3	5848.4	5863.4	5878.4	5906.4	5934.3
12.5°	6043.2	6011.8	5980.9	5968.1	5955.4	5953.2	5955.4	5968.1	5980.9	6011.8	6043.2
15°	6268.4	6224.9	6181.7	6165.1	6148.5	6147.0	6148.5	6165.1	6181.7	6224.9	6268.4
17.5°	6485.1	6420.8	6356.2	6335.1	6313.8	6310.5	6313.8	6335.1	6356.2	6420.8	6485.1
20°	6616.6	6534.4	6451.8	6425.5	6399.2	6390.9	6399.2	6425.5	6451.8	6534.4	6616.6
22.5°	6621.3	6534.6	6447.7	6418.5	6389.4	6377.0	6389.4	6418.5	6447.7	6534.6	6621.3
25°	6487.2	6411.9	6336.9	6309.4	6282.2	6266.1	6282.2	6309.4	6336.9	6411.9	6487.2
27.5°	6224.6	6174.2	6123.6	6111.0	6098.5	6094.4	6098.5	6111.0	6123.6	6174.2	6224.6
30°	5901.0	5875.3	5849.3	5849.3	5849.3	5853.5	5849.3	5849.3	5849.3	5875.3	5901.0
32.5°	5576.4	5559.5	5542.6	5544.8	5547.3	5551.5	5547.3	5544.8	5542.6	5559.5	5576.4
35°	5289.7	5263.9	5238.5	5232.9	5227.4	5224.6	5227.4	5232.9	5238.5	5263.9	5289.7
37.5°	5045.9	4999.1	4952.6	4927.9	4903.3	4889.4	4903.3	4927.9	4952.6	4999.1	5045.9
40°	4822.3	4754.3	4686.6	4640.6	4595.2	4568.0	4595.2	4640.6	4686.6	4754.3	4822.3
42.5°	4595.8	4511.2	4426.8	4360.0	4293.2	4249.4	4293.2	4360.0	4426.8	4511.2	4595.8
45°	4372.8	4276.1	4179.6	4101.2	4022.9	3972.5	4022.9	4101.2	4179.6	4276.1	4372.8
47.5°	4196.2	4110.5	4024.6	3952.0	3879.6	3831.1	3879.6	3952.0	4024.6	4110.5	4196.2
50°	4091.0	4022.3	3953.6	3886.6	3819.6	3773.0	3819.6	3886.6	3953.6	4022.3	4091.0
52.5°	4020.2	3964.2	3908.2	3848.1	3788.2	3745.3	3788.2	3848.1	3908.2	3964.2	4020.2
55°	3953.6	3904.8	3856.2	3803.5	3750.9	3712.0	3750.9	3803.5	3856.2	3904.8	3953.6
57.5°	3883.2	3833.9	3784.6	3732.5	3680.2	3640.1	3680.2	3732.5	3784.6	3833.9	3883.2
60°	3785.4	3737.3	3689.4	3635.6	3581.9	3540.4	3581.9	3635.6	3689.4	3737.3	3785.4
62.5°	3629.5	3586.1	3542.5	3486.0	3429.5	3379.6	3429.5	3486.0	3542.5	3586.1	3629.5
65°	3419.0	3377.2	3335.4	3280.5	3225.9	3182.9	3225.9	3280.5	3335.4	3377.2	3419.0
67.5°	3178.8	3140.3	3102.1	3051.1	3000.1	2961.3	3000.1	3051.1	3102.1	3140.3	3178.8
70°	2922.0	2890.7	2859.4	2810.7	2761.9	2717.6	2761.9	2810.7	2859.4	2890.7	2922.0
72.5°	2639.5	2613.4	2587.4	2540.9	2494.5	2451.6	2494.5	2540.9	2587.4	2613.4	2639.5
75°	2302.6	2289.8	2277.1	2238.1	2198.9	2157.9	2198.9	2238.1	2277.1	2289.8	2302.6
77.5°	1975.7	1958.0	1939.7	1900.4	1861.0	1828.3	1861.0	1900.4	1939.7	1958.0	1975.7
80°	1606.7	1599.0	1591.5	1538.5	1485.4	1423.9	1485.4	1538.5	1591.5	1599.0	1606.7
82.5°	1199.5	1196.2	1192.6	1148.0	1103.1	1063.7	1103.1	1148.0	1192.6	1196.2	1199.5
85°	761.8	756.2	750.7	715.9	680.9	645.4	680.9	715.9	750.7	756.2	761.8
87.5°	330.3	323.6	316.3	298.6	280.3	263.1	280.3	298.6	316.3	323.6	330.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P969308

CATALOG NUMBER: NVN-SB5D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2
2.5°	6683.1	6709.4	6742.1	6774.5	6816.4	6858.5	6900.3	6942.1	6989.8	7037.6	7090.6
5°	6288.1	6324.4	6376.4	6428.3	6495.8	6563.2	6637.4	6711.6	6795.5	6879.8	6980.4
7.5°	6051.2	6094.4	6155.9	6217.8	6300.0	6382.6	6476.2	6569.5	6680.3	6791.1	6924.4
10°	5983.0	6031.3	6105.2	6178.9	6271.8	6364.5	6465.4	6565.9	6676.7	6787.6	6928.3
12.5°	6105.5	6167.8	6262.0	6356.2	6452.1	6548.2	6626.8	6706.1	6779.2	6852.9	6967.6
15°	6363.1	6457.9	6592.0	6726.0	6809.4	6892.8	6913.3	6933.8	6923.9	6913.8	6968.7
17.5°	6624.7	6764.3	6941.8	7119.4	7186.5	7253.7	7189.8	7125.5	7004.7	6883.9	6864.0
20°	6787.6	6958.7	7161.5	7364.5	7395.9	7426.9	7292.6	7158.2	6948.2	6738.5	6644.4
22.5°	6797.8	6974.0	7167.9	7361.8	7343.2	7324.4	7149.6	6974.8	6734.9	6495.5	6356.2
25°	6643.4	6800.3	6959.0	7118.0	7054.0	6989.8	6817.7	6645.7	6430.1	6215.0	6054.3
27.5°	6346.3	6467.9	6580.9	6694.2	6622.4	6551.0	6413.0	6275.0	6098.3	5921.3	5766.1
30°	5988.6	6075.6	6162.0	6248.2	6190.0	6131.9	6017.2	5902.8	5755.9	5609.1	5485.5
32.5°	5645.9	5715.5	5794.9	5874.2	5809.4	5744.8	5634.8	5525.2	5407.7	5290.5	5217.7
35°	5353.7	5417.9	5474.2	5530.7	5453.1	5375.6	5266.7	5158.1	5068.9	4979.4	4959.2
37.5°	5105.2	5164.2	5190.2	5216.3	5120.4	5024.5	4916.0	4807.7	4743.7	4679.4	4701.6
40°	4872.5	4922.7	4916.5	4910.2	4799.7	4689.4	4584.7	4480.0	4433.7	4387.4	4437.5
42.5°	4637.8	4680.3	4648.4	4616.5	4497.4	4378.3	4278.9	4179.6	4141.7	4104.0	4170.5
45°	4410.7	4448.9	4403.2	4357.5	4234.0	4110.5	4016.3	3922.1	3889.9	3858.3	3922.9
47.5°	4222.9	4249.4	4196.9	4144.2	4022.3	3900.4	3808.5	3716.2	3686.6	3656.7	3710.9
50°	4092.1	4093.7	4026.2	3958.7	3849.5	3740.3	3653.6	3566.6	3519.8	3473.3	3521.2
52.5°	4005.7	3991.2	3911.2	3831.1	3729.3	3627.6	3548.0	3468.3	3398.5	3328.4	3375.7
55°	3933.6	3913.8	3828.7	3743.9	3654.9	3565.8	3479.9	3394.1	3294.9	3195.4	3270.5
57.5°	3863.0	3842.8	3757.4	3671.9	3583.5	3495.5	3394.6	3293.7	3186.8	3079.9	3189.6
60°	3763.3	3741.1	3655.3	3569.4	3479.7	3390.2	3274.4	3158.5	3065.0	2971.1	3113.4
62.5°	3608.2	3586.9	3508.2	3429.5	3333.9	3238.4	3103.2	2968.3	2908.7	2849.2	3026.7
65°	3397.4	3375.5	3306.2	3237.0	3145.5	3054.1	2909.3	2764.6	2742.0	2718.9	2908.1
67.5°	3157.7	3136.4	3076.5	3016.8	2930.3	2843.6	2709.8	2576.2	2583.5	2590.7	2748.0
70°	2901.5	2881.0	2827.0	2772.9	2698.2	2623.4	2505.9	2388.5	2413.4	2438.4	2550.2
72.5°	2615.1	2590.7	2537.8	2484.9	2417.3	2349.7	2257.5	2164.9	2201.2	2237.8	2314.4
75°	2277.1	2251.6	2203.4	2155.2	2094.0	2032.8	1964.1	1895.3	1930.6	1965.4	2024.8
77.5°	1951.9	1928.0	1877.6	1827.0	1774.3	1721.7	1666.0	1610.1	1645.5	1681.0	1728.4
80°	1575.1	1543.5	1505.3	1466.8	1422.5	1378.2	1331.9	1285.4	1315.3	1344.9	1384.8
82.5°	1145.7	1092.0	1010.0	928.0	943.5	959.1	962.9	966.8	987.9	1008.9	1028.3
85°	695.4	628.8	551.9	475.1	518.0	561.0	581.2	601.2	624.6	648.2	669.0
87.5°	303.3	276.4	244.1	212.0	244.9	277.6	278.4	279.2	283.6	288.1	296.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P969308  
 CATALOG NUMBER: NVN-SB5D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2
2.5°	7143.7	7209.4	7268.5	7329.4	7390.4	7454.0	7517.8	7580.9	7644.3	7703.9	7763.5
5°	7080.6	7195.6	7311.9	7435.2	7558.5	7690.4	7822.5	7953.5	8084.8	8216.4	8348.0
7.5°	7057.9	7206.7	7365.4	7537.4	7709.4	7904.8	8100.1	8300.7	8501.1	8718.0	8935.2
10°	7069.0	7228.8	7424.7	7628.6	7831.9	8069.3	8306.4	8571.3	8836.3	9110.9	9385.4
12.5°	7082.9	7231.6	7437.4	7667.6	7897.8	8177.7	8457.4	8757.7	9058.0	9359.4	9661.0
15°	7023.8	7142.9	7371.0	7637.5	7903.9	8226.1	8548.3	8874.0	9199.8	9514.3	9828.6
17.5°	6843.7	6917.2	7185.4	7505.9	7826.4	8200.3	8574.3	8929.7	9285.2	9603.9	9922.8
20°	6550.2	6569.5	6881.7	7278.9	7676.2	8129.4	8582.6	8973.3	9363.8	9695.4	10026.8
22.5°	6216.8	6178.9	6534.4	7012.7	7491.2	8042.5	8593.7	9032.0	9469.9	9808.7	10147.2
25°	5893.5	5791.0	6155.3	6715.5	7276.0	7956.6	8637.5	9138.3	9638.9	9970.5	10302.4
27.5°	5611.1	5486.4	5818.0	6443.8	7069.5	7899.2	8728.9	9304.5	9879.9	10196.5	10512.9
30°	5362.6	5264.7	5543.2	6216.6	6890.0	7872.3	8854.1	9519.8	10185.4	10491.0	10796.8
32.5°	5144.8	5101.3	5325.7	6020.7	6715.5	7839.1	8962.1	9744.5	10526.7	10829.2	11132.0
35°	4939.3	4957.3	5144.3	5828.3	6512.1	7776.5	9041.3	10000.4	10959.4	11249.5	11539.2
37.5°	4723.7	4789.6	4953.1	5601.6	6250.1	7669.3	9088.5	10287.1	11485.7	11855.4	12224.9
40°	4487.8	4588.8	4737.0	5331.2	5925.4	7521.7	9118.1	10651.1	12183.9	12722.4	13260.9
42.5°	4237.0	4364.4	4501.0	5032.9	5564.7	7369.2	9174.4	11127.3	13080.3	13857.6	14635.0
45°	3987.7	4111.0	4249.4	4716.0	5182.5	7227.7	9273.3	11754.0	14234.7	15283.2	16331.7
47.5°	3765.2	3871.3	4050.0	4465.3	4880.5	7110.8	9341.1	12421.6	15502.0	16978.0	18453.7
50°	3569.4	3692.7	3927.6	4298.7	4670.0	6983.4	9296.8	13041.0	16785.2	19010.2	21234.9
52.5°	3423.4	3595.7	3865.8	4189.1	4512.7	6768.2	9023.9	13443.2	17862.3	21144.9	24427.6
55°	3345.8	3605.4	3856.7	4109.6	4362.5	6411.4	8460.1	13354.5	18248.7	23037.5	27826.6
57.5°	3299.3	3615.1	3836.7	4015.4	4194.1	5908.3	7622.2	12730.7	17839.5	24378.8	30918.2
60°	3255.5	3584.6	3730.9	3871.3	4011.7	5255.1	6498.3	11569.7	16641.1	24714.0	32786.7
62.5°	3204.6	3509.8	3527.8	3620.9	3714.3	4473.3	5232.3	9999.9	14767.4	23302.7	31837.8
65°	3097.0	3329.8	3327.6	3371.6	3415.6	3770.0	4124.3	8398.1	12672.3	21305.5	29938.9
67.5°	2905.4	3036.2	3042.2	3017.8	2993.2	3094.1	3194.6	6829.1	10463.6	18929.0	27394.5
70°	2662.1	2705.1	2705.1	2591.2	2477.1	2448.6	2419.7	5376.9	8334.2	16335.8	24337.6
72.5°	2391.2	2390.7	2363.5	2202.0	2040.3	1953.2	1866.5	4110.7	6354.8	13524.7	20694.8
75°	2083.7	2094.3	1969.0	1787.9	1606.7	1528.1	1449.4	2983.5	4517.6	10302.1	16086.6
77.5°	1775.7	1781.2	1574.8	1398.9	1223.0	1169.3	1115.8	2021.7	2927.5	7210.6	11493.5
80°	1424.4	1425.3	1178.8	1029.9	880.9	858.7	836.6	1302.6	1768.7	4645.6	7522.5
82.5°	1047.7	1036.1	825.5	715.9	606.1	601.7	597.8	801.1	1005.0	2688.8	4372.8
85°	689.8	674.6	518.0	437.7	357.3	359.6	361.5	428.2	495.3	1209.5	1923.9
87.5°	304.7	285.4	220.3	187.3	154.6	156.5	158.5	177.5	196.7	396.2	595.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P969308  
 CATALOG NUMBER: NVN-SB5D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2
2.5°	7792.9	7822.5	7864.3	7906.1	7931.0	7956.0	7968.5	7981.0	7975.4	7981.0	7968.5
5°	8450.7	8553.8	8655.7	8758.0	8813.4	8868.8	8902.3	8936.1	8961.6	8936.1	8902.3
7.5°	9102.6	9269.6	9420.1	9570.4	9661.0	9751.6	9800.6	9849.4	9873.0	9849.4	9800.6
10°	9583.2	9781.0	9957.5	10134.0	10240.9	10347.3	10394.8	10442.3	10460.2	10442.3	10394.8
12.5°	9875.5	10089.6	10249.2	10408.2	10485.8	10563.3	10589.4	10615.4	10618.2	10615.4	10589.4
15°	10013.7	10198.4	10298.5	10398.7	10401.5	10404.3	10376.6	10348.9	10316.2	10348.9	10376.6
17.5°	10047.8	10172.7	10174.7	10176.3	10064.2	9951.9	9849.1	9746.1	9673.5	9746.1	9849.1
20°	10070.2	10114.0	9982.4	9850.9	9603.1	9355.5	9175.2	8994.8	8884.0	8994.8	9175.2
22.5°	10090.2	10033.1	9760.5	9487.9	9123.6	8759.3	8533.8	8308.3	8186.0	8308.3	8533.8
25°	10122.3	9942.2	9528.4	9114.5	8672.1	8229.7	7992.5	7756.0	7640.2	7756.0	7992.5
27.5°	10191.0	9868.8	9320.6	8772.7	8282.3	7792.0	7558.8	7325.8	7216.4	7325.8	7558.8
30°	10316.7	9836.9	9162.2	8487.3	7976.6	7465.7	7249.3	7032.9	6931.0	7032.9	7249.3
32.5°	10474.7	9817.6	9054.1	8290.6	7810.6	7330.5	7160.6	6990.6	6917.2	6990.6	7160.6
35°	10734.8	9930.6	9135.0	8339.7	8006.2	7672.8	7633.3	7593.6	7587.6	7593.6	7633.3
37.5°	11278.6	10332.3	9609.3	8886.2	8864.6	8843.0	9024.2	9205.3	9299.5	9205.3	9024.2
40°	12231.8	11202.6	10665.0	10127.3	10506.8	10886.3	11326.8	11767.2	11986.7	11767.2	11326.8
42.5°	13613.8	12592.7	12283.1	11973.3	12801.1	13628.8	14430.0	15231.1	15701.5	15231.1	14430.0
45°	15414.5	14497.0	14360.5	14223.6	15549.7	16876.0	18192.4	19509.1	20308.3	19509.1	18192.4
47.5°	17561.4	16668.9	16641.1	16613.4	18526.5	20439.0	22366.3	24293.2	25424.8	24293.2	22366.3
50°	20132.6	19030.7	19035.4	19040.1	21505.6	23971.1	26514.9	29058.7	30596.8	29058.7	26514.9
52.5°	23092.9	21758.5	21623.6	21488.4	24433.4	27378.4	30525.9	33673.1	35516.7	33673.1	30525.9
55°	26508.0	25189.4	24663.3	24137.3	27415.0	30692.4	34444.6	38196.8	40389.4	38196.8	34444.6
57.5°	30200.1	29481.8	28426.6	27371.7	30681.3	33990.8	38240.9	42490.7	45209.6	42490.7	38240.9
60°	33902.0	35017.5	33707.2	32396.9	35528.9	38660.8	43211.1	47761.5	50700.1	47761.5	43211.1
62.5°	34885.4	37932.9	37785.2	37637.3	40506.4	43375.7	47704.9	52033.9	54750.2	52033.9	47704.9
65°	32799.1	35659.3	36225.3	36790.9	40437.1	44083.5	48281.5	52479.2	54791.7	52479.2	48281.5
67.5°	30114.8	32835.2	33100.5	33365.6	37164.7	40963.4	45179.4	49395.4	51207.1	49395.4	45179.4
70°	27296.4	30255.5	30374.1	30492.9	33890.3	37287.3	40915.5	44543.3	45550.3	44543.3	40915.5
72.5°	24090.2	27485.9	27571.2	27656.2	30314.3	32972.3	35689.6	38406.5	38508.5	38406.5	35689.6
75°	19600.8	23115.1	23430.6	23746.1	25814.1	27882.0	29794.8	31707.7	31195.2	31707.7	29794.8
77.5°	14774.0	18054.8	18506.3	18957.8	20529.9	22102.0	23458.6	24815.5	23934.5	24815.5	23458.6
80°	10282.4	13042.1	13603.3	14164.6	15351.8	16538.6	17251.2	17963.3	16546.4	17963.3	17251.2
82.5°	6259.6	8146.6	8773.5	9400.7	10217.9	11035.0	11332.3	11629.2	10515.7	11629.2	11332.3
85°	2925.4	3926.8	4460.0	4993.3	5664.8	6336.0	6504.6	6673.4	5781.4	6673.4	6504.6
87.5°	932.1	1268.7	1566.3	1863.8	2199.5	2535.2	2549.7	2563.8	2152.4	2563.8	2549.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P969308  
 CATALOG NUMBER: NVN-SB5D-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2	7219.2
2.5°	7956.0	7931.0	7906.1	7864.3	7822.5	7792.9	7763.5
5°	8868.8	8813.4	8758.0	8655.7	8553.8	8450.7	8348.0
7.5°	9751.6	9661.0	9570.4	9420.1	9269.6	9102.6	8935.2
10°	10347.3	10240.9	10134.0	9957.5	9781.0	9583.2	9385.4
12.5°	10563.3	10485.8	10408.2	10249.2	10089.6	9875.5	9661.0
15°	10404.3	10401.5	10398.7	10298.5	10198.4	10013.7	9828.6
17.5°	9951.9	10064.2	10176.3	10174.7	10172.7	10047.8	9922.8
20°	9355.5	9603.1	9850.9	9982.4	10114.0	10070.2	10026.8
22.5°	8759.3	9123.6	9487.9	9760.5	10033.1	10090.2	10147.2
25°	8229.7	8672.1	9114.5	9528.4	9942.2	10122.3	10302.4
27.5°	7792.0	8282.3	8772.7	9320.6	9868.8	10191.0	10512.9
30°	7465.7	7976.6	8487.3	9162.2	9836.9	10316.7	10796.8
32.5°	7330.5	7810.6	8290.6	9054.1	9817.6	10474.7	11132.0
35°	7672.8	8006.2	8339.7	9135.0	9930.6	10734.8	11539.2
37.5°	8843.0	8864.6	8886.2	9609.3	10332.3	11278.6	12224.9
40°	10886.3	10506.8	10127.3	10665.0	11202.6	12231.8	13260.9
42.5°	13628.8	12801.1	11973.3	12283.1	12592.7	13613.8	14635.0
45°	16876.0	15549.7	14223.6	14360.5	14497.0	15414.5	16331.7
47.5°	20439.0	18526.5	16613.4	16641.1	16668.9	17561.4	18453.7
50°	23971.1	21505.6	19040.1	19035.4	19030.7	20132.6	21234.9
52.5°	27378.4	24433.4	21488.4	21623.6	21758.5	23092.9	24427.6
55°	30692.4	27415.0	24137.3	24663.3	25189.4	26508.0	27826.6
57.5°	33990.8	30681.3	27371.7	28426.6	29481.8	30200.1	30918.2
60°	38660.8	35528.9	32396.9	33707.2	35017.5	33902.0	32786.7
62.5°	43375.7	40506.4	37637.3	37785.2	37932.9	34885.4	31837.8
65°	44083.5	40437.1	36790.9	36225.3	35659.3	32799.1	29938.9
67.5°	40963.4	37164.7	33365.6	33100.5	32835.2	30114.8	27394.5
70°	37287.3	33890.3	30492.9	30374.1	30255.5	27296.4	24337.6
72.5°	32972.3	30314.3	27656.2	27571.2	27485.9	24090.2	20694.8
75°	27882.0	25814.1	23746.1	23430.6	23115.1	19600.8	16086.6
77.5°	22102.0	20529.9	18957.8	18506.3	18054.8	14774.0	11493.5
80°	16538.6	15351.8	14164.6	13603.3	13042.1	10282.4	7522.5
82.5°	11035.0	10217.9	9400.7	8773.5	8146.6	6259.6	4372.8
85°	6336.0	5664.8	4993.3	4460.0	3926.8	2925.4	1923.9
87.5°	2535.2	2199.5	1863.8	1566.3	1268.7	932.1	595.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)