

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P959324

Luminaire Tested: **NVN-SB1A-740-U-SLL**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P959324  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: NVN-SB1A-740-U-SLL  
Description: NAVION ROADWAY AND AREA HIGH DENSITY LED LUMINAIRE  
(1) 70 CRI, 4000K, 350mA LIGHTSQUARE WITH 26 LEDS AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4848.3 lumens  
Efficiency: N/A  
Efficacy: 156.9 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2  
  
Input Watts (W): 30.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P959324  
 CATALOG NUMBER: NVN-SB1A-740-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.5 fc  
 Type IV - Short - N/A

REPORT NUMBER: P959324  
CATALOG NUMBER: NVN-SB1A-740-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P959324

CATALOG NUMBER: NVN-SB1A-740-U-SLL

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1232.2	0.0	1232.2
	% Fixture	25.4	0.0	25.4
<b>Street Side</b>	Lumens	3616.1	0.0	3616.1
	% Fixture	74.6	0.0	74.6
<b>Total</b>	Lumens	4848.3	0.0	4848.3
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	66.1	1.4
10°-20°	207.6	4.3
20°-30°	320.7	6.6
30°-40°	406.4	8.4
40°-50°	612.9	12.6
50°-60°	990.3	20.4
60°-70°	1234.5	25.5
70°-80°	809.6	16.7
80°-90°	200.1	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4848.3	100.0
0°-180°	4848.3	100.0

**Coefficient of Utilization**



REPORT NUMBER: P959324


CATALOG NUMBER: NVN-SB1A-740-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	326.1	6.7			
FM (30°-60°)	1414.1	29.2			
FH (60°-80°)	1711.0	35.3			G1/1800
FVH (80°-90°)	164.9	3.4			G2/225
BL (0°-30°)	268.3	5.5	B1/500		
BM (30°-60°)	595.5	12.3	B1/1000		
BH (60°-80°)	333.1	6.9	B1/500		G1/500
BVH (80°-90°)	35.3	0.7			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**

Type IV Short



REPORT NUMBER: P959324

CATALOG NUMBER: NVN-SB1A-740-U-SLL

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7
2.5°	717.0	719.7	722.4	726.2	730.1	732.5	734.7	735.8	737.1	736.6	737.1
5°	770.9	780.4	790.0	799.3	808.8	814.0	819.0	822.2	825.2	827.6	825.2
7.5°	825.1	840.6	856.1	869.9	883.9	892.2	900.6	905.1	909.6	911.7	909.6
10°	866.7	885.0	903.2	919.5	935.8	945.8	955.5	959.9	964.3	966.0	964.3
12.5°	892.2	911.9	931.7	946.5	961.1	968.3	975.5	978.0	980.3	980.6	980.3
15°	907.6	924.8	941.8	951.1	960.3	960.5	960.8	958.3	955.7	952.7	955.7
17.5°	916.4	927.9	939.4	939.6	939.7	929.4	919.0	909.6	900.1	893.3	900.1
20°	926.0	930.0	934.0	921.9	909.7	886.8	864.0	847.3	830.7	820.4	830.7
22.5°	937.1	931.8	926.5	901.4	876.2	842.6	808.9	788.1	767.3	755.9	767.3
25°	951.4	934.8	918.2	880.0	841.7	800.8	760.0	738.1	716.3	705.6	716.3
27.5°	970.9	941.2	911.3	860.8	810.2	764.9	719.6	698.0	676.5	666.5	676.5
30°	997.1	952.7	908.5	846.1	783.8	736.7	689.4	669.4	649.4	640.1	649.4
32.5°	1028.1	967.3	906.6	836.1	765.7	721.3	676.9	661.2	645.5	638.8	645.5
35°	1065.6	991.4	917.1	843.6	770.2	739.3	708.6	704.9	701.3	700.7	701.3
37.5°	1128.9	1041.6	954.2	887.4	820.6	818.7	816.6	833.3	850.1	858.8	850.1
40°	1224.7	1129.6	1034.5	984.9	935.2	970.3	1005.3	1046.0	1086.7	1106.9	1086.7
42.5°	1351.6	1257.3	1163.0	1134.4	1105.8	1182.1	1258.6	1332.6	1406.6	1450.0	1406.6
45°	1508.2	1423.5	1338.8	1326.1	1313.5	1436.0	1558.5	1680.1	1801.6	1875.4	1801.6
47.5°	1704.2	1621.8	1539.3	1536.8	1534.2	1710.9	1887.5	2065.5	2243.4	2348.0	2243.4
50°	1961.0	1859.2	1757.5	1757.9	1758.3	1986.0	2213.7	2448.6	2683.6	2825.6	2683.6
52.5°	2255.8	2132.6	2009.4	1996.9	1984.4	2256.4	2528.4	2819.1	3109.6	3279.9	3109.6
55°	2569.8	2448.0	2326.2	2277.7	2229.1	2531.8	2834.4	3180.9	3527.4	3729.9	3527.4
57.5°	2855.2	2788.9	2722.6	2625.1	2527.8	2833.4	3139.0	3531.5	3923.9	4175.0	3923.9
60°	3027.8	3130.8	3233.8	3112.8	2991.8	3281.0	3570.3	3990.5	4410.7	4682.1	4410.7
62.5°	2940.2	3221.6	3503.0	3489.4	3475.8	3740.7	4005.7	4405.4	4805.3	5056.1	4805.3
65°	2764.8	3029.0	3293.1	3345.4	3397.6	3734.3	4071.1	4458.8	4846.4	5059.9	4846.4
67.5°	2529.8	2781.0	3032.3	3056.8	3081.3	3432.1	3782.9	4172.3	4561.6	4728.9	4561.6
70°	2247.5	2520.8	2794.0	2805.0	2816.0	3129.7	3443.4	3778.5	4113.5	4206.5	4113.5
72.5°	1911.1	2224.7	2538.3	2546.2	2554.0	2799.5	3045.0	3295.9	3546.8	3556.2	3546.8
75°	1485.5	1810.2	2134.7	2163.8	2192.9	2383.8	2574.9	2751.5	2928.1	2880.9	2928.1
77.5°	1061.4	1364.4	1667.4	1709.0	1750.7	1895.9	2041.1	2166.3	2291.7	2210.3	2291.7
80°	694.6	949.6	1204.4	1256.2	1308.1	1417.7	1527.4	1593.2	1658.9	1528.1	1658.9
82.5°	403.8	578.1	752.3	810.3	868.2	943.6	1019.1	1046.5	1074.0	971.1	1074.0
85°	177.6	270.2	362.6	411.8	461.1	523.2	585.1	600.6	616.2	533.9	616.2
87.5°	55.0	86.1	117.2	144.6	172.1	203.2	234.1	235.4	236.8	198.7	236.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P959324

CATALOG NUMBER: NVN-SB1A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7
2.5°	735.8	734.7	732.5	730.1	726.2	722.4	719.7	717.0	711.5	705.9	700.1
5°	822.2	819.0	814.0	808.8	799.3	790.0	780.4	770.9	758.8	746.6	734.5
7.5°	905.1	900.6	892.2	883.9	869.9	856.1	840.6	825.1	805.1	785.0	766.6
10°	959.9	955.5	945.8	935.8	919.5	903.2	885.0	866.7	841.4	816.0	791.5
12.5°	978.0	975.5	968.3	961.1	946.5	931.7	911.9	892.2	864.3	836.5	808.7
15°	958.3	960.8	960.5	960.3	951.1	941.8	924.8	907.6	878.6	849.6	819.5
17.5°	909.6	919.0	929.4	939.7	939.6	939.4	927.9	916.4	886.9	857.5	824.6
20°	847.3	864.0	886.8	909.7	921.9	934.0	930.0	926.0	895.3	864.7	828.7
22.5°	788.1	808.9	842.6	876.2	901.4	926.5	931.8	937.1	905.8	874.5	834.0
25°	738.1	760.0	800.8	841.7	880.0	918.2	934.8	951.4	920.8	890.1	843.9
27.5°	698.0	719.6	764.9	810.2	860.8	911.3	941.2	970.9	941.7	912.4	859.3
30°	669.4	689.4	736.7	783.8	846.1	908.5	952.7	997.1	968.8	940.6	879.1
32.5°	661.2	676.9	721.3	765.7	836.1	906.6	967.3	1028.1	1000.1	972.1	899.8
35°	704.9	708.6	739.3	770.2	843.6	917.1	991.4	1065.6	1038.8	1012.1	923.5
37.5°	833.3	816.6	818.7	820.6	887.4	954.2	1041.6	1128.9	1094.8	1060.7	950.0
40°	1046.0	1005.3	970.3	935.2	984.9	1034.5	1129.6	1224.7	1174.9	1125.1	983.6
42.5°	1332.6	1258.6	1182.1	1105.8	1134.4	1163.0	1257.3	1351.6	1279.7	1208.0	1027.6
45°	1680.1	1558.5	1436.0	1313.5	1326.1	1338.8	1423.5	1508.2	1411.4	1314.6	1085.5
47.5°	2065.5	1887.5	1710.9	1534.2	1536.8	1539.3	1621.8	1704.2	1567.9	1431.6	1147.1
50°	2448.6	2213.7	1986.0	1758.3	1757.9	1757.5	1859.2	1961.0	1755.5	1550.1	1204.3
52.5°	2819.1	2528.4	2256.4	1984.4	1996.9	2009.4	2132.6	2255.8	1952.7	1649.5	1241.5
55°	3180.9	2834.4	2531.8	2229.1	2277.7	2326.2	2448.0	2569.8	2127.5	1685.2	1233.3
57.5°	3531.5	3139.0	2833.4	2527.8	2625.1	2722.6	2788.9	2855.2	2251.3	1647.5	1175.7
60°	3990.5	3570.3	3281.0	2991.8	3112.8	3233.8	3130.8	3027.8	2282.3	1536.8	1068.5
62.5°	4405.4	4005.7	3740.7	3475.8	3489.4	3503.0	3221.6	2940.2	2152.0	1363.8	923.4
65°	4458.8	4071.1	3734.3	3397.6	3345.4	3293.1	3029.0	2764.8	1967.6	1170.2	775.5
67.5°	4172.3	3782.9	3432.1	3081.3	3056.8	3032.3	2781.0	2529.8	1748.0	966.3	630.7
70°	3778.5	3443.4	3129.7	2816.0	2805.0	2794.0	2520.8	2247.5	1508.6	769.7	496.5
72.5°	3295.9	3045.0	2799.5	2554.0	2546.2	2538.3	2224.7	1911.1	1249.0	586.8	379.7
75°	2751.5	2574.9	2383.8	2192.9	2163.8	2134.7	1810.2	1485.5	951.4	417.2	275.5
77.5°	2166.3	2041.1	1895.9	1750.7	1709.0	1667.4	1364.4	1061.4	665.8	270.4	186.7
80°	1593.2	1527.4	1417.7	1308.1	1256.2	1204.4	949.6	694.6	429.1	163.4	120.3
82.5°	1046.5	1019.1	943.6	868.2	810.3	752.3	578.1	403.8	248.3	92.8	74.0
85°	600.6	585.1	523.2	461.1	411.8	362.6	270.2	177.6	111.7	45.7	39.6
87.5°	235.4	234.1	203.2	172.1	144.6	117.2	86.1	55.0	36.6	18.1	16.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P959324

CATALOG NUMBER: NVN-SB1A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7
2.5°	694.2	688.4	682.4	676.8	671.3	665.7	659.7	654.8	650.0	645.5	641.1
5°	722.4	710.2	698.0	686.6	675.3	664.5	653.8	644.6	635.3	627.6	619.8
7.5°	748.0	730.0	712.0	696.1	680.2	665.5	651.8	639.5	627.2	616.9	606.7
10°	767.1	745.2	723.2	704.5	685.6	667.6	652.8	639.8	626.8	616.5	606.4
12.5°	781.0	755.2	729.4	708.1	686.9	667.8	654.1	643.5	632.8	626.1	619.3
15°	789.5	759.6	729.9	705.3	680.7	659.7	648.6	643.6	638.5	639.4	640.3
17.5°	791.8	757.3	722.7	693.1	663.6	638.8	632.0	633.9	635.7	646.9	658.0
20°	792.6	750.7	708.9	672.2	635.5	606.7	604.9	613.6	622.3	641.6	661.0
22.5°	793.7	742.7	691.8	647.6	603.4	570.6	574.1	587.0	599.8	622.0	644.1
25°	797.7	734.8	671.9	620.1	568.5	534.8	544.3	559.1	573.9	593.8	613.8
27.5°	806.1	729.5	652.8	595.1	537.3	506.7	518.1	532.5	546.8	563.1	579.5
30°	817.6	727.0	636.3	574.1	511.9	486.2	495.2	506.6	518.0	531.6	545.1
32.5°	827.7	724.0	620.1	556.0	491.8	471.1	475.1	481.9	488.6	499.4	510.2
35°	835.0	718.1	601.4	538.2	475.1	457.8	456.1	458.0	459.8	468.1	476.3
37.5°	839.3	708.3	577.2	517.3	457.5	442.3	436.2	434.2	432.1	438.1	444.0
40°	842.0	694.6	547.2	492.3	437.5	423.7	414.4	409.8	405.2	409.5	413.7
42.5°	847.3	680.5	513.9	464.7	415.6	403.0	391.2	385.1	379.0	382.5	386.0
45°	856.4	667.5	478.6	435.5	392.5	379.7	368.3	362.2	356.3	359.3	362.2
47.5°	862.6	656.7	450.7	412.4	374.0	357.5	347.7	342.7	337.7	340.4	343.2
50°	858.5	644.9	431.2	397.0	362.7	341.0	329.6	325.1	320.7	325.0	329.3
52.5°	833.3	625.0	416.8	386.8	357.0	332.1	316.1	311.7	307.4	313.9	320.3
55°	781.3	592.0	402.8	379.6	356.2	332.9	308.9	302.1	295.1	304.3	313.4
57.5°	703.9	545.6	387.3	370.8	354.3	333.8	304.7	294.6	284.4	294.3	304.2
60°	600.1	485.3	370.4	357.5	344.5	331.1	300.6	287.5	274.4	283.0	291.7
62.5°	483.2	413.1	343.0	334.4	325.7	324.1	295.9	279.5	263.1	268.7	274.1
65°	380.9	348.2	315.4	311.4	307.3	307.5	286.0	268.5	251.1	253.2	255.3
67.5°	295.0	285.8	276.4	278.7	281.0	280.3	268.3	253.8	239.2	238.6	237.9
70°	223.4	226.1	228.8	239.3	249.8	249.8	245.9	235.5	225.2	222.8	220.6
72.5°	172.4	180.4	188.4	203.4	218.2	220.8	220.8	213.7	206.6	203.3	199.9
75°	133.9	141.1	148.4	165.1	181.8	193.4	192.4	187.0	181.5	178.2	175.1
77.5°	103.0	107.9	113.0	129.1	145.4	164.5	164.0	159.6	155.2	152.0	148.7
80°	77.3	79.3	81.4	95.1	108.9	131.6	131.5	127.9	124.2	121.5	118.7
82.5°	55.2	55.6	56.0	66.1	76.3	95.6	96.8	94.9	93.2	91.2	89.3
85°	33.4	33.2	33.0	40.4	47.9	62.3	63.7	61.8	59.9	57.7	55.6
87.5°	14.7	14.5	14.2	17.3	20.3	26.3	28.2	27.4	26.6	26.2	25.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P959324

CATALOG NUMBER: NVN-SB1A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7
2.5°	637.2	633.3	629.5	625.7	622.6	619.6	617.2	614.8	612.8	611.0	609.3
5°	612.9	606.1	599.8	593.7	588.9	584.0	580.7	577.4	574.9	572.6	570.7
7.5°	598.1	589.4	581.8	574.2	568.5	562.8	558.8	554.8	552.1	549.4	547.8
10°	597.1	587.7	579.2	570.6	563.9	557.0	552.6	548.1	545.4	542.8	541.5
12.5°	612.0	604.8	595.8	587.0	578.3	569.6	563.9	558.1	555.1	552.4	551.1
15°	638.5	636.5	628.8	621.2	608.7	596.3	587.6	578.9	574.8	570.8	569.3
17.5°	664.0	669.8	663.7	657.4	641.0	624.6	611.8	598.9	593.0	587.0	585.1
20°	673.4	685.8	683.0	680.1	661.3	642.7	626.8	611.0	603.4	595.8	593.4
22.5°	660.3	676.4	678.1	679.9	661.9	644.0	627.8	611.5	603.4	595.4	592.8
25°	629.7	645.5	651.4	657.3	642.7	628.0	613.6	599.1	592.1	585.2	582.7
27.5°	592.2	605.0	611.6	618.2	607.7	597.3	586.1	574.8	570.2	565.5	564.4
30°	555.7	566.3	571.6	577.0	569.1	561.1	553.1	545.0	542.5	540.2	540.2
32.5°	520.4	530.5	536.5	542.4	535.2	527.8	521.4	515.0	513.4	511.9	512.1
35°	486.4	496.4	503.6	510.8	505.5	500.3	494.4	488.5	486.2	483.8	483.3
37.5°	454.0	464.0	472.8	481.7	479.3	476.9	471.5	466.0	461.7	457.4	455.1
40°	423.4	433.1	443.2	453.5	454.1	454.6	450.0	445.4	439.0	432.8	428.6
42.5°	395.1	404.4	415.3	426.3	429.3	432.2	428.3	424.5	416.6	408.8	402.6
45°	370.8	379.6	391.0	402.4	406.6	410.8	407.3	403.8	394.9	386.0	378.7
47.5°	351.7	360.2	371.5	382.7	387.6	392.5	390.0	387.6	379.6	371.7	365.0
50°	337.4	345.4	355.5	365.6	371.8	378.0	377.9	377.8	371.5	365.1	359.0
52.5°	327.7	335.0	344.4	353.8	361.2	368.6	369.9	371.3	366.1	360.9	355.4
55°	321.3	329.3	337.5	345.7	353.5	361.4	363.3	365.1	360.6	356.1	351.3
57.5°	313.4	322.8	331.0	339.1	347.0	354.9	356.7	358.6	354.0	349.5	344.7
60°	302.4	313.0	321.3	329.6	337.5	345.5	347.6	349.6	345.1	340.7	335.8
62.5°	286.6	299.1	307.9	316.7	324.0	331.3	333.2	335.2	331.2	327.2	322.0
65°	268.7	282.1	290.5	298.9	305.3	311.7	313.8	315.7	311.9	308.0	303.0
67.5°	250.2	262.6	270.6	278.6	284.1	289.7	291.6	293.6	290.0	286.5	281.8
70°	231.4	242.3	249.2	256.0	261.1	266.1	267.9	269.9	266.9	264.0	259.5
72.5°	208.5	217.0	223.2	229.5	234.3	239.2	241.5	243.7	241.4	238.9	234.6
75°	181.4	187.7	193.4	199.1	203.5	208.0	210.3	212.7	211.5	210.3	206.6
77.5°	153.9	159.0	163.9	168.7	173.4	178.0	180.3	182.4	180.8	179.2	175.5
80°	123.0	127.3	131.4	135.5	139.0	142.6	145.4	148.4	147.7	147.0	142.1
82.5°	89.0	88.6	87.1	85.7	93.3	100.9	105.8	110.8	110.5	110.1	106.0
85°	53.7	51.8	47.9	43.9	50.9	58.1	64.2	70.3	69.8	69.3	66.1
87.5°	25.7	25.6	22.7	19.6	22.5	25.5	28.0	30.5	29.9	29.2	27.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P959324

CATALOG NUMBER: NVN-SB1A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7
2.5°	607.4	605.3	607.4	609.3	611.0	612.8	614.8	617.2	619.6	622.6	625.7
5°	569.0	567.1	569.0	570.7	572.6	574.9	577.4	580.7	584.0	588.9	593.7
7.5°	546.1	544.9	546.1	547.8	549.4	552.1	554.8	558.8	562.8	568.5	574.2
10°	540.1	539.6	540.1	541.5	542.8	545.4	548.1	552.6	557.0	563.9	570.6
12.5°	550.0	549.8	550.0	551.1	552.4	555.1	558.1	563.9	569.6	578.3	587.0
15°	567.8	567.6	567.8	569.3	570.8	574.8	578.9	587.6	596.3	608.7	621.2
17.5°	583.1	582.8	583.1	585.1	587.0	593.0	598.9	611.8	624.6	641.0	657.4
20°	590.9	590.2	590.9	593.4	595.8	603.4	611.0	626.8	642.7	661.3	680.1
22.5°	590.1	588.9	590.1	592.8	595.4	603.4	611.5	627.8	644.0	661.9	679.9
25°	580.2	578.7	580.2	582.7	585.2	592.1	599.1	613.6	628.0	642.7	657.3
27.5°	563.2	562.8	563.2	564.4	565.5	570.2	574.8	586.1	597.3	607.7	618.2
30°	540.2	540.6	540.2	540.2	540.2	542.5	545.0	553.1	561.1	569.1	577.0
32.5°	512.3	512.7	512.3	512.1	511.9	513.4	515.0	521.4	527.8	535.2	542.4
35°	482.8	482.5	482.8	483.3	483.8	486.2	488.5	494.4	500.3	505.5	510.8
37.5°	452.8	451.5	452.8	455.1	457.4	461.7	466.0	471.5	476.9	479.3	481.7
40°	424.4	421.9	424.4	428.6	432.8	439.0	445.4	450.0	454.6	454.1	453.5
42.5°	396.5	392.5	396.5	402.6	408.8	416.6	424.5	428.3	432.2	429.3	426.3
45°	371.5	366.8	371.5	378.7	386.0	394.9	403.8	407.3	410.8	406.6	402.4
47.5°	358.2	353.8	358.2	365.0	371.7	379.6	387.6	390.0	392.5	387.6	382.7
50°	352.7	348.4	352.7	359.0	365.1	371.5	377.8	377.9	378.0	371.8	365.6
52.5°	349.8	345.8	349.8	355.4	360.9	366.1	371.3	369.9	368.6	361.2	353.8
55°	346.3	342.8	346.3	351.3	356.1	360.6	365.1	363.3	361.4	353.5	345.7
57.5°	339.9	336.2	339.9	344.7	349.5	354.0	358.6	356.7	354.9	347.0	339.1
60°	330.8	327.0	330.8	335.8	340.7	345.1	349.6	347.6	345.5	337.5	329.6
62.5°	316.7	312.1	316.7	322.0	327.2	331.2	335.2	333.2	331.3	324.0	316.7
65°	297.9	294.0	297.9	303.0	308.0	311.9	315.7	313.8	311.7	305.3	298.9
67.5°	277.1	273.5	277.1	281.8	286.5	290.0	293.6	291.6	289.7	284.1	278.6
70°	255.0	250.9	255.0	259.5	264.0	266.9	269.9	267.9	266.1	261.1	256.0
72.5°	230.4	226.4	230.4	234.6	238.9	241.4	243.7	241.5	239.2	234.3	229.5
75°	203.1	199.3	203.1	206.6	210.3	211.5	212.7	210.3	208.0	203.5	199.1
77.5°	171.9	168.8	171.9	175.5	179.2	180.8	182.4	180.3	178.0	173.4	168.7
80°	137.1	131.5	137.1	142.1	147.0	147.7	148.4	145.4	142.6	139.0	135.5
82.5°	101.9	98.2	101.9	106.0	110.1	110.5	110.8	105.8	100.9	93.3	85.7
85°	62.8	59.7	62.8	66.1	69.3	69.8	70.3	64.2	58.1	50.9	43.9
87.5°	25.9	24.3	25.9	27.6	29.2	29.9	30.5	28.0	25.5	22.5	19.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P959324

CATALOG NUMBER: NVN-SB1A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7	666.7
2.5°	629.5	633.3	637.2	641.1	645.5	650.0	654.8	659.7	665.7	671.3	676.8
5°	599.8	606.1	612.9	619.8	627.6	635.3	644.6	653.8	664.5	675.3	686.6
7.5°	581.8	589.4	598.1	606.7	616.9	627.2	639.5	651.8	665.5	680.2	696.1
10°	579.2	587.7	597.1	606.4	616.5	626.8	639.8	652.8	667.6	685.6	704.5
12.5°	595.8	604.8	612.0	619.3	626.1	632.8	643.5	654.1	667.8	686.9	708.1
15°	628.8	636.5	638.5	640.3	639.4	638.5	643.6	648.6	659.7	680.7	705.3
17.5°	663.7	669.8	664.0	658.0	646.9	635.7	633.9	632.0	638.8	663.6	693.1
20°	683.0	685.8	673.4	661.0	641.6	622.3	613.6	604.9	606.7	635.5	672.2
22.5°	678.1	676.4	660.3	644.1	622.0	599.8	587.0	574.1	570.6	603.4	647.6
25°	651.4	645.5	629.7	613.8	593.8	573.9	559.1	544.3	534.8	568.5	620.1
27.5°	611.6	605.0	592.2	579.5	563.1	546.8	532.5	518.1	506.7	537.3	595.1
30°	571.6	566.3	555.7	545.1	531.6	518.0	506.6	495.2	486.2	511.9	574.1
32.5°	536.5	530.5	520.4	510.2	499.4	488.6	481.9	475.1	471.1	491.8	556.0
35°	503.6	496.4	486.4	476.3	468.1	459.8	458.0	456.1	457.8	475.1	538.2
37.5°	472.8	464.0	454.0	444.0	438.1	432.1	434.2	436.2	442.3	457.5	517.3
40°	443.2	433.1	423.4	413.7	409.5	405.2	409.8	414.4	423.7	437.5	492.3
42.5°	415.3	404.4	395.1	386.0	382.5	379.0	385.1	391.2	403.0	415.6	464.7
45°	391.0	379.6	370.8	362.2	359.3	356.3	362.2	368.3	379.7	392.5	435.5
47.5°	371.5	360.2	351.7	343.2	340.4	337.7	342.7	347.7	357.5	374.0	412.4
50°	355.5	345.4	337.4	329.3	325.0	320.7	325.1	329.6	341.0	362.7	397.0
52.5°	344.4	335.0	327.7	320.3	313.9	307.4	311.7	316.1	332.1	357.0	386.8
55°	337.5	329.3	321.3	313.4	304.3	295.1	302.1	308.9	332.9	356.2	379.6
57.5°	331.0	322.8	313.4	304.2	294.3	284.4	294.6	304.7	333.8	354.3	370.8
60°	321.3	313.0	302.4	291.7	283.0	274.4	287.5	300.6	331.1	344.5	357.5
62.5°	307.9	299.1	286.6	274.1	268.7	263.1	279.5	295.9	324.1	325.7	334.4
65°	290.5	282.1	268.7	255.3	253.2	251.1	268.5	286.0	307.5	307.3	311.4
67.5°	270.6	262.6	250.2	237.9	238.6	239.2	253.8	268.3	280.3	281.0	278.7
70°	249.2	242.3	231.4	220.6	222.8	225.2	235.5	245.9	249.8	249.8	239.3
72.5°	223.2	217.0	208.5	199.9	203.3	206.6	213.7	220.8	220.8	218.2	203.4
75°	193.4	187.7	181.4	175.1	178.2	181.5	187.0	192.4	193.4	181.8	165.1
77.5°	163.9	159.0	153.9	148.7	152.0	155.2	159.6	164.0	164.5	145.4	129.1
80°	131.4	127.3	123.0	118.7	121.5	124.2	127.9	131.5	131.6	108.9	95.1
82.5°	87.1	88.6	89.0	89.3	91.2	93.2	94.9	96.8	95.6	76.3	66.1
85°	47.9	51.8	53.7	55.6	57.7	59.9	61.8	63.7	62.3	47.9	40.4
87.5°	22.7	25.6	25.7	25.8	26.2	26.6	27.4	28.2	26.3	20.3	17.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P959324

CATALOG NUMBER: NVN-SB1A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	666.7	666.7	666.7	666.7	666.7	666.7	666.7
2.5°	682.4	688.4	694.2	700.1	705.9	711.5	717.0
5°	698.0	710.2	722.4	734.5	746.6	758.8	770.9
7.5°	712.0	730.0	748.0	766.6	785.0	805.1	825.1
10°	723.2	745.2	767.1	791.5	816.0	841.4	866.7
12.5°	729.4	755.2	781.0	808.7	836.5	864.3	892.2
15°	729.9	759.6	789.5	819.5	849.6	878.6	907.6
17.5°	722.7	757.3	791.8	824.6	857.5	886.9	916.4
20°	708.9	750.7	792.6	828.7	864.7	895.3	926.0
22.5°	691.8	742.7	793.7	834.0	874.5	905.8	937.1
25°	671.9	734.8	797.7	843.9	890.1	920.8	951.4
27.5°	652.8	729.5	806.1	859.3	912.4	941.7	970.9
30°	636.3	727.0	817.6	879.1	940.6	968.8	997.1
32.5°	620.1	724.0	827.7	899.8	972.1	1000.1	1028.1
35°	601.4	718.1	835.0	923.5	1012.1	1038.8	1065.6
37.5°	577.2	708.3	839.3	950.0	1060.7	1094.8	1128.9
40°	547.2	694.6	842.0	983.6	1125.1	1174.9	1224.7
42.5°	513.9	680.5	847.3	1027.6	1208.0	1279.7	1351.6
45°	478.6	667.5	856.4	1085.5	1314.6	1411.4	1508.2
47.5°	450.7	656.7	862.6	1147.1	1431.6	1567.9	1704.2
50°	431.2	644.9	858.5	1204.3	1550.1	1755.5	1961.0
52.5°	416.8	625.0	833.3	1241.5	1649.5	1952.7	2255.8
55°	402.8	592.0	781.3	1233.3	1685.2	2127.5	2569.8
57.5°	387.3	545.6	703.9	1175.7	1647.5	2251.3	2855.2
60°	370.4	485.3	600.1	1068.5	1536.8	2282.3	3027.8
62.5°	343.0	413.1	483.2	923.4	1363.8	2152.0	2940.2
65°	315.4	348.2	380.9	775.5	1170.2	1967.6	2764.8
67.5°	276.4	285.8	295.0	630.7	966.3	1748.0	2529.8
70°	228.8	226.1	223.4	496.5	769.7	1508.6	2247.5
72.5°	188.4	180.4	172.4	379.7	586.8	1249.0	1911.1
75°	148.4	141.1	133.9	275.5	417.2	951.4	1485.5
77.5°	113.0	107.9	103.0	186.7	270.4	665.8	1061.4
80°	81.4	79.3	77.3	120.3	163.4	429.1	694.6
82.5°	56.0	55.6	55.2	74.0	92.8	248.3	403.8
85°	33.0	33.2	33.4	39.6	45.7	111.7	177.6
87.5°	14.2	14.5	14.7	16.4	18.1	36.6	55.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)