

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P885283

Luminaire Tested: **NVN-SB6C-730-U-SL4-HSS**

Issue Date: 10/7/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P885283  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: NVN-SB6C-730-U-SL4-HSS  
Description: NAVION ROADWAY AND AREA HIGH DENSITY LED LUMINAIRE  
(6) 70 CRI, 3000K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE IV SPILL  
LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 31235 lumens  
Efficiency: N/A  
Efficacy: 103.8 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G5  
  
Input Watts (W): 300.9  
Input Voltage (V): 120.0  
Input Current (Ain): 2.518  
Voltage Rise (V): NR  
Power Factor: 0.997  
Total Harmonic Distortion (THDi): 6.297  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P885283  
 CATALOG NUMBER: NVN-SB6C-730-U-SL4-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.6 fc  
 Type IV - Short - N/A

REPORT NUMBER: P885283  
CATALOG NUMBER: NVN-SB6C-730-U-SL4-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral      - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P885283  
 CATALOG NUMBER: NVN-SB6C-730-U-SL4-HSS

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	4033.7	0.0	4033.7
	% Fixture	12.9	0.0	12.9
<b>Street Side</b>	Lumens	27201.3	0.0	27201.3
	% Fixture	87.1	0.0	87.1
<b>Total</b>	Lumens	31235.0	0.0	31235.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	377.7	1.2
10°-20°	1025.7	3.3
20°-30°	1659.7	5.3
30°-40°	2450.3	7.8
40°-50°	4124.0	13.2
50°-60°	6403.4	20.5
60°-70°	8012.4	25.7
70°-80°	6559.8	21.0
80°-90°	622.0	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	31235.0	100.0
0°-180°	31235.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P885283


CATALOG NUMBER: NVN-SB6C-730-U-SL4-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2073.1	6.6			
FM (30°-60°)	10500.7	33.6			
FH (60°-80°)	14010.3	44.9			G5
FVH (80°-90°)	617.3	2.0			G4/750
BL (0°-30°)	990.0	3.2	B2/1000		
BM (30°-60°)	2476.9	7.9	B2/2500		
BH (60°-80°)	561.9	1.8	B2/1000		G2/1000
BVH (80°-90°)	4.7	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G5**

Type IV Short



REPORT NUMBER: P885283

CATALOG NUMBER: NVN-SB6C-730-U-SL4-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
0°	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8
2.5°	4260.5	4276.9	4267.5	4248.7	4244.0	4234.6	4222.8	4218.1	4201.6	4187.5	4171.1
5°	4380.4	4396.9	4385.1	4359.3	4347.5	4335.7	4319.3	4305.2	4272.2	4241.6	4204.0
7.5°	4512.2	4526.3	4512.2	4474.5	4455.7	4441.6	4418.1	4396.9	4359.3	4314.6	4267.5
10°	4658.0	4669.8	4648.6	4599.2	4568.6	4547.5	4526.3	4502.8	4467.5	4418.1	4361.6
12.5°	4794.5	4808.6	4775.7	4716.8	4681.6	4660.4	4636.9	4618.0	4582.8	4535.7	4476.9
15°	4919.2	4940.3	4883.9	4820.4	4780.4	4763.9	4740.4	4728.6	4705.1	4672.1	4618.0
17.5°	5013.3	5027.4	4968.6	4893.3	4848.6	4836.8	4820.4	4827.4	4822.7	4806.2	4771.0
20°	5093.3	5102.7	5025.0	4933.3	4883.9	4886.2	4881.5	4905.0	4914.5	4914.5	4912.1
22.5°	5192.1	5194.4	5095.6	4980.3	4921.5	4938.0	4945.0	4970.9	4989.7	5008.6	5050.9
25°	5321.4	5316.7	5199.1	5041.5	4989.7	5013.3	5029.7	5039.1	5060.3	5090.9	5187.4
27.5°	5514.4	5500.2	5349.7	5140.3	5079.1	5100.3	5130.9	5126.2	5116.8	5140.3	5302.6
30°	5759.0	5740.2	5540.2	5279.1	5222.6	5241.5	5250.9	5208.5	5140.3	5161.5	5403.8
32.5°	6147.2	6114.3	5836.7	5434.4	5347.3	5368.5	5356.7	5269.7	5168.5	5189.7	5504.9
35°	6822.4	6742.4	6349.5	5759.0	5488.5	5465.0	5436.7	5352.0	5227.3	5206.2	5589.6
37.5°	8257.4	8116.3	7445.8	6391.9	5808.4	5655.5	5568.5	5483.8	5290.9	5206.2	5686.1
40°	9876.0	9732.5	8958.5	7450.5	6340.1	6081.3	5874.3	5639.0	5356.7	5236.8	5836.7
42.5°	11565.1	11407.5	10612.3	8763.2	7100.0	6568.3	6182.5	5763.7	5465.0	5330.9	6036.6
45°	13451.8	13254.2	12214.4	10132.4	8203.3	7377.6	6678.9	6020.2	5653.2	5497.9	6309.5
47.5°	15442.1	15185.7	13811.8	11461.6	9391.3	8497.4	7586.9	6478.9	5930.8	5747.3	6678.9
50°	17206.5	16952.4	15460.9	12851.9	10501.7	9563.1	8622.1	7114.1	6347.2	6100.1	7175.3
52.5°	18474.5	18281.6	16961.8	14287.0	11656.8	10562.9	9560.7	7852.8	6874.1	6551.8	7761.0
55°	19323.8	19147.3	18025.2	15646.8	13000.1	11663.9	10485.3	8655.0	7509.3	7092.9	8408.0
57.5°	19839.0	19737.8	18794.5	16860.7	14331.7	12868.4	11543.9	9537.2	8257.4	7730.5	9130.2
60°	20022.5	19940.1	19272.0	18018.1	15940.8	14315.2	12788.4	10532.3	9165.5	8455.0	9871.3
62.5°	19533.1	19549.6	19615.5	19389.6	17637.0	16009.0	14279.9	11727.4	10172.4	9276.1	10567.6
65°	17230.0	17366.5	18618.0	20909.4	19883.7	18131.0	16178.4	13186.0	11325.1	10210.0	11120.5
67.5°	14265.8	14463.4	16020.8	21798.6	22278.6	20885.9	18822.7	15044.5	12699.0	11160.5	11329.8
70°	10920.5	11132.2	13019.0	21612.8	24520.5	23897.1	22092.7	17408.8	14122.3	11819.2	10795.8
72.5°	7794.0	7902.2	9389.0	19959.0	25440.4	25948.5	24501.7	19648.4	14849.2	11454.5	8805.6
75°	5476.7	5457.9	6443.6	16072.6	24007.7	25699.2	23657.2	18436.9	13437.7	9099.6	5429.7
77.5°	2385.5	2390.2	3218.3	9760.7	19161.4	21949.2	19664.9	11548.6	9367.8	4822.7	2291.4
80°	618.7	637.5	1181.0	3886.4	11536.9	14486.9	11993.3	5076.8	4328.7	1176.3	437.6
82.5°	218.8	232.9	543.4	1221.0	4255.7	6643.6	5340.3	1623.3	1129.2	336.4	117.6
85°	63.5	75.3	291.7	374.1	879.9	1877.3	1296.3	315.2	277.6	174.1	30.6
87.5°	0.0	9.4	58.8	51.8	51.8	35.3	65.9	35.3	44.7	21.2	9.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P885283

CATALOG NUMBER: NVN-SB6C-730-U-SL4-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8	4135.8
2.5°	4156.9	4140.5	4105.2	4067.5	4032.3	3999.3	3989.9	3954.6	3938.2	3940.5	3938.2
5°	4178.1	4147.5	4079.3	3997.0	3912.3	3815.8	3735.8	3622.9	3526.5	3514.7	3507.6
7.5°	4234.6	4185.2	4074.6	3914.6	3702.9	3437.1	3190.0	2945.4	2806.6	2731.3	2726.6
10°	4321.6	4255.7	4086.4	3780.5	3331.2	2856.0	2481.9	2173.7	2016.1	1943.2	1929.1
12.5°	4425.1	4352.2	4105.2	3552.3	2851.3	2227.9	1823.2	1635.0	1602.1	1597.4	1595.0
15°	4571.0	4491.0	4126.4	3244.2	2331.4	1696.2	1510.3	1512.7	1538.6	1552.7	1550.3
17.5°	4733.3	4653.3	4095.8	2867.7	1818.5	1449.2	1444.5	1465.6	1503.3	1517.4	1515.0
20°	4898.0	4822.7	3987.6	2425.5	1470.3	1380.9	1399.8	1423.3	1460.9	1479.7	1479.7
22.5°	5067.4	5001.5	3815.8	1955.0	1326.8	1331.5	1355.1	1378.6	1420.9	1442.1	1442.1
25°	5248.5	5192.1	3587.6	1566.8	1265.7	1279.8	1310.4	1338.6	1383.3	1409.2	1409.2
27.5°	5432.0	5389.7	3328.8	1308.0	1209.2	1225.7	1261.0	1298.6	1343.3	1373.9	1376.2
30°	5632.0	5608.5	3121.8	1211.6	1155.1	1169.2	1209.2	1251.6	1301.0	1338.6	1343.3
32.5°	5836.7	5831.9	3020.7	1282.1	1105.7	1115.1	1150.4	1192.7	1253.9	1301.0	1305.7
35°	6039.0	6048.4	2961.8	1482.1	1089.2	1063.3	1086.9	1124.5	1197.4	1256.3	1265.7
37.5°	6297.8	6321.3	2959.5	1698.5	1129.2	1011.6	1028.1	1053.9	1117.5	1185.7	1197.4
40°	6683.6	6808.3	3110.1	1884.4	1199.8	964.5	969.2	974.0	1006.9	1063.3	1082.2
42.5°	7196.4	7561.1	3653.5	2011.4	1228.0	922.2	905.7	879.9	875.1	905.7	922.2
45°	7834.0	8471.5	4608.6	2082.0	1199.8	875.1	830.4	762.2	736.3	757.5	757.5
47.5°	8584.4	9469.0	5740.2	2098.5	1152.7	816.3	736.3	646.9	625.8	632.8	630.5
50°	9316.1	10217.1	6735.3	1962.0	1075.1	741.1	632.8	557.6	543.4	545.8	545.8
52.5°	9963.0	10473.5	7017.6	1639.7	971.6	649.3	543.4	491.7	482.3	482.3	479.9
55°	10391.2	10195.9	6257.8	1253.9	842.2	555.2	465.8	439.9	435.2	432.9	428.2
57.5°	10480.6	9292.5	4726.3	905.7	658.7	468.2	414.0	399.9	390.5	381.1	376.4
60°	10160.6	7786.9	3008.9	632.8	494.0	399.9	367.0	357.6	338.8	319.9	312.9
62.5°	9469.0	5881.4	1665.6	439.9	397.6	341.1	324.7	312.9	277.6	247.0	237.6
65°	8539.7	3909.9	736.3	343.5	324.7	287.0	277.6	261.1	218.8	183.5	176.4
67.5°	7605.8	2251.4	331.7	275.2	261.1	235.3	228.2	216.4	185.9	152.9	148.2
70°	6540.1	1141.0	228.2	218.8	202.3	178.8	185.9	183.5	152.9	124.7	120.0
72.5°	4869.8	567.0	171.7	164.7	145.9	127.0	152.9	150.6	120.0	94.1	89.4
75°	2757.2	280.0	124.7	115.3	87.0	94.1	122.3	115.3	82.3	61.2	56.5
77.5°	1093.9	143.5	82.3	70.6	51.8	63.5	89.4	77.6	42.3	25.9	23.5
80°	251.7	70.6	42.3	30.6	23.5	37.6	47.1	28.2	11.8	2.4	0.0
82.5°	70.6	30.6	14.1	11.8	11.8	14.1	11.8	4.7	0.0	0.0	0.0
85°	23.5	14.1	4.7	2.4	2.4	2.4	2.4	0.0	0.0	0.0	0.0
87.5°	9.4	4.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)