

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P964595

Luminaire Tested: **NVN-SB3C-740-U-SLR-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P964595
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: NVN-SB3C-740-U-SLR-HSS
Description: NAVION ROADWAY AND AREA HIGH DENSITY LED LUMINAIRE
(3) 70 CRI, 4000K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18596.6 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G4


Input Watts (W): 149.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P964595
 CATALOG NUMBER: NVN-SB3C-740-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P964595
CATALOG NUMBER: NVN-SB3C-740-U-SLR-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P964595
 CATALOG NUMBER: NVN-SB3C-740-U-SLR-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2604.3	0.0	2604.3
	% Fixture	14.0	0.0	14.0
Street Side	Lumens	15992.3	0.0	15992.3
	% Fixture	86.0	0.0	86.0
Total	Lumens	18596.6	0.0	18596.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.5	1.4
10°-20°	760.0	4.1
20°-30°	1119.6	6.0
30°-40°	1438.4	7.7
40°-50°	2326.3	12.5
50°-60°	4079.4	21.9
60°-70°	5104.4	27.4
70°-80°	2982.8	16.0
80°-90°	532.2	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	18596.6	100.0
0°-180°	18596.6	100.0

Coefficient of Utilization



REPORT NUMBER: P964595


CATALOG NUMBER: NVN-SB3C-740-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1450.5	7.8			
FM (30°-60°)	6517.9	35.0			
FH (60°-80°)	7512.2	40.4			G4/12000
FVH (80°-90°)	511.7	2.8			G4/750
BL (0°-30°)	682.6	3.7	B2/1000		
BM (30°-60°)	1326.2	7.1	B2/2500		
BH (60°-80°)	575.0	3.1	B2/1000		G2/1000
BVH (80°-90°)	20.4	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G4

Type IV Short



REPORT NUMBER: P964595

CATALOG NUMBER: NVN-SB3C-740-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0
2.5°	2909.4	2859.4	2829.9	2756.9	2684.0	2625.0	2545.6	2493.0	2430.3	2370.0	2316.3
5°	3242.5	3161.8	3064.4	2931.2	2809.4	2685.2	2564.8	2445.6	2320.1	2204.8	2134.4
7.5°	3524.4	3407.7	3236.1	3059.3	2904.2	2754.4	2613.4	2455.9	2303.5	2122.8	2026.7
10°	3739.6	3591.0	3365.5	3133.6	2955.5	2804.4	2667.3	2534.0	2380.3	2162.5	2042.1
12.5°	3870.2	3711.4	3443.6	3172.1	2968.3	2799.3	2692.9	2633.9	2573.8	2357.2	2216.4
15°	3966.3	3794.7	3498.7	3198.9	2938.9	2731.3	2653.2	2712.1	2781.3	2643.0	2480.2
17.5°	4066.3	3885.6	3570.5	3210.5	2859.4	2599.4	2566.1	2718.5	2878.6	2872.3	2710.8
20°	4161.1	3981.7	3633.2	3202.8	2731.3	2439.2	2468.7	2663.5	2849.2	2927.3	2840.2
22.5°	4269.9	4080.3	3693.5	3173.3	2564.8	2289.3	2381.6	2576.3	2739.0	2831.3	2804.4
25°	4403.2	4204.7	3777.9	3129.7	2385.4	2165.1	2293.2	2475.1	2607.1	2671.1	2669.8
27.5°	4546.7	4353.2	3890.7	3106.7	2240.6	2076.6	2193.3	2354.6	2472.5	2517.4	2517.4
30°	4724.7	4526.2	4023.9	3081.0	2145.8	2025.4	2089.5	2215.0	2330.3	2375.1	2375.1
32.5°	4919.5	4718.3	4152.1	3019.5	2088.2	1987.0	1988.3	2067.7	2172.8	2226.6	2234.3
35°	5162.8	4948.9	4289.1	2885.1	2042.1	1942.2	1889.6	1928.0	2015.2	2079.2	2095.9
37.5°	5510.1	5251.3	4457.0	2692.9	1974.2	1873.0	1785.9	1794.9	1861.5	1931.9	1957.5
40°	5989.2	5657.4	4654.3	2493.0	1876.8	1775.6	1671.9	1668.0	1716.7	1785.9	1814.0
42.5°	6637.4	6194.2	4891.3	2302.1	1783.3	1657.7	1551.4	1545.0	1583.4	1643.7	1673.1
45°	7493.2	6880.8	5182.1	2138.1	1710.3	1542.4	1437.4	1434.8	1466.9	1519.4	1550.1
47.5°	8588.6	7835.3	5472.9	2026.7	1671.9	1451.5	1343.9	1349.0	1377.2	1424.5	1446.4
50°	10006.8	9079.2	5561.3	1970.4	1671.9	1402.8	1260.6	1286.3	1309.3	1345.2	1358.0
52.5°	11706.7	10273.3	5269.2	1919.1	1682.1	1409.2	1190.1	1245.3	1261.9	1292.6	1297.8
55°	13282.6	10858.6	4530.0	1848.7	1684.7	1448.9	1130.0	1212.0	1242.7	1254.2	1253.0
57.5°	14197.3	10657.5	3662.7	1729.5	1674.4	1475.8	1091.5	1171.0	1229.9	1237.6	1226.0
60°	14023.0	9951.6	2696.8	1638.6	1598.8	1465.5	1079.9	1108.1	1201.7	1213.2	1197.8
62.5°	12680.4	8768.0	1871.8	1568.0	1432.2	1420.8	1076.1	1009.5	1140.2	1168.4	1146.6
65°	10192.5	6902.7	1322.1	1350.3	1255.5	1323.4	1055.6	907.0	1065.9	1104.3	1071.0
67.5°	7394.6	4670.9	954.4	1094.1	1137.6	1165.8	1009.5	832.7	981.3	1032.6	989.0
70°	4745.2	2522.5	670.0	722.5	958.3	990.3	930.1	766.1	895.5	954.4	907.0
72.5°	3373.2	1489.9	481.6	506.0	770.0	825.0	818.7	691.8	795.6	867.4	811.0
75°	2327.8	821.2	325.4	361.3	558.5	670.0	631.6	594.4	673.8	746.9	691.8
77.5°	1459.2	367.7	194.7	251.1	366.4	526.5	433.1	459.9	525.2	593.2	535.5
80°	812.2	142.2	108.9	166.6	199.9	383.0	239.5	295.9	386.9	435.6	389.5
82.5°	176.8	17.9	48.7	71.8	78.1	222.9	126.8	171.7	243.4	239.5	207.6
85°	0.0	0.0	8.9	10.2	5.1	96.0	46.1	56.4	79.4	74.3	56.4
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.6	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P964595
 CATALOG NUMBER: NVN-SB3C-740-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°	185°
0°	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0
2.5°	2306.0	2243.2	2197.1	2174.0	2154.9	2172.8	2183.0	2183.0	2226.6	2252.2	2262.5
5°	2089.5	1976.7	1890.9	1833.3	1798.7	1810.3	1823.1	1837.1	1892.2	1929.4	1953.6
7.5°	1939.6	1766.7	1636.0	1555.2	1513.0	1519.4	1528.4	1539.9	1593.7	1630.9	1662.9
10°	1911.4	1662.9	1478.4	1372.1	1320.8	1311.9	1306.8	1302.9	1335.0	1363.1	1388.8
12.5°	2026.7	1668.0	1410.5	1281.1	1218.3	1191.5	1160.7	1136.3	1141.4	1159.4	1191.5
15°	2233.0	1733.4	1388.8	1233.7	1155.6	1110.7	1074.8	1045.4	1038.9	1045.4	1050.5
17.5°	2468.7	1821.7	1386.2	1192.7	1095.3	1049.2	1019.8	992.8	983.9	985.1	991.6
20°	2625.0	1892.2	1378.5	1146.6	1037.7	996.7	971.1	944.1	935.2	937.8	939.0
22.5°	2640.4	1929.4	1366.9	1095.3	980.0	945.5	919.8	895.5	894.2	894.2	901.9
25°	2557.1	1929.4	1342.6	1049.2	925.0	894.2	871.1	841.7	846.9	849.4	859.7
27.5°	2427.7	1883.2	1296.5	1012.1	877.6	845.5	822.5	795.6	802.0	805.9	817.3
30°	2299.6	1824.3	1241.4	969.8	832.7	795.6	778.9	755.8	758.4	763.5	776.3
32.5°	2180.5	1761.6	1176.1	935.2	787.9	750.7	737.9	712.3	716.2	721.3	735.3
35°	2062.6	1692.4	1099.2	894.2	746.9	709.7	699.5	670.0	672.6	680.3	695.7
37.5°	1935.7	1619.3	1036.4	853.2	707.1	668.7	658.5	627.7	630.3	639.3	657.2
40°	1802.6	1547.5	974.9	809.6	664.9	626.5	617.5	584.1	586.7	597.0	616.2
42.5°	1668.0	1469.4	927.5	753.3	621.4	580.4	571.3	540.6	544.5	556.0	575.2
45°	1543.8	1376.0	896.8	690.5	580.4	534.2	525.2	497.0	504.7	517.5	536.8
47.5°	1437.4	1279.8	884.0	638.0	536.8	486.8	479.1	456.1	468.8	483.0	498.4
50°	1346.4	1187.6	867.4	584.1	495.8	445.9	438.2	422.8	439.4	453.6	467.6
52.5°	1281.1	1082.5	831.5	535.5	459.9	411.2	408.7	401.0	416.4	429.2	442.0
55°	1224.8	973.6	773.8	493.2	427.9	381.8	384.4	380.5	393.3	403.5	415.1
57.5°	1173.5	878.8	700.8	459.9	393.3	356.2	363.9	358.7	365.1	371.6	385.6
60°	1112.0	782.8	613.7	422.8	352.3	330.6	339.5	325.4	324.1	326.7	330.6
62.5°	1021.0	653.3	522.6	376.7	316.4	302.4	306.2	279.3	258.8	258.8	262.6
65°	894.2	525.2	438.2	325.4	275.4	263.9	261.4	222.9	194.7	192.2	203.7
67.5°	746.9	431.7	363.9	274.2	229.3	221.6	224.2	196.0	167.8	165.2	178.0
70°	608.5	357.4	293.4	219.0	176.8	184.5	196.0	167.8	140.9	137.0	148.6
72.5°	494.5	284.4	229.3	167.8	130.7	152.4	166.6	137.0	111.4	108.9	119.1
75°	381.8	208.8	164.0	114.0	94.8	117.9	130.7	99.9	79.4	75.5	84.6
77.5°	254.9	129.4	92.2	71.8	56.4	80.7	87.1	52.5	46.1	44.8	51.2
80°	155.0	60.2	39.7	34.5	19.2	29.4	34.5	21.7	24.3	25.6	30.7
82.5°	78.1	16.6	6.4	1.2	0.0	0.0	10.2	5.1	10.2	12.8	19.2
85°	6.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.6	6.4	11.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P964595
 CATALOG NUMBER: NVN-SB3C-740-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°	285°
0°	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0
2.5°	2334.2	2387.9	2439.2	2521.2	2605.8	2689.1	2773.6	2855.5	2885.1	2906.8	2955.5
5°	2065.2	2166.3	2284.2	2446.9	2621.1	2800.5	2982.4	3149.0	3224.5	3275.8	3391.1
7.5°	1787.2	1919.1	2088.2	2332.9	2605.8	2891.4	3177.2	3439.8	3561.5	3660.2	3835.7
10°	1511.7	1655.2	1869.2	2148.4	2517.4	2927.3	3321.9	3683.2	3840.8	3965.0	4203.3
12.5°	1269.6	1404.1	1628.3	1937.0	2379.0	2899.1	3405.2	3839.4	4025.3	4164.9	4426.3
15°	1099.2	1194.0	1392.6	1725.7	2215.0	2808.2	3410.3	3913.8	4117.5	4263.5	4490.3
17.5°	1004.4	1036.4	1165.8	1510.4	2033.1	2689.1	3362.9	3939.4	4157.2	4293.0	4450.5
20°	953.1	958.3	994.1	1231.1	1800.0	2577.6	3318.0	3965.0	4194.4	4308.4	4355.7
22.5°	912.1	912.1	921.2	1007.0	1498.9	2444.3	3304.0	4009.9	4245.5	4316.1	4218.7
25°	875.0	875.0	877.6	900.7	1187.6	2240.6	3295.0	4079.1	4316.1	4335.2	4067.5
27.5°	836.6	837.8	837.8	850.6	956.9	1963.9	3256.6	4168.8	4400.6	4360.9	3922.8
30°	798.2	800.7	800.7	809.6	846.9	1639.8	3181.0	4276.3	4510.8	4394.2	3779.3
32.5°	759.7	762.3	762.3	770.0	796.8	1309.3	3086.2	4375.0	4622.2	4408.3	3646.0
35°	720.0	723.9	721.3	731.5	759.7	1041.5	2965.7	4473.6	4742.7	4453.1	3580.7
37.5°	680.3	682.9	681.5	691.8	723.9	899.3	2826.1	4547.9	4906.7	4553.0	3658.8
40°	640.5	639.3	639.3	650.8	685.4	858.3	2650.6	4665.8	5142.4	4728.5	3999.7
42.5°	599.5	599.5	597.0	609.8	652.1	827.6	2482.8	4877.2	5485.7	5007.8	4604.3
45°	562.4	561.1	556.0	567.5	620.0	773.8	2423.8	5271.8	5993.1	5460.1	5335.8
47.5°	526.5	525.2	512.4	522.6	581.6	725.1	2644.2	5917.4	6696.3	6125.0	6021.3
50°	494.5	495.8	471.4	480.4	543.1	688.0	3122.0	6755.3	7630.3	7020.5	6670.7
52.5°	465.0	465.0	433.1	438.2	495.8	654.7	3576.8	7663.6	8862.8	8269.6	7427.9
55°	435.6	433.1	397.2	399.7	448.4	607.2	3644.8	8550.1	10543.6	10148.9	8463.0
57.5°	402.3	397.2	363.9	363.9	404.9	572.7	3159.3	9231.7	12629.2	12911.0	9955.5
60°	361.3	357.4	335.7	329.2	370.2	603.4	2229.2	9311.1	13974.3	16584.0	12813.6
62.5°	308.7	313.9	302.4	293.4	336.9	626.5	1320.8	8671.8	13648.9	17752.4	16236.8
65°	243.4	263.9	261.4	254.9	370.2	527.8	780.2	7444.6	12651.0	16809.5	15538.6
67.5°	207.6	221.6	217.8	217.8	388.2	401.0	490.7	5816.3	11277.6	15691.0	13879.5
70°	176.8	190.9	176.8	176.8	293.4	243.4	339.5	4061.2	9795.4	14453.5	12790.6
72.5°	146.1	160.1	144.7	134.5	234.4	181.9	248.6	2537.9	8388.7	13164.7	12045.0
75°	111.4	128.1	116.5	103.7	155.0	135.8	188.3	1474.6	6950.0	11263.5	10983.0
77.5°	70.4	92.2	87.1	73.0	114.0	98.6	135.8	877.6	5362.7	8801.3	9446.9
80°	43.6	47.4	48.7	46.1	65.3	66.6	92.2	499.6	3670.4	6133.9	7380.5
82.5°	28.2	28.2	21.7	24.3	32.0	38.4	52.5	188.3	2157.4	3734.5	5137.3
85°	20.5	17.9	11.5	11.5	15.4	19.2	20.5	57.6	875.0	1474.6	2008.8
87.5°	10.2	8.9	3.8	5.1	7.7	6.4	5.1	2.6	220.4	471.4	330.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P964595
 CATALOG NUMBER: NVN-SB3C-740-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	295°	305°	315°	325°	335°	345°	355°	360°
0°	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0	2575.0
2.5°	2981.1	3020.9	3023.4	3023.4	2988.8	2987.6	2917.0	2909.4
5°	3510.2	3535.8	3542.3	3529.5	3460.3	3409.0	3272.0	3242.5
7.5°	3994.5	4045.8	4045.8	4015.0	3902.3	3797.2	3598.7	3524.4
10°	4381.4	4440.3	4427.5	4364.8	4222.5	4077.8	3836.9	3739.6
12.5°	4569.8	4629.9	4596.6	4524.9	4386.5	4234.1	3980.4	3870.2
15°	4565.9	4549.3	4514.6	4505.7	4439.1	4323.8	4086.8	3966.3
17.5°	4403.2	4262.3	4235.3	4325.0	4409.5	4381.4	4179.0	4066.3
20°	4145.7	3899.7	3875.3	4047.0	4287.9	4410.9	4264.8	4161.1
22.5°	3874.1	3608.9	3552.5	3742.2	4104.7	4419.8	4373.7	4269.9
25°	3616.6	3350.1	3293.7	3470.5	3900.9	4404.4	4491.5	4403.2
27.5°	3401.4	3143.9	3091.3	3268.1	3705.0	4360.9	4609.4	4546.7
30°	3234.8	2996.5	2958.0	3128.5	3535.8	4307.0	4759.3	4724.7
32.5°	3137.4	2963.2	2977.3	3116.9	3444.9	4248.1	4902.8	4919.5
35°	3233.6	3241.3	3364.2	3421.9	3529.5	4239.2	5097.5	5162.8
37.5°	3711.4	3977.8	4232.7	4185.4	3943.3	4342.9	5388.3	5510.1
40°	4524.9	5071.9	5485.7	5305.1	4695.2	4660.7	5807.2	5989.2
42.5°	5519.0	6446.5	7128.1	6643.8	5665.1	5216.6	6405.5	6637.4
45°	6568.2	8141.5	9215.1	8208.1	6698.9	5995.6	7311.3	7493.2
47.5°	7673.9	10201.5	11590.2	9942.7	7657.2	6882.2	8546.2	8588.6
50°	8883.3	12460.1	14011.5	11676.1	8582.1	7898.0	10055.5	10006.8
52.5°	10035.0	14782.8	16381.6	13417.0	9394.3	9158.7	11806.7	11706.7
55°	11134.2	17104.1	18765.7	15090.2	10160.5	10824.1	13887.2	13282.6
57.5°	12408.9	19191.1	21222.8	16771.0	11231.5	12986.6	16213.8	14197.3
60°	14293.3	21562.3	24001.6	19074.4	13268.4	15259.3	17047.7	14023.0
62.5°	16699.3	23742.8	26021.9	21331.8	15314.4	15687.2	15819.1	12680.4
65°	17166.9	24295.0	26136.0	21935.2	15050.5	13306.9	12914.9	10192.5
67.5°	15926.8	23297.0	24542.2	20811.6	13313.3	10283.5	9691.6	7394.6
70°	14535.4	21394.5	21764.7	18901.5	11709.3	7563.7	6545.2	4745.2
72.5°	13109.5	18856.6	18090.5	16414.9	10291.2	5507.5	4720.8	3373.2
75°	11415.9	15519.3	14249.8	13638.6	8520.6	4322.4	3415.4	2327.8
77.5°	9142.0	10924.0	10584.6	10571.7	6403.0	3157.9	2279.1	1459.2
80°	6449.1	7089.6	6916.7	7962.1	4295.6	2290.7	1372.1	812.2
82.5°	3122.0	3920.2	4023.9	4741.3	2089.5	1347.8	316.4	176.8
85°	1222.2	1890.9	1595.0	1800.0	586.7	375.4	7.7	0.0
87.5°	137.0	219.0	201.1	158.9	71.8	15.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)